

## Chip Ferrite Bead BLM18□□□□□□N1□ Reference Specification

#### 1.Scope

This Reference Specification applies to Chip Ferrite Bead BLM18\_□N Series.

### 2.Part Numbering

(ex.) <u>BL</u> <u>M</u> <u>18</u> <u>AG</u> <u>121</u> <u>S</u> <u>N</u> <u>1</u> <u>D</u> (1) (2) (3) (4) (5) (6) (7) (8) (9)

(1)Product ID (2)Type (3)Dimension(LxW) (4)Characteristics (5)Typical Impedance at 100MHz

(6)Performance (7)Category (8)Numbers of Circuit (9)Packaging(D:Taping / B:Bulk)

#### 3.Rating

Customer	MURATA	Impedance (Ω) (at 100MHz, Under Standa Testing Condi		Curre	Rated Current (mA)		sistance nax.) Values	Remark
Part Number	Part Number		Typical	at 85°C	at 125°C	Initial Values	After Testing	Remark
	BLM18RK121SN1D	120±25%	120	2	00	0.25	0.35	
	BLM18RK121SN1B							
	BLM18RK221SN1D	220±25%	220	2	00	0.30	0.40	
	BLM18RK221SN1B BLM18RK471SN1D							For
	BLM18RK471SN1B	470±25%	470	2	00	0.50	0.60	Digital
	BLM18RK601SN1D							Interface
	BLM18RK601SN1B	600±25%	600	2	00	0.60	0.70	
	BLM18RK102SN1D							
	BLM18RK102SN1B	1000±25%	1000	2	00	0.80	0.90	
	BLM18PG300SN1D							
	BLM18PG300SN1B	20 min.	30	10	000	0.05	0.10	
	BLM18PG330SN1D						0.050	
	BLM18PG330SN1B	33±25%	33	3000*1	1000*1	0.025		
	BLM18PG600SN1D	40 .				0.1		
	BLM18PG600SN1B	40 min.	60	5	500		0.2	
	BLM18PG121SN1D	100.050/	120	2000*1	1000*1	0.05	0.10	
	BLM18PG121SN1B	120±25%	120	2000	1000	0.05	0.10	
	BLM18PG181SN1D	180±25%	180	1500*1	1000*1	0.09	0.18	
	BLM18PG181SN1B	100±2576	100	1300	1000	0.09	0.10	
	BLM18PG221SN1D	220±25%	220	1400*1	1000*1	0.10	0.14	
	BLM18PG221SN1B	22012070	220	1.00	1000	0.10	0.14	For DC
	BLM18PG331SN1D	330±25%	330	1200*1	1000*1	0.15	0.20	power line
	BLM18PG331SN1B						0.20	1
	BLM18PG471SN1D	470±25%	470	1000		0.20	0.26	
	BLM18PG471SN1B							
	BLM18KG221SN1D BLM18KG221SN1B	220±25%	220	2200*1	1000*1	0.050	0.060	
	BLM18KG331SN1D							
	BLM18KG331SN1B	330±25%	330	1700*1	1000*1	0.080	0.095	
	BLM18KG471SN1D			. 4	. 4			
	BLM18KG471SN1B	470±25%	470	1500*1	1000*1	0.130	0.145	
	BLM18KG601SN1D	202 + 252/	000	4000*1	4000*1	0.450	0.405	
	BLM18KG601SN1B	600±25%	600	1300*1	1000*1	0.150	0.165	
	BLM18AG121SN1D	400.050/	400			0.40	0.00	
	BLM18AG121SN1B	120±25%	120	500		0.18	0.28	_
	BLM18AG151SN1D	450:050/	450	-	00	0.05	0.05	For
	BLM18AG151SN1B	150±25%	150	5	00	0.25	0.35	general use
	BLM18AG221SN1D	220±25%	220		00	0.25	0.35	use
	BLM18AG221SN1B	∠∠∪±∠ე <sup>7</sup> 0	220	5	UU	0.25	0.35	

Spec. No. JENF243A-0003W-01

P.2/12

Customer MURATA		Impedance (Ω) (at 100MHz, Under Sta Testing Co	ndard			sistance nax.) Values	Remark	
Part Number	Part Number		Typical	ot ot	Initial Values	After Testing	Romaik	
	BLM18AG331SN1D BLM18AG331SN1B	330±25%	330	500	0.30	0.40		
	BLM18AG471SN1D BLM18AG471SN1B	470±25%	470	500	0.35	0.45	For	
	BLM18AG601SN1D BLM18AG601SN1B	600±25%	600	500	0.38	0.48	general use	
	BLM18AG102SN1D BLM18AG102SN1B	1000±25%	1000	400	0.50	0.60		
	BLM18BB050SN1D BLM18BB050SN1B	5±25%	5	700	0.05	0.10		
	BLM18BA050SN1D BLM18BA050SN1B	5±25%	5	500	0.2	0.3		
	BLM18BB100SN1D BLM18BB100SN1B	10±25%	10	700	0.10	0.20		
	BLM18BA100SN1D BLM18BA100SN1B	10±25%	10	500	0.25	0.35		
	BLM18BB220SN1D BLM18BB220SN1B	22±25%	22	600	0.20	0.30		
	BLM18BA220SN1D BLM18BA220SN1B	22±25%	22	500	0.35	0.45		
	BLM18BB470SN1D BLM18BB470SN1B	47±25%	47	550	0.25	0.35		
	BLM18BD470SN1D BLM18BD470SN1B	47±25%	47	500	0.3	0.4		
	BLM18BA470SN1D BLM18BA470SN1B	47±25%	47	300	0.55	0.65		
	BLM18BB600SN1D BLM18BB600SN1B	60±25%	60	550	0.25	0.35		
	BLM18BA750SN1D BLM18BA750SN1B	75±25%	75	300	0.70	0.80		
	BLM18BB750SN1D BLM18BB750SN1B	75±25%	75	500	0.30	0.40	For high speed	
	BLM18BB121SN1D BLM18BB121SN1B	120±25%	120	500	0.30	0.40	signal line	
	BLM18BD121SN1D BLM18BD121SN1B	120±25%	120	300	0.4	0.5		
	BLM18BA121SN1D BLM18BA121SN1B	120±25%	120	200	0.9	1.0		
	BLM18BB141SN1D BLM18BB141SN1B	140±25%	140	450	0.35	0.45		
	BLM18BB151SN1D BLM18BB151SN1B	150±25%	150	450	0.37	0.47		
	BLM18BD151SN1D BLM18BD151SN1B	150±25%	150	300	0.4	0.5		
	BLM18BB221SN1D BLM18BB221SN1B	220±25%	220	450	0.45	0.55		
	BLM18BD221SN1D BLM18BD221SN1B	220±25%	220	250	0.45	0.55		
	BLM18BB331SN1D BLM18BB331SN1B	330±25%	330	400	0.58	0.68		
	BLM18BD331SN1D BLM18BD331SN1B	330±25%	330	250	0.5	0.6		
	BLM18BD421SN1D BLM18BD421SN1B	420±25%	420	250	0.55	0.65		

Spec. No. JENF243A-0003W-01

P.3/12


<u> </u>	243A-0003W-01							P.3/12				
		Impedance (Ω) (at 100MHz, Under Standard		Rated Current		DC Resistance (Ω max.)						
Customer	MURATA				Testing Condition)				(mA)		Values	Remark
Part Number	Part Number	10011119 00		at at		at at		at at		Initial Values	After	Kemark
			Typical	ลเ 85°C	ลเ 125°C	Values	Testing					
	DI MAODO AZACNAD			05 0	123 0							
	BLM18BB471SN1D	470±25%	470	3	00	0.85	0.95					
	BLM18BB471SN1B							-				
	BLM18BD471SN1D	470±25%	470	2	50	0.55	0.65					
	BLM18BD471SN1B							-				
	BLM18BD601SN1D	600±25%	600	2	00	0.65	0.75					
	BLM18BD601SN1B							-				
	BLM18BD102SN1D	1000±25%	1000	2	00	0.85	0.95	For				
	BLM18BD102SN1B	.000==070				0.00	0.00					
	BLM18BD152SN1D	1500±25%	1500	1	50	1.2	1.3	high speed signal line				
	BLM18BD152SN1B	130012370	1300		30	1.2	1.5					
	BLM18BD182SN1D	1800±25%	1800	1	50	1.5	1.6					
	BLM18BD182SN1B	1000±23%	1600	'	30	1.5	1.0					
	BLM18BD222SN1D	0000 050/	0000	_	<b>-</b> 0	4.5	4.0					
	BLM18BD222SN1B	2200±25%	2200	ı	50	1.5	1.6	-				
	BLM18BD252SN1D											
	BLM18BD252SN1B	2500±25%	2500	1	50	1.5	1.6					
	BLM18TG121TN1D											
	BLM18TG121TN1B	120±25%	120	120 20		0.25	0.3	For general				
	BLM18TG221TN1D						<b>†</b>					
	BLM18TG221TN1B	220±25%	220		00	0.3	0.4					
	BLM18TG601TN1D							use				
	BLM18TG601TN1B	600±25%	600	2	00	0.45	0.6	(Thin type)				
	BLM18TG102TN1D							, ,,				
	BLM18TG102TN1B	1000±25%	1000	100		0.6	8.0					
	BLM18SG260TN1D											
	BLM18SG260TN1B	26±25%	26	6000*1	1000*1	0.007	0.012					
	BLM18SG700TN1D							1				
	BLM18SG700TN1B	70±25%	70	4000*1	1000*1	0.020	0.030					
	BLM18SG121TN1D							1				
	BLM18SG121TN1B	120±25%	120	3000*1	1000*1	0.025	0.035					
	BLM18SG221TN1D							-				
	BLM18SG221TN1B	220±25%	220	2500*1	1000*1	0.040	0.055					
	BLM18SG331TN1D							-				
	BLM18SG331TN1B	330±25%	330	1500*1	1000*1	0.070	0.085					
	BLM18SN220TN1D			<u> </u>				For DC				
	BLM18SN220TN1B	22±7	22	8000*1	5000*1	0.004	0.005	power line				
	BLM18KG260TN1D							(Thin type)				
	BLM18KG260TN1B	26±25%	26	6000*1	1000*1	0.007	0.012					
	BLM18KG300TN1D											
	BLM18KG300TN1B	30±25%	30	5000*1 1000*1 3500*1 1000*1		0.010	0.015					
	BLM18KG700TN1D		-					†				
	BLM18KG700TN1B	70±25%	70			0.022	0.032					
	BLM18KG101TN1D		-	-				1				
	BLM18KG101TN1B	100±25%	100	3000*1	1000*1	0.030	0.040					
	BLM18KG121TN1D							1				
	BLM18KG121TN1B	120±25%	120	3000*1	1000*1	0.030	0.040					
	PLINIONGIZITINIB		1	1			l	L				

<sup>•</sup> Operating Temperature : -55°C to +125°C • Storage Temperature : -55°C to +125°C


Spec. No. JENF243A-0003W-01


P.4/12

(\*1)In case of Rated current is more than 1A, Rated Current is derated as right figure depending on the operating temperature.




#### 4. Style and Dimensions





■ Equivalent Circuit



Resistance element becomes dominant at high frequencies.

■ Unit Mass (Typical value) BLM18\*\*\*\*\*SN1\*:0.005g BLM18\*\*\*\*\*TN1\*:0.004g

(in mm)

## 5.Marking

No marking.

BLM18SG\*\*\*TN1\* 0.5±0.15

BLM18SN\*\*\*TN1\* 0.6±0.15

BLM18TG\*\*\*TN1\* 0.6±0.1

BLM18KG\*\*\*TN1\* 0.6±0.15

BLM18\*\*\*\*\*SN1\* 0.8±0.15

6.Standard Testing

< Unless otherwise

Conditions

specified >

< In case of doubt

Temperature : Ordinary Temp. (15 °C to 35 °C ) Humidity : Ordinary Humidity (25%(RH) to 85%(RH)) Temperature : 20°C±2 °C Humidity : 60%(RH) to 70%(RH)

Atmospheric pressure: 86kPa to 106kPa

#### 7. Specifications

#### 7-1.Electrical Performance

	ectricari err	Officialise	
No.	Item	Specification	Test Method
7-1-1	Impedance	Meet item 3.	Measuring Frequency : 100MHz±1MHz Measuring Equipment : Agilent 4291A or the equivalent Test Fixture : Agilent 16192A or the equivalent
7-1-2	DC Resistance	Meet item 3.	Measuring Equipment : Digital multi meter  For BLM18SN_TN Measuring Equipment : YOKOGAWA 755611 or the equivalent Test Fixture : Agilent 16044A or the equivalent *Except resistance of the Substrate and Wire



## 7-2.Mechanical Performance

No.	echanical Pe Item		ification	Test Method				
7-2-1	Appearance	Meet item 4.		Visual Inspection and measured with Slide Calipers.				
	and							
7.0.0	Dimensions	N4		It shall be called an dear the substitute				
7-2-2	Bonding	Meet Table 1	•	It shall be soldered on the substrate.				
	Strength	Table 1		Applying Force(F): 6.8N Applying Time: 5s±1s				
			No damage	Applied direction :Parallel to substrate				
		Appearance Impedance	Within ±30%	Side view				
		Change	(for					
		(at 100MHz)	BLM18SN	R0.5				
		,	Within					
			±50%)					
		DC	Meet item 3.	Substrate				
7 0 0	Danding	Resistance	weet item 3.	It shall be caldered as the authorizate				
7-2-3	Bending Strength			It shall be soldered on the substrate. Substrate: Glass-epoxy 100mm×40mm×1.6mm				
	- Circingtii	-		Deflection: 1.0mm				
				Speed of Applying Force: 0.5mm/s Pressure jig				
				Keeping Time : 30s				
				Deflection				
				45mm 45mm Product				
				Product				
7-2-4	Vibration			It shall be soldered on the substrate.				
				Oscillation Frequency: 10Hz to 55Hz to 10Hz for 1 min				
				Total Amplitude : 1.5mm				
				Testing Time: A period of 2 hours in each of 3 mutually				
7-2-5	Resistance	Meet Table 2		perpendicular directions. (Total 6 h)  Pre-Heating: 150°C±10°C, 60s∼90s				
1-2-3	to Soldering	Weet Table 2	•	Solder : Sn-3.0Ag-0.5Cu				
	Heat	Table 2		Solder Temperature : 270°C±5°C				
		Appearance	No damage	Immersion Time: 10s±0.5s				
		Impedance	Within ±30%	Immersion and emersion rates : 25mm/s				
		Change	(for BLM18KG	Then measured after exposure in the room condition for 48h±4h.				
		(at 100MHz)	Within ±40%)					
			(for BLM18SN					
		DO.	Within ±50%)					
		DC Resistance	Meet item 3.					
		Resistance						
7-2-6	Drop		ll be no failure	It shall be dropped on concrete or steel board.				
		after tested.		Method : free fall				
				Height: 75cm Attitude from which the product is dropped: 3 direction				
				The number of times: 3 times for each direction(Total 9 times)				
7-2-7	Solderability	The electrode	es shall be at	Flux : Ethanol solution of rosin,25(wt)%				
			vered with new	Pre-Heating: 150°C±10°C, 60s~90s				
		solder coating	J.	Solder: Sn-3.0Ag-0.5Cu				
				Solder Temperature : 240°C±5°C				
				Immersion Time : 3s±1s Immersion and emersion rates : 25mm/s				
				אווווויסוסוטוז מווע פווופוסוטוז זמנפס . בטוווווויס				



## 7-3. Environmental Performance

It shall be soldered on the substrate.


No.	Item	Specifica	ation	Test Method
7-3-1	Temperature Cycle	Impedance Change (fc (at 100MHz) W	lo damage //ithin ±30% or BLM18KG //ithin-10%to 50%) or BLM18SN //ithin ±50%)	1 cycle: 1 step:-55 °C(+0 °C,-3 °C) / 30min±3min 2 step:Ordinary temp. / 10min to 15min 3 step:+125 °C(+3 °C,-0 °C) / 30min±3min 4 step: Ordinary temp. / 10min to 15min Total of 100 cycles Then measured after exposure in the room condition for 48h±4h.
7-3-2	Humidity	Meet Table 1.		Temperature: 40°C±2°C Humidity: 90%(RH) to 95%(RH) Time: 1000h(+48h,-0h) Then measured after exposure in the room condition for 48h±4h.
7-3-3	Heat Life			Temperature: 125°C±3°C (in case of Rated current is more than 1A, do the test at: +85 °C±3°C)  Applying Current: Rated Current Time: 1000h(+48h,-0h) Then measured after exposure in the room condition for 48h±4h.
7-3-4	Cold Resistance			Temperature: -55±2°C Time: 1000h(+48h,-0h) Then measured after exposure in the room condition for 48h±4h.

(in mm)

## Reference Only

## 8. Specification of Packaging

8-1.Appearance and Dimensions (8mm-wide paper tape)



(1) Taping

Products shall be packaged in the cavity of the base tape continuously and sealed by top tape and bottom tape.

- (2) Sprocket hole: The sprocket holes are to the right as the tape is pulled toward the user.
- (3) Spliced point: The base tape and top tape have no spliced point
- (4) Cavity: There shall not be burr in the cavity.
- (5) Missing components number

Missing components number within 0.1% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.

#### 8-2. Tape Strength


(1)Pull Strength

u •	
Top tape	5N min
Bottom tape	ON MIII.

(2)Peeling off force of Top tape

0.1N to 0.6N (Minimum value is typical.)

\*Speed of Peeling off:300mm/min



#### 8-3. Taping Condition

(1)Standard quantity per reel

Type	Quantity per 180mm reel
BLM18(except BLM18SG/BLM18TG)	4000 pcs. / reel
BLM18SG/BLM18TG	10000 pcs. / reel

- (2) There shall be leader-tape (top tape and empty tape) and trailer- tape (empty tape) as follows.
- (3)On paper tape, the top tape and the base tape shall not be adhered at the tip of the empty leader tape for more than 5 pitch.

#### (4)Marking for reel

The following items shall be marked on a label and the label is stuck on the reel.

(Customer part number, MURATA part number, Inspection number(\*1), RoHS Marking(\*2), Quantity, etc)

\*1) « Expression of Inspection No. »

 $\Box\Box$  OOOO  $\times\times\times$ 

(1) Factory Code

(2) Date

First digit Second digit Year / Last digit of year

: Month / Jan. to Sep. ightarrow 1 to 9, Oct. to Dec. ightarrow O, N, D

Third, Fourth digit: Day

(3) Serial No.

\*2) « Expression of RoHS Marking »

 $ROHS - \underline{Y}_{(1)} (\underline{\triangle})$ 


- (1) RoHS regulation conformity parts.
- (2) MURATĂ classification number

#### (5)Outside package


These reels shall be packed in the corrugated cardboard package and the following items shall be marked on a label and the label is stuck on the box.

(Customer name, Purchasing order number, Customer part number, MURATA part number, RoHS discrimination(\*2), Quantity, etc)

(6) Dimensions of reel and taping (leader-tape, trailer-tape)



#### 8-4. Specification of Outer Case



Outer Case Dimensions (mm)			Standard Reel Quantity in Outer Case (Reel)
W	D	Н	(Neel)
186	186	93	5

<sup>\*</sup> Above Outer Case size is typical. It depends on a quantity of an order.



## 9. 🛕 Caution

#### 9-1.Surge current

Excessive surge current (pulse current or rush current) than specified rated current applied to the product may cause a critical failure, such as an open circuit, burnout caused by excessive temperature rise.

Please contact us in advance in case of applying the surge current.

#### 9-2.Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (6) Disaster prevention / crime prevention equipment
- (2) Aerospace equipment
- (7) Traffic signal equipment
- (3) Undersea equipment
- (8) Transportation equipment (vehicles,trains,ships,etc.)(9) Applications of similar complexity and /or reliability requirements
- (4) Power plant control equipment(5) Medical equipment
- to the applications listed in the above


## 10. Notice

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

#### 10-1.Land pattern designing


- Standard land dimensions
- < For BLM18 series (except BLM18PG/BLM18SG/BLM18KG/ BLM18SN type) >



Туре	Soldering	а	b	С
BLM18 (except18PG/18SG/	Flow	0.7	2.2 to 2.6	0.7
BLM18KG/18SN type)	Reflow	0.7	1.8 to 2.0	0.7

(in mm)

< For BLM18PG/BLM18SG/BLM18KG/BLM18SN type > Chip Ferrite Bead



Туре	Rated Current	а	b	С		pad thic dimens	
	(A)				18µm	35µm	70µm
DI MAODO	0.5 to 1.5		Flow		0.7	0.7	0.7
BLM18PG BLM18SG	1.7 to 2.5	0.7	2.2 to 2.6	0.7	1.2	0.7	0.7
BLM18KG	3 to 4	Reliow		0.7	2.4	1.2	0.7
DLIVITORG	5 to 6		1.8 to 2.0		6.4	3.3	1.65
BLM18SN	8	0.7	2.0	0.7	-	6.4	3.3

(in mm)

## 10-2. Soldering Conditions

Products can be applied to reflow and flow soldering.

#### (1) Flux, Solder

Flux	Use rosin-based flux, but not highly acidic flux (with chlorine content exceeding 0.2(wt)%.) Do not use water-soluble flux.
Solder	Use Sn-3.0Ag-0.5Cu solder Standard thickness of solder paste : 100 μm to 200 μm

#### (2) Soldering conditions

• Pre-heating should be in such a way that the temperature difference between solder and ferrite surface is limited to 150°C max. Also cooling into solvent after soldering should be in such a way that the temperature difference is limited to 100°C max.

Insufficient pre-heating may cause cracks on the ferrite, resulting in the deterioration of product quality.


<sup>\*</sup>The excessive heat by land pads may cause deterioration at joint of products with substrate.

• Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.


#### (3) soldering profile

#### ☐Flow soldering profile



	Standard Profile	Limit Profile
Pre-heating	150°C、60s min.	
Heating	250°C、4∼6s	265°C±3°C, 5s max.
Cycle of flow	2 times	2 times

#### □Reflow soldering profile



	Standard Profile	Limit Profile
Pre-heating	150~180°C 、90s±30s	
Heating	above 220°C、30s∼60s	above 230°C、60s max.
Peak temperature	245±3°C	260°C,10s
Cycle of reflow	2 times	2 times

## 10-3. Reworking with soldering iron

• Pre-heating: 150°C, 1 min • Soldering iron output: 80W max.

• Tip temperature:  $350^{\circ}$ C max. 
• Tip diameter:  $\phi$  3mm max.

• Soldering time : 3(+1,-0) seconds. • Times : 2times max.

Note :Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the ferrite material due to the thermal shock.

#### 10-4. Solder Volume

Solder shall be used not to be exceeded as shown below.




Accordingly increasing the solder volume, the mechanical stress to product is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.

#### 10-5. Attention regarding P.C.B. bending

The following shall be considered when designing and laying out P.C.B.'s.

(1) P.C.B. shall be designed so that products are not subject to the mechanical stress for board warpage. <Products direction>




Products shall be located in the sideways direction (Length: a<b) to the mechanical stress.

P.11/12

(2)Products location on P.C.B. separation. Products (A, B, C, D) shall be located carefully

so that products are not subject to the mechanical stress due to warping the board. Because they may be subjected the mechanical stress in order of  $A>C>B \cong D$ .



#### 10-6. Mounting density

Add special attention to radiating heat of products when mounting the inductor near the products with heating. The excessive heat by other products may cause deterioration at joint of this product with substrate.

#### 10-7. Operating Environment

Do not use this product under the following environmental conditions, on deterioration of the Insulation Resistance of the Ferrite material and/or corrosion of Inner Electrode may result from the use.

- (1) in the corrodible atmosphere (acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc.)
- (2) in the atmosphere where liquid such as organic solvent, may splash on the products
- (3) in the atmosphere where the temperature / humidity changes rapidly and it is easy to dew

#### 10-8. Resin coating

The impedance value may change and/or it may affect on the product's performance due to high cure-stress of resin to be used for coating / molding products. So please pay your careful attention when you select resin. In prior to use, please make the reliability evaluation with the product mounted in your application set.

#### 10-9. Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1)Cleaning temperature shall be limited to 60°C max. (40°C max. for IPA.)
- (2)Ultrasonic cleaning shall comply with the following conditions, avoiding the resonance phenomenon at the mounted products and P.C.B.

Power:20W/ℓ max. Frequency:28kHz to 40kHz Time:5 min max.

(3)Cleaner

- 1.Alternative cleaner
  - •Isopropyl alcohol (IPA)
- 2. Aqueous agent
  - •PINE ALPHA ST-100S
- (4) There shall be no residual flux and residual cleaner after cleaning.

In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.

(5)Other cleaning

Please contact us.

MURATA MFG.CO., LTD.



P.12/12

#### 10-10. Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the product.





#### 10-11. Storage Conditions

(1)Storage period

Use the products within 6 months after delivered.

Solderability should be checked if this period is exceeded.

(2)Storage conditions

• Products should be stored in the warehouse on the following conditions.

Temperature: -10°C to 40°C

Humidity : 15% to 85% relative humidity No rapid change on temperature and humidity

- Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization
  of electrode, resulting in poor solderability.
- Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be stored under the airtight packaged condition.

(3)Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

#### 11 . / Note

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.