



Let our IDXPert printer work for you.

IDXPert™
HANDHELD LABELER

Rely on the IDXPERT™ for all your identification needs.

When you need clear, durable labels on the spot, you need the IDXPERT™ Hand-held Labeller from Brady. It offers the crisp printing, easy formatting, convenient label sizes, and portability you need for electrical identification, datacomm installations, facility and safety labelling, industrial ID, and much more.



EASY

- Drop, Lock, & Print quick loading cartridge lets you change ribbon and labels in one fast step.
- Just push the ON button, and the IDXPERT™ Smart Cartridge automatically formats your labels... no extra buttons to press, no label size to select.

FAST

- Print labels on the spot, 50-70 % faster than dot matrix printers.
- Intuitive user interface lets you easily access complex functions in just a few steps.




CLEAR

- Sharp, non-smearing 300 dpi thermal transfer printing makes your labels legible and your work look great.
- Large, informative display clearly displays label to be printed.




SMART

- Die-cut label styles help organise print jobs and make you more efficient.
- Store frequently used set-ups in memory for even faster access.
- Edge-to-edge printing and die cut labels reduce your materials waste.



VERSATILE

- Self-Lams, Sleeves, Repositionable Wire Markers, and more – over 90 label styles.
- Continuous label styles give you more choices for miscellaneous labelling.
- 82 symbols plus bar codes.



STRONG

- Rugged, drop-tested construction.
- Ergonomic design really fits your hand!

MULTIPLE

- Make pre-sized and pre-formatted Punch Block ID strips for 110-blocks, 66-blocks, BIX-blocks, and patch panels. Print single strips or multiples at one time (serialized data carries over to next strip).
- Pre-sized Desi-Strip Faceplate Inserts (48.26 mm strips) fit into recessed areas commonly found on network port face plates. This new label offers more convenience and time savings.

PC CONNECTIVE

- Create and print your job from your PC using Brady's LabelMark™ Labelling Software. Compatible with Windows®.

VARIABLE

- The IDXPART v2.0 Hand-held Labeller offers 21 font sizes, plus font autosizing, fine-tuneable HR barcode fonts, and a narrow-width barcode option. Print large or small, with 21 text sizes from 1.52 mm to 31.75 mm high, and label sizes up to 38.10 mm wide.

31.75 mm

21 FONT SIZES




Electrical ID

Wire & Cable Markers – Adhesive Wrap Around

Durable vinyl cloth wrap around wire and cable markers. Firm adhesive can be removed cleanly and reapplied if necessary. Printer automatically “multiple repeats” your text for 360° legend visibility.

- **B-498 Vinyl Cloth** material. Ideal for wrapping wires and cable. Aggressive tack adhesive but still repositionable.
Temp. Range: -40°C to 70°C.




Max. Wire Diameter	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
				A	B	
2.80 mm	★	X-7-498	300	12.70	12.70	BK on WT
4.00 mm	★	X-11-498	275	12.70	19.05	BK on WT
5.00 mm	★	X-163-498	225	12.70	25.40	BK on WT
5.00 mm	★	X-18-498	225	19.05	25.40	BK on WT
5.00 mm	★	X-19-498	200	25.40	25.40	BK on WT
7.00 mm	★	X-162-498	165	12.70	38.10	BK on WT
7.00 mm	★	X-103-498	200	25.40	31.75	BK on WT
7.00 mm	★	X-31-498	200	25.40	38.10	BK on WT
14.00 mm	★	X-21-498	95	25.40	63.50	BK on WT
22.00 mm	★	X-23-498	60	25.40	101.60	BK on WT

Wire & Cable Markers – Self Laminating

Protected printing area offers superior chemical and abrasion resistance. Features a non-printed clear area that wraps around and overlaminates the printed text. Printer automatically “multiple repeats” your text in the white print area.

- **B-427 Vinyl Self-Laminating** material, resistant to water, oil, solvents, and abrasion.
Temp. range: -70°C to 70°C.
UL recognised.




Max. Wire Diameter	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm			Colour
				A	B	C	
4.00 mm	▶	XSL-11-427	500	12.70	19.05	9.53	BK on WT
4.00 mm	▶	XSL-96-427	250	25.40	19.05	9.53	BK on WT
5.00 mm	▶	XSL-17-427	500	12.70	25.40	9.53	BK on WT
5.00 mm	▶	XSL-18-427	250	19.05	25.40	9.53	BK on WT
5.00 mm	▶	XSL-19-427	250	25.40	25.40	9.53	BK on WT
7.00 mm	▶	XSL-102-427	250	12.70	31.75	9.53	BK on WT
7.00 mm	▶	XSL-103-427	250	25.40	31.75	12.70	BK on WT
7.00 mm	▶	XSL-115-427	250	38.10	31.75	12.70	BK on WT
8.00 mm	▶	XSL-29-427	450	12.70	38.10	12.70	BK on WT
8.00 mm	▶	XSL-30-427	250	19.05	38.10	12.70	BK on WT
8.00 mm	▶	XSL-31-427	250	25.40	38.10	12.70	BK on WT
8.00 mm	▶	XSL-31-427-YL-BK	250	25.40	38.10	12.70	BK on YL
8.00 mm	▶	XSL-32-427	225	38.10	38.10	12.70	BK on WT
14.00 mm	▶	XSL-21-427	100	25.40	63.50	19.05	BK on WT
14.00 mm	▶	XSL-21-427-YL-BK	100	25.40	63.50	19.05	BK on YL
14.00 mm	▶	XSL-116-427	100	38.10	63.50	19.05	BK on WT
22.00 mm	▶	XSL-23-427	85	25.40	101.60	25.40	BK on WT
22.00 mm	▶	XSL-23-427-YL-BK	85	25.40	101.60	25.40	BK on YL
22.00 mm	▶	XSL-33-427	85	38.10	101.60	25.40	BK on WT
33.00 mm	▶	XSL-34-427	50	38.10	152.40	38.10	BK on WT

Wire & Cable Markers – Permasleeve™ Sleeves

These full circle heat-shrink sleeves are the ultimate in marker durability, permanence and aesthetic appearance. Fast shrink rate saves time and costs during installation. Available as individual 25.40 mm long markers or in cut-to-length continuous supply.

- **B-342 Heat Shrink Polyolefin** material, 3-to-1 shrink ratio, self-extinguishing, meets material and physical properties requirements of MIL-DTL-23053/5C class 1, MIL-M-81531, MIL-STD-202F, method 215 and UL 224.
Temp. Range: -55°C to 135°C.





Wire Diameter Range	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
25.78 mm Marker Length						
1.20 - 2.80 mm dia		XPS-125-1	100	25.78	5.96	BK on WT
1.60 - 3.80 mm dia		XPS-187-1	100	25.78	8.50	BK on WT
2.40 - 5.50 mm dia		XPS-250-1	100	25.78	11.15	BK on WT
3.20 - 8.10 mm dia		XPS-375-1	100	25.78	16.38	BK on WT
Continuous (cut-to-length)						
1.20 - 2.80 mm dia		XPS-125-CONT	1 roll (cont.)	2.44 m	5.96	BK on WT
1.20 - 2.80 mm dia		XPS-125-CONT-YL-BK	1 roll (cont.)	2.44 m	5.96	BK on YL
1.60 - 3.80 mm dia		XPS-187-CONT	1 roll (cont.)	2.44 m	8.50	BK on WT
1.60 - 3.80 mm dia		XPS-187-CONT-YL-BK	1 roll (cont.)	2.44 m	8.50	BK on YL
2.40 - 5.50 mm dia		XPS-250-CONT	1 roll (cont.)	2.44 m	11.15	BK on WT
2.40 - 5.50 mm dia		XPS-250-CONT-YL-BK	1 roll (cont.)	2.44 m	11.15	BK on YL
3.20 - 8.10 mm dia		XPS-375-CONT	1 roll (cont.)	2.44 m	16.38	BK on WT

Wire & Cable Markers – Flags

Pre-formatted with two printable zones on either side of a thin void space, allowing label to be easily folded around wires to create a two-sided, printed flag. A pre-printed line makes it easy to centre the label on the wire. This marker utilises the new “Next Zone” feature on the IDXPRT v2.0 printer.

- **B-499 Nylon Cloth** material, permanent adhesive.
Pliable for rough or smooth surfaces.
Temp. Range: -70°C to 90°C. UL recognised.




Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm			Colour
				A	B	C	
Standard Flag	★	XF-151-499	115	25.40	25.40	6.350	BK on WT
approx 25.40 x 25.40 mm resulting flag size							
Low Profile Flag	★	XF-152-499	200	12.70	38.10	6.350	BK on WT
approx 127 x 38.10 mm resulting flag size							

Electrical ID

Terminal Block Markers

Specially-designed, narrow-width markers automatically set to fixed spacing between legends and rotate to top-down orientation for perfect alignment on terminal blocks. Printer can auto-serialise these labels to save you time.

- **B-498 Vinyl Cloth** material.
Temp. Range: -40°C to 70°C.






Width of Strip	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
				A	B	
6.09 mm wide	●	XC-240-498	1 roll (cont.)	6.10	6.10 m	BK on WT
8.00 mm wide	●	XC-318-498	1 roll (cont.)	8.07	6.10 m	BK on WT
9.53 mm wide	●	XC-375-498	1 roll (cont.)	9.53	6.10 m	BK on WT

Automation & Electrical Component Markers

Various sizes and label types for marking relays, solenoids, switches, drive motors, and other components.

- **B-499 Nylon Cloth** material, permanent adhesive. Pliable for rough or smooth surfaces. Temp. Range: -70°C to 90°C. UL recognised.
- **B-428 Metallised Polyester** material, permanent adhesive, silver finish. Temp. Range: -40°C to 80°C. UL recognised.
- **B-422 Gloss Polyester** material, permanent adhesive. For smooth surfaces. Temp. Range: -40°C to 100°C. UL recognised.
- **B-483 Ultra Aggressive Polyester** permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces. Temp. Range: -40°C to 100°C. UL recognised.
- **B-580 Indoor/Outdoor Vinyl** material, permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colours Temp. Range: -40°C to 82°C.



Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
				A	B	
Nylon Cloth (Extra Pliable)	▲	X-11-499	275	19.05	12.70	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-84-499	250	22.86	12.70	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-162-499	165	38.10	12.70	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-30-499	300	38.10	19.05	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-78-499	125	50.80	25.40	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-132-499	200	31.75	38.10	BK on WT
Metallised Polyester	▲	X-17-428-SV-BK	450	25.40	12.70	BK on SV
Metallised Polyester (Black Border)	▲	X-24-428-SVBB-BK	450	28.70	12.70	BK on SV
Metallised Polyester	▲	X-29-428-SV-BK	450	38.10	12.70	BK on SV
Metallised Polyester	▲	X-30-428-SV-BK	325	38.10	19.05	BK on SV
Metallised Polyester	▲	X-20-428-SV-BK	100	50.80	25.40	BK on SV
Polyester (Gloss)	▲	X-7-422	350	12.70	12.70	BK on WT
Polyester (Gloss)	▲	X-17-422	500	25.40	12.70	BK on WT
Polyester (Gloss)	▲	X-29-422	500	38.10	12.70	BK on WT
Polyester (Ultra Aggressive)	▲	X-61-483	100	50.80	12.70	BK on WT
Polyester (Gloss)	▲	X-30-422	250	38.10	19.05	BK on WT
Polyester (Gloss)	▲	X-19-422	250	25.40	25.40	BK on WT
Polyester (Ultra Aggressive)	▲	X-20-483	100	50.88	25.40	BK on WT
Polyester (Gloss)	▲	X-132-422	250	31.75	38.10	BK on WT
Polyester (Gloss)	○	XC-1000-422	1 roll (cont.)	9.14 m	25.40	BK on WT
Indoor/Outdoor Vinyl*	○	XC-1000-580-OR-BK	1 roll (cont.)	9.14 m	25.40	BK on OR


*For additional continuous general purpose tapes, refer to "Facility & Safety labels" on p. 10 for 23 more parts.

Cable Markers

Ideal for marking data cabling, with a protected printing area for superior resistance to abrasion, dirt, oils, solvents, and water.

Features a clear, non-printed area which wraps around and overlaminates the printed text. Printer automatically “multiple repeats” your text in white print area.

- **B-427 Vinyl Self-Laminating** material, resistant to water, oil, solvents, and abrasion. Temp. range: -70°C to 70°C. UL recognised.




Sized to Fit	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm			Colour
				A	B	C	
2 pair Fibre/Coaxial, Single/Multi-Mode	▶	XSL-19-427	250	25.40	25.40	9.53	BK on WT
CAT-5, 4 pair UTP Copper	▶	XSL-102-427	250	12.70	31.75	9.53	BK on WT
CAT-5, 4 pair UTP Copper, Fibre, Coaxial	▶	XSL-103-427	250	25.40	31.75	12.70	BK on WT
CAT-5, 4 pair UTP Copper	▶	XSL-115-427	250	38.10	31.75	12.70	BK on WT
CAT-5, 4 pair UTP Copper	▶	XSL-29-427	450	12.70	38.10	12.70	BK on WT
CAT-5, 4 pair UTP Copper	▶	XSL-30-427	250	19.05	38.10	12.70	BK on WT
CAT-5, 4 pair UTP Copper, Fibre, Coaxial	▶	XSL-31-427	250	25.40	38.10	12.70	BK on WT
CAT-5, 4 pair UTP Copper, Fibre, Coaxial	▶	XSL-31-427-YL-BK	250	25.40	38.10	12.70	BK on YL
CAT-5, 4 pair UTP Copper, Fibre, Coaxial	▶	XSL-32-427	225	38.10	38.10	12.70	BK on WT
25 pair Copper, 4-12 pair Fibre, Coaxial	▶	XSL-21-427	100	25.40	63.50	19.05	BK on WT
25 pair Copper, 4-12 pair Fibre, Coaxial	▶	XSL-21-427-YL-BK	100	25.40	63.50	19.05	BK on YL
25 pair Copper, 4-12 pair Fibre, Coaxial	▶	XSL-116-427	100	38.10	63.50	19.05	BK on WT
50 pair Copper, 24 pair Fibre, Backbone	▶	XSL-23-427	85	25.40	101.60	25.40	BK on WT
50 pair Copper, 24 pair Fibre, Backbone	▶	XSL-23-427-YL-BK	85	25.40	101.60	25.40	BK on YL
50 pair Copper, 24 pair Fibre, Backbone	▶	XSL-33-427	85	38.10	101.60	25.40	BK on WT
100 pair Copper, 36 pair Fibre, Backbone	▶	XSL-34-427	50	38.10	152.40	38.10	BK on WT

Cable Flags

Pre-formatted with two printable zones on either side of a thin void space, allowing label to be easily folded around data cables to create a two-sided, printed flag. A pre-printed line makes it easy to centre the label on the cable. This marker utilizes the new “Next Zone” feature on the IDXPert v2.0 printer.

- **B-499 Nylon Cloth** material, permanent adhesive. Pliable for rough or smooth surfaces. Temp. Range: -70°C to 90°C. UL recognised.




Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm			Colour
				A	B	C	
Standard Flag	★	XF-151-499	115	25.40	25.40	6.350	BK on WT
approx 25.40 x 25.40 mm resulting flag size							
Low Profile Flag	★	XF-152-499	200	12.70	38.10	6.350	BK on WT
approx 127 x 38.10 mm resulting flag size							

Voice/DataComm ID

Punch Block & Patch Panel I.D.

Now you can make fully-formatted punch block strips in one easy process. Choose the width of material that will fit your equipment. Then, select the appropriate punch block configuration from a list pre-loaded into your IDXPRT™ v2.0 printer (ex: 110 block - 4 pair). The printer automatically prints the grid lines in the correct size and populates the cells with data based on the serialisation you specify.

- **B-412 Polypropylene Tag** material, non-adhesive, much thicker than paper. Temp. range: -40°C to 100°C.
- **B-422 Gloss Polyester** material, permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces. Temp. range: -40°C to 100°C.



1	3	6	9	12	15	18
25	27	30	33	36	39	42
A1	A2	NOT USED	B8B	1F 22	2F 22	12
507	T4	T5	T6	NOT USED	NOT USED	77
						5


Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
Non-Adhesive Slide-in Strips*						
9.53 mm Wide Strips		XC-375-412	1 roll (cont.)	7.32 m	9.530	BK on WT
12.07 mm Wide Strips		XC-475-412	1 roll (cont.)	7.32 m	12.07	BK on WT
15.88 mm Wide Strips		XC-625-412	1 roll (cont.)	7.32 m	15.88	BK on WT
Adhesive Stick-On Strips*						
9.53 mm Wide Strips		XC-375-422	1 roll (cont.)	9.14 m	9.530	BK on WT
12.07 mm Wide Strips		XC-475-422	1 roll (cont.)	9.14 m	12.07	BK on WT
15.88 mm Wide Strips		XC-625-422	1 roll (cont.)	9.14 m	15.88	BK on WT
Label Each Port						
Stick-on Gloss Polyester		X-7-422	350	12.70	12.70	BK on WT

* Determine need for slide-in strips or stick-on strips, then access the templates for 110-blocks, BIX-blocks, or 66-blocks in your IDXPRT v2.0 printer.

Faceplate & Outlet Labels

Label your ports, jacks, and outlets with a variety of adhesive labels or slide-in strips. The IDXPRT v2.0 printer contains preset templates for 48.26 mm Desi-Strip/Faceplate Strips.

- **B-412 Polypropylene Tag** material, non-adhesive, much thicker than paper. Temp. range: -40°C to 100°C.
- **B-422 Gloss Polyester** material, non-adhesive, much thicker than paper. Temp. range: -40°C to 100°C.
- **B-483 Ultra Aggressive Polyester** permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces. Temp. Range: -40°C to 100°C. UL recognised.





Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
Non-Adhesive Slide-in Strips*						
Slide-in Polypropylene Tag Stock	○	XC-375-412	1 roll (cont.)	7.32 m	9.530	BK on WT
Slide-in Polypropylene Tag Stock	○	XC-475-412	1 roll (cont.)	7.32 m	12.07	BK on WT
Adhesive Stick-On Strips*						
Polyester (Gloss)	○	XC-375-422	1 roll (cont.)	9.14 m	9.530	BK on WT
Polyester (Gloss)	○	XC-475-422	1 roll (cont.)	9.14 m	12.07	BK on WT
Stick-on Individual Labels						
Polyester (Gloss)	▲	X-7-422	350	12.70	12.70	BK on WT
Polyester (Gloss)	▲	X-29-422	500	38.10	12.70	BK on WT
Polyester (Gloss)	▲	X-17-422	500	25.40	12.70	BK on WT
Polyester (Gloss)	▲	X-30-422	250	38.10	19.05	BK on WT
Polyester (Gloss)	▲	X-61-483	100	50.80	12.70	BK on WT

* Access the Desi-Strip template in your IDXPRT printer and your strip cuts to a 48.26 mm length for a perfect fit and big time savings.

ID for Data Centre Equipment, Bays, Racks & Frames


Durable materials with permanent adhesive in a variety of sizes for marking racks, bays, frames, slots, and other voice/data equipment.

- **B-422 Gloss Polyester** material, permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces.
Temp. Range: -40°C to 100°C. UL recognised.
- **B-483 Ultra Aggressive Polyester** material, extra-strong permanent adhesive for powder-coated/textured surfaces. Best on flat surfaces.
Temp. Range: -40°C to 120°C. UL recognised.
- **B-432 Gloss Clear Polyester** material, permanent adhesion, nameplate-like quality, good for metal or textured surfaces.
Temp. Range: -40°C to 100°C.
- **B-580 Indoor/Outdoor Vinyl** material, permanent adhesion, very pliable, good for rough surfaces and outdoor use, wide range of colours.
Temp. Range: -40°C to 82°C.



Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
Polyester (Gloss) - for smooth or textured surfaces	▲	X-7-422	350	12.70	12.70	BK on WT
Polyester (Gloss) - for smooth or textured surfaces	▲	X-17-422	500	25.40	12.70	BK on WT
Polyester (Gloss) - for smooth or textured surfaces	▲	X-29-422	500	38.10	12.70	BK on WT
Polyester (Gloss) - for smooth or textured surfaces	▲	X-30-422	250	38.10	19.50	BK on WT
Polyester (Gloss) - for smooth or textured surfaces	▲	X-19-422	250	25.40	25.40	BK on WT
Polyester (Gloss) - for smooth or textured surfaces	▲	X-132-422	250	31.75	38.10	BK on WT
Polyester (Gloss White) - for smooth or textured surfaces	⊙	XC-1000-422	1 roll (cont.)	9.14 m	25.40	BK on WT
Polyester (Ultra Aggressive) - for smooth or textured surfaces	▲	X-17-483	500	25.40	12.70	BK on WT
Polyester (Ultra Aggressive) - for smooth or textured surfaces	▲	X-61-483	100	50.80	27.70	BK on WT
Polyester (Ultra Aggressive) - for smooth or textured surfaces	▲	X-20-483	100	50.80	25.40	BK on WT
Polyester (Gloss Clear) - for smooth or textured surfaces	⊙	XC-1000-432-CL-BK	1 roll (cont.)	9.14 m	25.40	BK on CL
Indoor/Outdoor Vinyl (coloured supplies)*	⊙	XC-500-580-YL-BK	1 roll (cont.)	9.14 m	12.70	BK on YL
Indoor/Outdoor Vinyl (coloured supplies)*	⊙	XC-1000-580-YL-BK	1 roll (cont.)	9.14 m	25.40	BK on YL
Indoor/Outdoor Vinyl (coloured supplies)*	⊙	XC-1500-580-YL-BK	1 roll (cont.)	9.14 m	38.10	BK on YL

*For additional colours of continuous vinyl tapes, refer to "Facility & Safety labels" on p.10 for 21 more parts.



MRO/Facility/Safety

Indoor/Outdoor Grade Facility & Safety Labels

This indoor/5-yr outdoor pliable vinyl conforms well to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins, and equipment. Aggressive permanent adhesive; labels offer excellent resistance to oils, detergents, dirt, grime, and many solvents.

- **B-580 Indoor/Outdoor Vinyl** material, permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colours.
Temp. Range: -40°C to 120°C. UL recognised.





Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
A	B				
⊙	XC-500-580-WT-BK	1 roll (cont.)	9.14 m	12.70	BK on WT
⊙	XC-1000-580-WT-BK	1 roll (cont.)	9.14 m	25.40	BK on WT
⊙	XC-1500-580-WT-BK	1 roll (cont.)	9.14 m	38.10	BK on WT
⊙	XC-500-580-OR-BK	1 roll (cont.)	9.14 m	12.70	BK on OR
⊙	XC-1000-580-OR-BK	1 roll (cont.)	9.14 m	25.40	BK on OR
⊙	XC-1500-580-OR-BK	1 roll (cont.)	9.14 m	38.10	BK on OR
⊙	XC-500-580-YL-BK	1 roll (cont.)	9.14 m	12.70	BK on YL
⊙	XC-1000-580-YL-BK	1 roll (cont.)	9.14 m	25.40	BK on YL
⊙	XC-1500-580-YL-BK	1 roll (cont.)	9.14 m	38.10	BK on YL
⊙	XC-500-580-CL-BK	1 roll (cont.)	9.14 m	12.70	BK on CL
⊙	XC-1000-580-CL-BK	1 roll (cont.)	9.14 m	25.40	BK on CL
⊙	XC-1500-580-CL-BK	1 roll (cont.)	9.14 m	38.10	BK on CL
⊙	XC-500-580-RD-WT	1 roll (cont.)	9.14 m	12.70	WT on RD
⊙	XC-1000-580-RD-WT	1 roll (cont.)	9.14 m	25.40	WT on RD
⊙	XC-1500-580-RD-WT	1 roll (cont.)	9.14 m	38.10	WT on RD
⊙	XC-500-580-GN-WT	1 roll (cont.)	9.14 m	12.70	WT on GN
⊙	XC-1000-580-GN-WT	1 roll (cont.)	9.14 m	25.40	WT on GN
⊙	XC-1500-580-GN-WT	1 roll (cont.)	9.14 m	38.10	WT on GN
⊙	XC-500-580-BL-WT	1 roll (cont.)	9.14 m	12.70	WT on BL
⊙	XC-1000-580-BL-WT	1 roll (cont.)	9.14 m	25.40	WT on BL
⊙	XC-1500-580-BL-WT	1 roll (cont.)	9.14 m	38.10	WT on BL
⊙	XC-500-580-WT-RD	1 roll (cont.)	9.14 m	12.70	RD on WT
⊙	XC-1000-580-WT-RD	1 roll (cont.)	9.14 m	25.40	RD on WT
⊙	XC-1500-580-WT-RD	1 roll (cont.)	9.14 m	38.10	RD on WT



Bins & Storage ID, General Industrial ID


Choose from several materials with aggressive adhesives for use in commercial/industrial applications.

- B-499 Nylon Cloth material, permanent adhesive. Pliable for rough or smooth surfaces. Temp. Range: -70°C to 90°C. UL recognised.
- B-422 Gloss Polyester material, permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces. Temp. Range: -40°C to 100°C. UL recognised.
- B-483 Ultra Aggressive Polyester material, extra-strong permanent adhesive for powder-coated/textured surfaces. Best on flat surfaces. Temp. Range: -40°C to 120°C. UL recognised.
- B-580 Indoor/Outdoor Vinyl material, permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colours. Temp. Range: -40°C to 120°C. UL recognised.



Material Notes	Diagram	Order Reference	Labels per Cartridge	Dimensions – mm		Colour
				A	B	
Nylon Cloth (Extra Pliable)	▲	X-11-499	275	19.05	12.70	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-84-499	250	22.86	12.70	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-162-499	165	38.10	12.70	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-30-499	300	38.10	19.05	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-78-499	125	50.80	25.40	BK on WT
Nylon Cloth (Extra Pliable)	▲	X-132-499	200	31.75	38.10	BK on WT
Nylon Cloth (Round Label)	✖	X-82-499	300	9.53 dia		BK on WT
Nylon Cloth (Round Label)	✖	X-83-499	300	12.70 dia		BK on WT
Polyester (Gloss)	▲	X-7-422	350	12.70	12.70	BK on WT
Polyester (Gloss)	▲	X-17-422	500	25.40	12.70	BK on WT
Polyester (Gloss)	▲	X-29-422	500	38.10	12.70	BK on WT
Polyester (Gloss)	▲	X-30-422	250	38.10	19.05	BK on WT
Polyester (Gloss)	▲	X-19-422	250	25.40	25.40	BK on WT
Polyester (Gloss)	▲	X-132-422	250	31.75	38.10	BK on WT
Polyester (Ultra Aggressive)	▲	X-17-483	500	25.40	12.70	BK on WT
Polyester (Ultra Aggressive)	▲	X-61-483	100	50.80	12.70	BK on WT
Polyester (Ultra Aggressive)	▲	X-20-483	100	50.80	25.40	BK on WT
Indoor/Outdoor Vinyl (coloured supplies)*	⊙	XC-500-580-YL-BK	1 roll (cont.)	9.14 m	12.70	BK on YL
Indoor/Outdoor Vinyl (coloured supplies)*	⊙	XC-1000-580-YL-BK	1 roll (cont.)	9.14 m	25.40	BK on YL
Indoor/Outdoor Vinyl (coloured supplies)*	⊙	XC-1500-580-YL-BK	1 roll (cont.)	9.14 m	38.10	BK on YL

*For additional colours of continuous industrial tapes, refer to "Facility & Safety labels" on facing page for 21 more parts.



The label options you need for your applications...



Electrical Identification

Versatile label styles, sizes, and materials for all types of wire, cable, and component labelling.

- Repositionable labels
- Self-laminating labels
- Full circle heat-shrink sleeves
- Continuous vinyl tapes

MRO/Facility/Safety ID

Tough label materials that conform to smooth or rough surfaces in a variety of sizes to meet virtually any general identification need.

- Continuous vinyl tapes
- Aggressive Permanent Adhesive
- Resistant to oils, detergent, dirt, and many solvents

Voice/Datacomm ID

Versatile sizes and materials for wire, cable, ports, faceplates, racks, bays, frames, slots, and other voice/data equipment.

- Continuous labels
- Die-cut labels
- Self-laminating labels
- Non-adhesive slide-in strips

Two printer keypad layouts. Identical functionality and supplies.

Printer and Accessories



Order Reference	Description
XPRT-ABC	IDXPert v2.0 Printer – ABC Layout*
XPRT-KEY	IDXPert v2.0 Printer – KEYBOARD Layout*
XPRT-AC	AC Adapter (for ABC or KEY printers)
LM3	LabelMark™ Labelling Software
PCCABLE-1	Spare Serial PC Communications Cable
81701	Serial-to-USB Adapter for Serial PC Cable
PKK-4	Cleaning Kit
XPRT-HC-ABC	Spare Hard Case for ABC Layout Printer
XPRT-HC-KEY	Spare Hard Case for KEYBOARD Layout Printer

* Printer ships with: Hardside case, 38.10 mm x 9.14 m continuous tape, PC cable, and product CD with driver.

IDXPert™ Kits

European: IDXPert-EUR-ABC-KIT-LM ... reference no. 806805

UK: IDXPert-UK-ABC-KIT-LM reference no. 806806

Content of the kit

- IDXPert Hand-held Labeller (ABC Layout)
- LabelMark V3.1.1 - Europe CD
- Cleaning Kit IDXPert
- AC Adapter (Europe / UK)

Including consumables:

- Selflaminating labels (Order Ref.: XSL-30-427)
- Gloss Polyester labels (Order Ref.: X-17-422)
- Outdoor Vinyl Black on White (Order Ref.: XC-1500-580-WT-BK)



BRADY Belgium

Lindestraat 20
9240 Zele
Tel.: +32 (0) 52 45 78 11
Fax: +32 (0) 52 45 78 12

BRADY Denmark

Islandsgade 12/P. O. Box 36
5100 Odense C
Tel.: +45 66 14 44 00
Fax: +45 66 14 44 50

BRADY France

Parc EURO CIT
45, avenue de l'Europe
59436 Roncq Cedex
Tel.: +33 (0) 3 20 76 94 48
Fax: +33 (0) 3 20 76 76 06

BRADY Germany

Otto-Hahn-Str. 5-7
632 25 Langen
Tel.: +49 (0) 6103 7598 660
Fax: +49 (0) 6103 7598 670

BRADY Hungary

Puskas Tivadar u. 4.
H-2040 Budaörs
Tel.: +36 23 428 525
Fax: +36 23 428 526

BRADY Italy

Via Lazzaroni 7
21047 Saronno (VA)
Tel.: +39 02 9628 6014
Fax: +39 02 9670 0882

BRADY Norway

Breivika Industriervei 7
6018 Alesund
Tel.: +47 70 19 10 30
Fax: +47 70 19 05 67

BRADY Slovakia

Na Pántoch 18
83106 Bratislava
Tel.: +421 2 3300 4800
Fax: +421 2 3300 4801

BRADY Spain

Carretera de Barcelona, 88
Esc B Entresuelo 9C
083 02 Mataró
Tel.: +34 900 902 993
Fax: +34 900 902 994

BRADY Sweden

Karins väg 5
194 54 Upplands Väsby
Tel.: +46 (0) 8 590 057 30
Fax: +46 (0) 8 590 818 68

BRADY Turkey

Selvili Sok. No: 3/4
4. Levent, Istanbul 34330
Tel.: +90 212 264 02 20
Fax: +90 212 270 83 19

BRADY UK

Wildmere Industrial Estate
Banbury, Oxon OX16 3JU
Tel.: +44 (0) 1295 228 288
Fax: +44 (0) 1295 228 100

BRADY Worldwide

Australia 612-8717-6300
Brazil 55-11-3686-4720
China (Beijing) 86-10-6788-7799
China (Shanghai) 86-21-6886-3666
China (Wuxi) 86-510-528-2222
Hong Kong 852-2359-3149
Japan 81-45-461-3600
Canada 1-800-263-6179
Korea 82-31-451-6600
Latin America 1-414-540-5560
Malaysia 60-4-646-2700
Mexico 525-399-6963
New Zealand 61-2-8717-2200
Philippines 63-2-658-2077
Singapore 65-6477-7261
Taiwan 886-3-327-7788
Thailand 66-2-793-9200
USA 1-800-537-8791