





LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L3	REVISED PER ECO-15-014472	09OCT2015	NK	MM




RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL



- | | |
|---|---|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING. |
| 2 | 0.00254[.000100]–0.00508[.000200] MATTE TIN–LEAD OVER
0.00127[.000050] NICKEL ENTIRE POST. |
| 3 | HOUSING: LCP, COLOR–BLACK.
POSTS: PHOSPHOR BRONZE. |
| 4 | 0.00254[.000100]–0.00508[.000200] MATTE TIN OVER
0.00127[.000050] NICKEL ENTIRE POST. |
| 5 | PRELIMINARY PART – NOT RELEASED FOR PRODUCTION. |
| 6 | OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI |

		4	35.56 [1.400]	14	35.69 [1.484]	15	6-146133-3	
		4	33.02 [1.300]	13	33.15 [1.384]	14	6-146133-2	
		4	30.48 [1.200]	12	30.61 [1.284]	13	6-146133-1	
		4	27.94 [1.100]	11	28.07 [1.184]	12	6-146133-0	
		4	25.40 [1.000]	10	27.53 [1.084]	11	5-146133-9	
		4	22.86 [.900]	9	24.99 [.984]	10	5-146133-8	
		4	20.32 [.800]	8	22.45 [.884]	9	5-146133-7	
		4	17.78 [.700]	7	19.91 [.784]	8	5-146133-6	
		4	15.24 [.600]	6	17.37 [.684]	7	5-146133-5	
		4	12.70 [.500]	5	14.83 [.584]	6	5-146133-4	
		4	10.16 [.400]	4	12.29 [.484]	5	5-146133-3	
		4	7.62 [.300]	3	9.75 [.384]	4	5-146133-2	
		4	5.08 [.200]	2	7.21 [.284]	3	5-146133-1	
		5	4	17.78 [.700]	7	19.91 [.784]	8	1-146133-5
		OBSOLETE 6	2	35.56 [1.400]	14	35.69 [1.484]	15	1-146133-3
2	33.02 [1.300]		13	33.15 [1.384]	14	1-146133-2		
2	30.48 [1.200]		12	30.61 [1.284]	13	1-146133-1		
2	27.94 [1.100]		11	28.07 [1.184]	12	1-146133-0		
2	25.40 [1.000]		10	27.53 [1.084]	11	146133-9		
2	22.86 [.900]		9	24.99 [.984]	10	146133-8		
OBSOLETE 6	2	20.32 [.800]	8	22.45 [.884]	9	146133-7		
	2	17.78 [.700]	7	19.91 [.784]	8	146133-6		
6 OBSOLETE	2	15.24 [.600]	6	17.37 [.684]	7	146133-5		
	2	12.70 [.500]	5	14.83 [.584]	6	146133-4		
	2	10.16 [.400]	4	12.29 [.484]	5	146133-3		
	2	7.62 [.300]	3	9.75 [.384]	4	146133-2		
	2	5.08 [.200]	2	7.21 [.284]	3	146133-1		
	PLATING	C	B	A	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 30SEP94 K KNAUB CHK 30SEP94 G DUBNICZKI APVD 30SEP94 G DUBNICZKI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .127[.005] 4 PLC ± - ANGLES ± -		NAME SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, SINGLE ROW, .100 X.100 C/L, .025 SQ. POST	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO RESTRICTED TO A1 00779 C-146133	
MATERIAL - FINISH SEE TABLE 		WEIGHT -		SCALE 1:1 SHEET 1 of 1 REV 1.3	
CUSTOMER DRAWING					