


[Skip to content](#)Search By: Part Number Text [Tips](#)

Thursday, April 27, 2006

[Sign In](#)[Home](#) > [Products](#) > [By Type](#) > [PolySwitch Resettable Devices](#) > [Product Feature Selector](#) > Product Details

Product Details for LVR025K-2



LVR025K-2

Tyco Part Number: F27075-000

[Active](#)

PolySwitch Resettable Devices

[RoHS Compliant](#)

Product Highlights:

- Radial Application
- Family Name = LVR
- Through Hole Construction
- Radial Construction
- IH (Room Temperature) = .25 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SCD25017](#) (PDF, English)

Catalog Pages / Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL Listed = File No. E74889

Electrical Characteristics:

- [IH \(Room Temperature\) \(Amps.\)](#) = 0.25
- [IT \(Room Temperature\) \(Amps.\)](#) = 0.56
- [Vmax Operating \(V\)](#) = 240
- [Rmin \(\$\Omega\$ \)](#) = 1.30
- [Rmax \(\$\Omega\$ \)](#) = 2.100
- [R1 Max \[Post Trip\] \(\$\Omega\$ \)](#) = 3.80
- [UL Rated Current \(Amps.\)](#) = 3.5
- Tripped Power Dissipation (Typical) (W) = 1.50

Termination Related Features:

- Construction = Radial, Through Hole

Body Related Features:

- Lead Type = Kinked
- CSA File No. = 78165C

Contact Related Features:

- Application = Radial
- Family Name = LVR

Configuration Related Features:

- Coating = Coated

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041437

Conditions for Usage:

- [Operating Temperature \(Max.\) \(\$^{\circ}\text{C}\$ \)](#) = 85

Packaging Related Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Italiano](#) | [正體中文 \(繁體\) \(Chinese\)](#) | [中文 \(•体\) \(Simplified Chinese\)](#) | [日本語 \(Japanese\)](#)

Country Sites: [China](#) | [Japan](#)

© [2006 Tyco Electronics All Rights Reserved](#)

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)