

C-TRIP CHARACTERISTICS

Application Examples:

Low inrush motors, lighting, wiring protection, appliances, business equipment, and control circuit applications. Relatively long thermal trip delay and medium magnetic trip point.

Type Designation

$\frac{2}{(a)} \quad \frac{C}{(b)} \quad \frac{N}{(c)} \quad \frac{U}{(d)} \quad \frac{60}{(e)}$

(a) = Number of Poles

(b) = Trip Characteristic

(c) = Blank: without neutral pole

= N: with neutral pole

(d) = U: UL/CSA version

= R: ring tongue terminals,
UL/CSA version

= Blank: European version

(e) = Rated Current

Approvals:



Voltage Rating^①

Interrupting Capacity (UL/CSA - Ratings)

Group Short Circuit (UL/CSA - Ratings)

Interrupting Capacity (VDE - Ratings)

Mechanical Endurance

Calibration Temperature

Standard Pack and Weight

Terminal Size Acceptability

Terminal Torque

Basic Dimensions (Elevation View)

① Not European standard rating.

② Please refer to page 21 for specific applications.

③ DC rating (Manufacturer's self certification):
One pole 48VDC, two pole series 125VDC

* VDE pending

ONE POLE



1C

ONE POLE PLUS NEUTRAL




2CN

Rated Current	Type/ Cat. No.	Approvals	Type/ Cat. No.	Approvals
0.3A	1CU03	UL SP	2CNU03	UL SP
0.5A	1CU05	UL SP	2CNU05	UL SP
0.75A	1CU075	UL SP	2CNU075	UL SP
0.8A	NA		NA	
1.0A	1CU1	UL SP	2CNU1	UL SP
1.6A	1CU1.6	UL SP	2CNU1.6	UL SP
2.0A	1CU2	UL SP	2CNU2	UL SP
2.5A	1CU2.5	UL SP	2CNU2.5	UL SP
3.0A	1CU3	UL SP	2CNU3	UL SP
3.5A	1CU3.5	UL SP	2CNU3.5	UL SP
4.0A	1CU4	UL SP	2CNU4	UL SP
5.0A	1CU5	UL SP	2CNU5	UL SP
6.0A	1CU6	UL SP	2CNU6	UL SP
8.0A	1CU8	UL SP	2CNU8	UL SP
10A	1CU10	UL SP	2CNU10	UL SP
12A	NA		NA	
12.5A	NA		NA	
13A	1CU13	UL SP	2CNU13	UL SP
15A	1CU15	UL SP	2CNU15	UL SP
16A	1CU16	UL SP	2CNU16	UL SP
20A	1CU20	UL SP	2CNU20	UL SP
25A	1CU25	UL SP	2CNU25	UL SP
30A	1CU30	UL SP	2CNU30	UL SP
32A	1CU32	UL SP	2CNU32	UL SP
40A	1CU40	UL SP	2CNU40	UL SP
50A	1CU50	UL SP	2CNU50	UL SP
60A	1CU60	UL SP	2CNU60	UL SP
63A	1CU63	UL SP	2CNU63	UL SP
277VAC			277VAC	
0.3-60A (RC): 10kA with UL-listed RK5 back-up fuse or MCCB			0.3-60A (RC): 10kA with UL-listed RK5 back-up fuse or MCCB	
0.3-10A (RC): 10kA; 13-60A (RC): 5kA no branch circuit protection required			0.3-10A (RC): 10kA; 13-60A (RC): 5kA no branch circuit protection required	
0.3-63A (RC): 10kA			0.3-63A (RC): 10kA	
10000 ON/OFF operations			10000 ON/OFF operations	
40°C (104°F)			40°C (104°F)	
10/0.3A - 32A = 1.4kg (3.1 lb.) 40A - 63A = 1.6kg (3.5 lb.)			5/0.3A - 32A = 1.3kg (2.9 lb.) 40A - 63A = 1.45kg (3.2 lb.)	
Top: 18-3 AWG; Bottom: 18-2 AWG			Top: 18-3 AWG; Bottom: 18-2 AWG	
20 lb.in.			20 lb.in.	


TWO POLE



THREE POLE



Basic Dimensions (side view)



Rated Current **Type/
Cat. No.** **Approvals**

0.3A	2CU03	UL, CE, A
0.5A	2CU05	UL, CE, A
0.75A	2CU075	UL, CE, A
0.8A	NA	
1.0A	2CU1	UL, CE, A
1.6A	2CU1.6	UL, CE, A
2.0A	2CU2	UL, CE, A
2.5A	2CU2.5	UL, CE, A
3.0A	2CU3	UL, CE, A
3.5A	2CU3.5	UL, CE, A
4.0A	2CU4	UL, CE, A
5.0A	2CU5	UL, CE, A
6.0A	2CU6	UL, CE, A
8.0A	2CU8	UL, CE, A
10A	2CU10	UL, CE, A
12A	NA	
12.5A	NA	
13A	2CU13	UL, CE, A
15A	2CU15	UL, CE, A
16A	2CU16	UL, CE, A
20A	2CU20	UL, CE, A
25A	2CU25	UL, CE, A
30A	2CU30	UL, CE, A
32A	2CU32	UL, CE, A*
40A	2CU40	UL, CE, A*
50A	2CU50	UL, CE, A*
60A	2CU60	UL, CE, A*
63A	2CU63	UL, CE, A*

480Y/277VAC

0.3-60A (RC): 10kA with UL-listed
RK5 back-up fuse or MCCB

0.3-10A (RC): 10kA; 13-60A (RC): 5kA
no branch circuit protection required


0.3-63A (RC): 10kA

10000 ON/OFF operations²

40°C (104°F)

5/1.4kg (3.1 lb.)

Top: 18-3 AWG; Bottom: 18-2 AWG
20 lb.in.



**Type/
Cat. No.** **Approvals**

3CU03	UL, CE, A
3CU05	UL, CE, A
3CU075	UL, CE, A
NA	
3CU1	UL, CE, A
3CU1.6	UL, CE, A
3CU2	UL, CE, A
3CU2.5	UL, CE, A
3CU3	UL, CE, A
3CU3.5	UL, CE, A
3CU4	UL, CE, A
3CU5	UL, CE, A
3CU6	UL, CE, A
3CU8	UL, CE, A
3CU10	UL, CE, A
NA	
NA	
3CU13	UL, CE, A
3CU15	UL, CE, A
3CU16	UL, CE, A
3CU20	UL, CE, A
3CU25	UL, CE, A
3CU30	UL, CE, A
3CU32	UL, CE, A*
3CU40	UL, CE, A*
3CU50	UL, CE, A*
3CU60	UL, CE, A*
3CU63	UL, CE, A*

480Y/277VAC

0.3-60A (RC): 10kA with UL-listed
RK5 back-up fuse or MCCB

0.3-10A (RC): 10kA; 13-60A (RC): 5kA
no branch circuit protection required


0.3-63A (RC): 10kA

10000 ON/OFF operations²


40°C (104°F)

4/1.68kg (3.7 lb.)


Top: 18-3 AWG; Bottom: 18-2 AWG
20 lb.in.



V-EA-C Trip 0.3A Through 10A Rated Current



V-EA-C Trip 13A Through 63A Rated Current



"C" Magnetic Trip Parameters

Rated current 0.3A to 63A.

1. Hold for a minimum of 100ms at surge of 5 times rated current.
2. Trip in under 100ms at 10 times rated current.

NB: Trip curves shown comply with North American standards. For trip curves according to European standards please consult Altech.