



Series 511 Standard DIP Socket w/Bifurcated Contacts & Solder Pin Tails

FEATURES


- Bifurcated Contacts with Solder Tail or Wire Wrap Pins

GENERAL SPECIFICATIONS

- **STANDARD BODY:** Black UL 94V-0 Glass-filled 4/6 Nylon
- **BIFURCATED CONTACTS:** Grade A Spring-tempered Phosphor Bronze per QQ-B-750
- **PIN PLATING:** 50-130μ min. matte Sn per ASTM B545-97(2004)e1 over 50μ Ni per SAE AMS-QQ-N-290B; -OR- 50-130μ 90/10 Sn/Pb per MIL-T-10727 Type 1 over 50μ Ni per SAE AMS-QQ-N-290B; -OR- 10μ [0.25μ] min. Au per MIL-G-45204 over 50μ Ni per SAE AMS-QQ-N-290B
- **CONTACT CURRENT RATING:** 1 amp
- **OPERATING TEMPERATURE:** -67°F to 221°F [-55°C to 105°C] Sn; -67°F to 257°F [-55°C 125°C] Au
- **INSERTION FORCE:** 110g/pin average
- **WITHDRAWAL FORCE:** 75g/pin average
- **ACCEPTS LEADS:** Flat up to 0.014 thick x 0.020 wide [0.36 x 0.51], Round up to 0.020 [0.51] dia.
- **LEAD LENGTHS:** accepts lengths from seating plane from 0.075-0.160 [1.91-4.06]

MOUNTING CONSIDERATIONS

- **SUGGESTED PCB HOLE SIZE:** 0.035 ±0.002 [0.89 ± 0.05] dia.



ORDERING INFORMATION

XX-X 511-X XXX XX

Rails Option
WR = Without Rails

Plating
0 = Sn
1 = Au
OTL = Sn/Pb

Termination
1 = Solder Pin Tail


Series

Row-to-Row Spacing (Dim. "C")
2 = 0.200 [5.08]
3 = 0.300 [7.62]
4 = 0.400 [10.16]
6 = 0.600 [15.24]

No. of Pins
(See Table)

Centers "C"	Width "D"	Available Sizes
0.200 [5.08]	0.290 [7.36]	8, 10
0.300 [7.62]	0.390 [9.90]	8, 14-20
0.400 [10.16]	0.490 [12.45]	22
0.600 [15.24]	0.690 [17.54]	8-24, 28-40, 48

CONTACT DETAIL



ALL DIMENSIONS: INCHES [MILLIMETERS]
ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED
FOR WIRE WRAP PINS, SEE DATA SHEETS 12005
CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION.
SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE
FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS
WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE
CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA
TEL 215-781-9956 • FAX 215-781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



12004
Rev. 5.2
1 of 1