

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/9/05	

6

5

4


3

2



1

APPROVED: _____

DATE: _____ TITLE: _____



SHOWN AS 12 POLE



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Plating:

Contacts: Brass, Tin plated

Screws: Steel, Nickel plated

Hardware: Brass, Tin plated

Electrical:

Operating voltage: 300 VAC max.

Current rating: 15 Amps max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 500 Mohms min.

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Mechanical:

Wire range: 22 — 14 AWG

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 235°C for 5 seconds

Positions: 2 thru 26
A = .325 [8.25] x No. of Positions + .071 [1.80]
B = .325 [8.25] x No. of Spaces
REPLACE XX IN PART NUMBER WITH TOTAL # OF SCREW
POLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				Holes			
.X ± .10				ØXX ± .10			
.XX ± .020				ØXXX ± .015			
.XXX ± .015				ØXXX ± .010			
APPROVALS				DATE			
DRAWN				SS			
6/9/05							
CHECKED							
APPROVED							
TITLE				.325 [8.25] STACKED BARRIER BLOCK			
VERTICAL, PCB TAILS, BARRIER ENDS							
SIZE				PART NO.			
X				TBH-XX-01-B			
REV.				-			
SCALE: NTS				SHEET 1 OF 1			

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.325 [8.25] STACKED BARRIER BLOCK

VERTICAL, PCB TAILS, BARRIER ENDS

PART NO.

TBH-XX-01-B

REV.

SHEET 1 OF 1

6

5

4

3

2

1