


60mm sq.**San Ace 60****General Specifications**

- Material.....Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1)
- Expected LifeRefer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature ...-30°C to +70°C (Non-condensing)

60×60×25mm [Mass : 90g] **9R type****Specifications** The following nos. **have pulse sensors and ribs.** For ribless, append "1" to the model no.


Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m³/min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]			
109R0605H401	5	4.5 to 5.5	0.34	1.70	3,800	0.53 18.7	40.2 0.161	28	−20 to +70	60,000/60°C			
109R0605F401			0.20	1.00	3,200	0.44 15.5	29.4 0.118	24	−20 to +60				
109R0605M401			0.13	0.65	2,600	0.36 12.7	19.6 0.079	20	−20 to +70				
109R0612J401	12	10.8 to 13.2	0.47	5.64	7,600	1.06 37.1	155.0 0.622	44	−20 to +60	40,000/60°C			
109R0612G401			0.24	2.88	5,600	0.78 27.5	87.3 0.351	39	−20 to +70		60,000/60°C		
109R0612D401		10.2 to 13.8	0.21	2.52	5,150	0.72 25.4	73.5 0.295	37					
109R0612S401			6 to 13.8	0.17	2.04	4,600	0.65 23.0	56.8 0.228		33			
109R0612H401		0.11		1.32	3,800	0.53 18.7	40.1 0.161	28					
109R0612F401		0.09		1.08	3,200	0.44 15.5	29.4 0.118	24					
109R0612M401		0.06		0.72	2,600	0.36 12.7	19.6 0.079	20					
109R0624J401		24	21.6 to 26.4	0.24	5.76	7,600	1.06 37.1	155.0 0.622		44		−20 to +60	40,000/60°C
109R0624G401			20.4 to 27.6	0.13	3.12	5,600	0.78 27.5	87.3 0.351		39		−20 to +70	
109R0624D401				12 to 27.6	0.12	2.88	5,150	0.72 25.4	73.5 0.295	37			
109R0624S401	0.08		1.92		4,600	0.65 23.0	56.8 0.228	33					
109R0624H401	0.06		1.44		3,800	0.53 18.7	40.2 0.161	28					
109R0624F401	0.05		1.20		3,200	0.44 15.5	29.4 0.118	24					
109R0624M401	14 to 27.6		0.04		0.96	2,600	0.36 12.7	19.6 0.079	20				
109R0648J401	48	43.2 to 52.8	0.12	5.76	7,600	1.06 37.1	155.0 0.622	44	−20 to +60	40,000/60°C			
109R0648G401		43 to 53	0.07	3.36	5,600	0.78 27.5	87.3 0.351	39	−20 to +70		60,000/60°C		
109R0648H401		40 to 53	0.04	1.92	3,800	0.53 18.7	40.2 0.161	28					

Other sensor specifications are available as options. Please refer to the index (pp. 498 to 499).

Dimensions (unit: mm) (With ribs)

Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)

Inlet side, Outlet side




Options (unit: mm)

Finger Guards



Model : 109-139E Surface treatment : Nickel-chrome plating (silver) Color : 109-139H : Cation electropainting (black)

Inlet side, Outlet side



Resin Finger Guards



Model : 109-1003G











Mass : 7g







Resin Filter Kits

Model : 109-1003F13 (13PPI), 109-1003F20 (20PPI)
: 109-1003F30 (30PPI), 109-1003F40 (40PPI)



Mass : 11g

60mm sq.**San Ace 60****60×60×25mm** [Mass : 90g]**Airflow - Static Pressure Characteristics****109R0612J401****109R0624J401****109R0648J401****109R0612G401****109R0624G401****109R0612S401****109R0624S401****109R0605H401****109R0612H401****109R0624H401****109R0605M401****109R0612M401****109R0624M401**

**109R0648G401****109R0612D401****109R0624D401****109R0648H401****109R0605F401****109R0612F401****109R0624F401**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[109R0605M4021](#) [109R0612F402](#) [109R0624F402](#) [109R0624S4021](#) [109R0605F402](#) [109R0605M402](#)
[109R0612D402](#) [109R0612J402](#) [109R0612S402](#) [109R0624S402](#) [109R0648G402](#) [109R0605H4021](#) [109R0612G4021](#)
[109R0624G4021](#) [109R0612J4021](#) [109R0624G402](#) [109R0612S4021](#) [109R0648H4021](#) [109R0624F4021](#)
[109R0624H402](#) [109R0612G402](#) [109R0612H4021](#) [109R0605H402](#) [109R0612M4021](#) [109R0612M402](#)
[109R0612H402](#) [109R0612F4021](#) [109R0624H4021](#) [109R0648H402](#) [109R0648G4D011](#) [109R0648H4D01](#)
[109R0624S4D01](#) [109R0612J4D011](#) [109R0624S4D011](#) [109R0624M402](#) [109R0624H4D011](#) [109R0624J402](#)
[109R0624H4D01](#) [109R0624G4D01](#) [109R0648H4D011](#) [109R0648J402](#) [109R0648J4021](#) [109R0648J4D01](#)
[109R0612S4D01](#) [109R0648G4D01](#) [109R0612F4D011](#) [109R0648G4021](#) [109R0605F4021](#) [109R0612F4D01](#)
[109R0624M4D01](#) [109R0624M4D011](#) [109R0612G4D01](#) [109R0612G4D011](#) [109R0624D402](#) [109R0624D4D01](#)
[109R0624G4D011](#) [109R0612M4D01](#) [109R0612S4D011](#) [109R0624M4021](#) [109R0624F4D01](#) [109R0612M4D011](#)
[109R0624F4D011](#) [109R0624J4021](#) [109R0605M4D01](#) [109R0612D4D011](#) [109R0605H4D01](#) [109R0624J4D01](#)
[109R0605F4D01](#) [109R0612D4021](#) [109R0612D4D01](#) [109R0612H4D01](#) [109R0612H4D011](#) [109R0624D4021](#)
[109R0612J4D01](#)