


FCI P/N (NOTE 1)	LENGTH "A" (NOTE 1)	AGERE COMCODE
56980-YXXX-ZZ	XXX	—
56980-M004-WH	4m	700017394

CABLE COLOR CODE  
TABLE

ZZ	COLOR
N	NATURAL
WH	WHITE
BK	BLACK
SL	SLATE
GN	GREEN
BR	BROWN
YE	YELLOW
BL	BLUE
RD	RED
OR	ORANGE

SPECIFICATIONS	
INSERTION LOSS	0.2dB MAX
RETURN LOSS	50dB MIN
FIBER PROTRUSION	50nm
FIBER UNDERCUT	GR326
APEX OFFSET	50um MAX
ROC	7-25mm
TENSILE TEST	SEE NOTE 3



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	Electronics		FCI	www.fciconnect.com		
ltr	ecn no	dr	date	linear	NOMINALS ONLY		projection	title	FCI	www.fciconnect.com			
A	V20457	JRW	3/20/02		UNLESS NOTED								
B	V20730	JRW	4/24/02	angles		dr J. WITMER 3/20/02		INCH	product family FIBER OPTICS	code			
				engr G. WARNER 3/20/02		chr G. WARNER 3/20/02							
				appd G. WARNER 3/20/02		scale N/A		size	dwg no	sheet			
				sheet		A4 56980							
				revision		3		cage code		4			
				index		22526		B					