




- 2 PER FEDERAL STANDARD H-28 3 WIRE METHOD.
DIMENSION OVER WIRES TO BE .497-.510

AMP PART NO & CUST PART NO	TIN	.12 X 45°	846793-5
AMP PART NO	GOLD	.03 R	846793-2
AMP PART NO	TIN	.03 R	846793-1
MARKING	PIN FINISH	A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. YEAGER 10NOV11 CHK D. EABY 10NOV11		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .02 3 PLC ± .005 4 PLC ± — ANGLES — ± — FINISH		NAME RECEPTACLE ASSEMBLY, LGH—1, FEED—THROUGH — — —	
MATERIAL GLASS EPOXY (MOLDED)		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-846793	RESTRICTED TO —
				SCALE 2:1	SHEET 1 of 1
				REV J	