

# Intel® Celeron® Processor 807UE (1M Cache, 1.0 GHz)

[Add to Compare](#)

## SPECIFICATIONS

### Essentials

Memory Specifications  
Graphics Specifications  
Package Specifications  
Advanced Technologies  
Intel® Data Protection Technology  
Intel® Platform Protection Technology

### COMPATIBLE PRODUCTS

### PRODUCT IMAGES

### ORDERING / SSPECS / STEPPINGS

## SPECIFICATIONS

### Essentials

Status	Launched
Launch Date	Q4'11
Processor Number	807UE
# of Cores	1
# of Threads	1
Clock Speed	1 GHz
Intel® Smart Cache	1 MB
Instruction Set	64-bit
Embedded Options Available	Yes
Lithography	32 nm
Max TDP	10 W
Recommended Customer Price	TRAY: \$117.00

### Memory Specifications

Max Memory Size (dependent on memory type)	4 GB
Memory Types	DDR3-1066/1333
# of Memory Channels	1
ECC Memory Supported ‡	Yes

### Graphics Specifications

Processor Graphics ‡	Intel® HD Graphics
Graphics Base Frequency	350 MHz
Graphics Max Dynamic Frequency	800 MHz
Intel® Quick Sync Video	No
Intel® InTru™ 3D Technology	No
Intel® Wireless Display	No
Intel® Clear Video HD Technology	No

### Package Specifications

T <sub>JUNCTION</sub>	100°C
Package Size	31mm x24mm (FCBGA1023)
Graphics and IMC Lithography	32nm
Sockets Supported	FCBGA1023
Low Halogen Options Available	See MDDDS

### Advanced Technologies

Intel® Turbo Boost Technology‡	No
Intel® vPro Technology‡	No
Intel® Hyper-Threading Technology‡	No
Intel® Virtualization Technology (VT-x)‡	Yes
Intel® Virtualization Technology for Directed I/O (VT-d)‡	No
Intel® 64‡	Yes
Intel® My WiFi Technology	No
4G WiMAX Wireless Technology	No
Idle States	Yes
Enhanced Intel SpeedStep® Technology	Yes
Intel® Demand Based Switching	No
Thermal Monitoring Technologies	Yes
Intel® Fast Memory Access	Yes
Intel® Flex Memory Access	Yes

### Intel® Data Protection Technology

AES New Instructions	No
----------------------	----

### Intel® Platform Protection Technology

## RELATED PRODUCTS

- [Intel® Celeron® Processor](#)
- [Intel® Celeron® Processor 800 Series for Mobile](#)
- [Products formerly Sandy Bridge](#)



- [Visit the Embedded Design Center >](#)

## QUICK LINKS

- [Download Datasheet](#)
- [Search Distributors](#)
- [Software Downloads](#)
- [Support Overview](#)
- [Search all of intel.com](#)

## PCN/MDDDS Information

**SR0NB**  
919712: [PCN](#) | [MDDDS](#)

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

"Intel classifications" consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company may be the exporter of record, and as such, your company is responsible for determining the correct classification of any item at the time of export.

"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

Intel processor numbers are not a measure of performance. Processor numbers differentiate features within each processor family, not across different processor families. See <http://www.intel.com/content/www/us/en/processors/processor-numbers.htm> for details.

For benchmarking data see <http://www.intel.com/performance>.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

‡ This feature may not be available on all computing systems. Please check with the system vendor to determine if your system delivers this feature, or reference the system specifications (motherboard, processor, chipset, power supply, HDD, graphics controller, memory, BIOS, drivers, virtual machine monitor-VM, platform software, and/or operating system) for feature compatibility. Functionality, performance, and other benefits of this feature may vary depending on system configuration.

Low Halogen: Applies only to brominated and chlorinated flame retardants (BFRs/CFRs) and PVC in the final product. Intel components as well as purchased components on the finished assembly meet JS-709 requirements, and the PCB / substrate meet IEC 61249-2-21 requirements. The replacement of halogenated flame retardants and/or PVC may not be better for the environment.

Max Turbo Frequency refers to the maximum single-core processor frequency that can be achieved with Intel® Turbo Boost Technology. See [www.intel.com/technology/turbo/boost/](http://www.intel.com/technology/turbo/boost/) for more information.

See <http://www.intel.com/content/www/us/en/architecture-and-technology/hyper-threading/hyper-threading-technology.htm?wapkw=hyper+threading> for more information including details on which processors support Intel® HT Technology.

Processors that support 64-bit computing on Intel® architecture require an Intel 64 architecture-enabled BIOS.

Some products can support AES New Instructions with a Processor Configuration update, in particular, i7-2630QM/i7-2635QM, i7-2670QM/i7-2675QM, i5-2430M/i5-2435M, i5-2410M/i5-2415M. Please contact OEM for the BIOS that includes the latest Processor configuration update.

 Send us your feedback!

