



© 1965 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING. APPROVED PER GOVT CONTRACT NO.


REVISIONS

SYM	ZONE	DESCRIPTION	DATE	APPROVAL
A		REVISED Y-68	1-19-66	m.s. J.H.
B		REVISED Y-296	3-22-66	m.s. J.H.
C		REV PER ECN D-644	10-6-75	MPH
D		ADDED -3 PER ECN H-373	11-5-80	MPH
E		REV. / ECN R-2305	7-20-86	MPH
F		OBSOLETE -3 PER ECN R-2604	2-23-87	SDG
F1		ADDED -4 PER ECN DF-0026	OCT 10-2-87	JW
G		REV PER ELO-05-001A12	05/05	DR
H		REV PER ECO-05-005359	11/05	PY/DE



PANEL CUTOUT
SCALE: 1-1

- 1 ZINC PLATE PER ASTM-B-633 TYPE II .000200-.000400 THK CLASS 3 COLORLESS SUPPLEMENTARY CHROMATE.
- 2 ELECTROLESS NICKEL PLATE PER SAE-AMS-C-2607A .000400-.000800 THK (NO INTENTIONAL ADDITIONS OF LEAD OR CADMIUM PER DFE STANDARD 230-700).
- 3 ZINC PLATED COLD ROLLED STEEL.
- 4 PASSIVATED STAINLESS STEEL.
- 5 CADMIUM PLATE PER QQ-P-416 .000200-.000400 THK.



5-202795-2	FOR PINS	2/4
5-202795-1	FOR SOCKETS	2/4
202795-4	FOR SOCKETS	1/5
202795-3	FOR PINS	1/3
202795-2	FOR PINS	1/3
202795-1	FOR SOCKETS	1/3
PART NO.	ASSY TYPE	FINISH

202795-2, -3 & 5-2

202795-2 FOR PINS SUPERSEDED BY 5-202795-2

202795-1 FOR SOCKETS SUPERSEDED BY 5-202795-1

202795-3 FOR PINS OBSOLETE

AMP INFO		QTY REQD	NOMENCLATURE OR DESCRIPTION	PART OR IDENTIFYING NO		
LOC	PRINT/DIST					
DF	10/H					
LIST OF MATERIALS OR PARTS LIST						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		SIGNATURE		DATE	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
FRACTIONS	DECIMALS	ANGLES	DR			
± .11	± .005	± .11	E. Benninger	10-12-65		
MATERIAL		CHK			NAME	
SEE CALL OUT		S. S. Heide		11-9-65	PLUG ASSEMBLY, MODULE SERIES "G" (3 BLOCKS)	
HEAT TREAT		DSGN ENGR				
— 11 —		J. B. Williams		11-9-65		
FINISH		OTHER APPD				
SEE CALL OUT						
		CODE IDENT NO		SIZE	NUMBER	
		00779		D	202795	
		SCALE		WT	CALC	ACTUAL
		1-1				