

# HCPL0452, HCPL0453, HCPL0500, HCPL0501, HCPL0530, HCPL0531, HCPL0534 High Speed Transistor Optocouplers

Single Channel: HCPL0452 HCPL0453 HCPL0500 HCPL0501  
Dual Channel: HCPL0530 HCPL0531 HCPL0534

## Features

- High speed – 1 MBit/s
- 15kV/μs minimum common mode transient immunity at  $V_{CM} = 1500V$  (HCPL0453/0534)
- Open collector output
- Guaranteed performance over temperature: 0°C to 70°C
- U.L. recognized (File # E90700)
- VDE0884 recognized (file#136616)
  - approval pending for HCPL0530/0531/0453
  - ordering option V, e.g., HCPL0500V
- BSI recognized (file# 8661, 8662)
  - HCPL0452/0500/0501 only

## Applications

- Line receivers
- Pulse transformer replacement
- Output interface to CMOS-LSTTL-TTL
- Wide bandwidth analog coupling

## Description


The HCPL05XX, and HCPL04XX optocouplers consist of an AlGaAs LED optically coupled to a high speed photo-detector transistor housed in a compact 8-pin small out-line package.

A separate connection for the bias of the photodiode improves the speed by several orders of magnitude over conventional phototransistor optocouplers by reducing the base-collector capacitance of the input transistor. The HCPL04XX devices do not have the base bonded out to a lead for additional noise margin. The HCPL053X devices have two channels per package for optimum mounting density.


## Truth Table (positive Logic)

| LED | V <sub>O</sub> |
|-----|----------------|
| ON  | LOW            |
| OFF | HIGH           |

## Schematics



HCPL0500, HCPL0501  
\*BASE NOT CONNECTED  
FOR HCPL0452, HCPL0453



HCPL0530/HCPL0531/HCPL0534

# **Absolute Maximum Ratings** ( $T_A = 25^{\circ}\text{C}$ unless otherwise specified)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

| Symbol           | Parameter                                                           | Value       | Units              |
|------------------|---------------------------------------------------------------------|-------------|--------------------|
| $T_{\text{STG}}$ | Storage Temperature                                                 | -40 to +125 | $^{\circ}\text{C}$ |
| $T_{\text{OPR}}$ | Operating Temperature                                               | -40 to +85  | $^{\circ}\text{C}$ |
|                  | Reflow Temperature Profile (Refer to page 11)                       |             |                    |
| <b>EMITTER</b>   |                                                                     |             |                    |
| $I_F$ (avg)      | DC/Average Forward Input Current                                    | 25          | mA                 |
| $I_F$ (pk)       | Peak Forward Input Current (50% duty cycle, 1ms P.W.)               | 50          | mA                 |
| $I_F$ (trans)    | Peak Transient Input Current - ( $\leq 1\mu\text{s}$ P.W., 300 pps) | 1.0         | A                  |
| $V_R$            | Reverse Input Voltage                                               | 5           | V                  |
| $P_D$            | Input Power Dissipation                                             | 45          | mW                 |
| <b>DETECTOR</b>  |                                                                     |             |                    |
| $I_O$ (avg)      | Average Output Current (Pin 6)                                      | 8           | mA                 |
| $I_O$ (pk)       | Peak Output Current                                                 | 16          | mA                 |
| $V_{\text{EBR}}$ | Emitter-Base Reverse Voltage (HCPL0500/HCPL0501 only)               | 5           | V                  |
| $V_{\text{CC}}$  | Supply Voltage                                                      | -0.5 to 30  | V                  |
| $V_O$            | Output Voltage                                                      | -0.5 to 20  | V                  |
| $I_B$            | Base Current (HCPL0500/HCPL0501 only)                               | 5           | mA                 |
| $P_D$            | Output power dissipation                                            | 100         | mW                 |

## Electrical Characteristics ( $T_A = 0$ to $70^\circ\text{C}$ unless otherwise specified)

### Individual Component Characteristics

| Symbol                    | Parameter                                  | Test Conditions                                                                             | Device            | Min. | Typ.* | Max. | Unit                 |
|---------------------------|--------------------------------------------|---------------------------------------------------------------------------------------------|-------------------|------|-------|------|----------------------|
| <b>EMITTER</b>            |                                            |                                                                                             |                   |      |       |      |                      |
| $V_F$                     | Input Forward Voltage                      | $I_F = 16\text{mA}$ , $T_A = 25^\circ\text{C}$                                              | All               |      | 1.45  | 1.7  | V                    |
|                           |                                            | $I_F = 16\text{mA}$                                                                         |                   |      |       | 1.8  |                      |
| $BV_R$                    | Input Reverse Breakdown Voltage            | $I_R = 10\mu\text{A}$                                                                       | All               | 5.0  |       |      | V                    |
| $\Delta V_F / \Delta T_A$ | Temperature Coefficient of Forward Voltage | $I_F = 16\text{mA}$                                                                         | All               |      | -1.6  |      | mV/ $^\circ\text{C}$ |
| <b>DETECTOR</b>           |                                            |                                                                                             |                   |      |       |      |                      |
| $I_{OH}$                  | Logic High Output Current                  | $I_F = 0\text{mA}$ , $V_O = V_{CC} = 5.5\text{V}$ , $T_A = 25^\circ\text{C}$                | All               |      | 0.001 | 0.5  | $\mu\text{A}$        |
|                           |                                            | $I_F = 0\text{mA}$ , $V_O = V_{CC} = 15\text{V}$ , $T_A = 25^\circ\text{C}$                 | All               |      | 0.005 | 1    |                      |
|                           |                                            | $I_F = 0\text{mA}$ , $V_O = V_{CC} = 15\text{V}$                                            | All               |      |       | 50   |                      |
| $I_{CCL}$                 | Logic Low Supply Current                   | $I_F = 16\text{mA}$ , $V_O = \text{Open}$ , $V_{CC} = 15\text{V}$                           | HCPL0452/3/0500/1 |      | 120   | 200  | $\mu\text{A}$        |
|                           |                                            |                                                                                             | HCPL0530/1/4      |      |       | 400  |                      |
| $I_{CCH}$                 | Logic High Supply Current                  | $I_F = 0\text{mA}$ , $V_O = \text{Open}$ , $V_{CC} = 15\text{V}$ , $T_A = 25^\circ\text{C}$ | All               |      | 0.01  | 1    | $\mu\text{A}$        |
|                           |                                            | $I_F = 0\text{mA}$ , $V_O = \text{Open}$ , $V_{CC} = 15\text{V}$                            | HCPL0452/3/0500/1 |      |       | 2    |                      |
|                           |                                            |                                                                                             | HCPL0530/1/4      |      |       | 4    |                      |

### Transfer Characteristics

| Symbol         | Parameter                       | Test Conditions                                                                                | Device          | Min. | Typ.* | Max. | Unit |
|----------------|---------------------------------|------------------------------------------------------------------------------------------------|-----------------|------|-------|------|------|
| <b>COUPLED</b> |                                 |                                                                                                |                 |      |       |      |      |
| CTR            | Current Transfer Ratio (Note 1) | $I_F = 16\text{mA}$ , $V_O = 0.4\text{V}$ , $V_{CC} = 4.5\text{V}$ , $T_A = 25^\circ\text{C}$  | HCPL0500/0530   | 7    | 2.7   | 50   | %    |
|                |                                 |                                                                                                | HCPL0452/3      | 19   | 27    | 50   |      |
|                |                                 |                                                                                                | HCPL0501/0531   |      |       |      |      |
|                |                                 | $I_F = 16\text{mA}$ , $V_O = 0.5\text{V}$ , $V_{CC} = 4.5\text{V}$                             | HCPL0500        | 5    | 30    |      |      |
|                |                                 |                                                                                                | HCPL0452/3      | 15   | 30    |      |      |
|                |                                 |                                                                                                | HCPL0501/0534   |      |       |      |      |
| $V_{OL}$       | Logic Low Output Voltage        | $I_F = 16\text{mA}$ , $I_O = 1.1\text{mA}$ , $V_{CC} = 4.5\text{V}$ , $T_A = 25^\circ\text{C}$ | HCPL0500        |      | 0.18  | 0.4  | V    |
|                |                                 |                                                                                                | HCPL0530        |      |       | 0.5  |      |
|                |                                 | $I_F = 16\text{mA}$ , $I_O = 3\text{mA}$ , $V_{CC} = 4.5\text{V}$ , $T_A = 25^\circ\text{C}$   | HCPL0452/3      |      | 0.25  | 0.4  |      |
|                |                                 |                                                                                                | HCPL0501/0531/4 |      |       |      |      |
|                |                                 | $I_F = 16\text{mA}$ , $I_O = 0.8\text{mA}$ , $V_{CC} = 4.5\text{V}$                            | HCPL0500        |      | 0.13  | 0.5  |      |
|                |                                 |                                                                                                | HCPL0530        |      |       |      |      |
|                |                                 | $I_F = 16\text{mA}$ , $I_O = 2.4\text{mA}$ , $V_{CC} = 4.5\text{V}$                            | HCPL0452/3      |      | 0.23  | 0.5  |      |
|                |                                 |                                                                                                | HCPL0501/0531/4 |      |       |      |      |

\*All typicals at  $T_A = 25^\circ\text{C}$

# **Electrical Characteristics** (Continued) ( $T_A = 0$ to $70^\circ\text{C}$ unless otherwise specified)

## **Switching Characteristics** $V_{CC} = 5\text{V}$

| Symbol     | Parameter                                    | Test Conditions                                                                                                       | Device          | Min.   | Typ.*  | Max. | Unit                   |
|------------|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|-----------------|--------|--------|------|------------------------|
| $T_{PHL}$  | Propagation Delay Time to Logic LOW          | $T_A = 25^\circ\text{C}$ , $R_L = 4.1\text{k}\Omega$ , $I_F = 16\text{mA}$ (Note 2) (Fig. 9)                          | HCPL0500/0530   |        | 0.45   | 1.5  | $\mu\text{s}$          |
|            |                                              | $R_L = 1.9\text{k}\Omega$ , $I_F = 16\text{mA}$ , $T_A = 25^\circ\text{C}$ (Note 3) (Fig. 9)                          | HCPL0452/3      |        | 0.45   | 0.8  |                        |
|            |                                              |                                                                                                                       | HCPL0501/0531/4 |        |        |      |                        |
|            |                                              | $R_L = 4.1\text{k}\Omega$ , $I_F = 16\text{mA}$ (Note 2) (Fig. 9)                                                     | HCPL0500/0530   |        |        | 2.0  |                        |
| $T_{PLH}$  | Propagation Delay Time to Logic HIGH         | $T_A = 25^\circ\text{C}$ , $R_L = 4.1\text{k}\Omega$ , $I_F = 16\text{mA}$ (Note 2) (Fig. 9)                          | HCPL0500/0530   |        | 0.5    | 1.5  | $\mu\text{s}$          |
|            |                                              | $R_L = 1.9\text{k}\Omega$ , $I_F = 16\text{mA}$ , $T_A = 25^\circ\text{C}$ (Note 3) (Fig. 9)                          | HCPL0452/3      |        | 0.3    | 0.8  |                        |
|            |                                              |                                                                                                                       | HCPL0501/0531/4 |        |        |      |                        |
|            |                                              | $R_L = 4.1\text{k}\Omega$ , $I_F = 16\text{mA}$ (Note 2) (Fig. 9)                                                     | HCPL0500/0530   |        |        | 2.0  |                        |
| $ICM_{HI}$ | Common Mode Transient Immunity at Logic HIGH | $I_F = 0\text{mA}$ , $V_{CM} = 10V_{P-P}$ , $R_L = 4.1\text{k}\Omega$ , $T_A = 25^\circ\text{C}$ (Note 4) (Fig. 10)   | HCPL0500        | 1,000  | 10,000 |      | $\text{V}/\mu\text{s}$ |
|            |                                              |                                                                                                                       | HCPL0530        |        |        |      |                        |
|            |                                              | $I_F = 0\text{mA}$ , $V_{CM} = 10V_{P-P}$ , $R_L = 1.9\text{k}\Omega$ , $T_A = 25^\circ\text{C}$ , (Note 4) (Fig. 10) | HCPL0452        | 1,000  | 10,000 |      |                        |
|            |                                              |                                                                                                                       | HCPL0501/31     |        |        |      |                        |
| $ICM_{LI}$ | Common Mode Transient Immunity at Logic LOW  | $I_F = 16\text{mA}$ , $V_{CM} = 10V_{P-P}$ , $R_L = 4.1\text{k}\Omega$ , $T_A = 25^\circ\text{C}$ (Note 4) (Fig. 10)  | HCPL0500        | 1,000  | 10,000 |      | $\text{V}/\mu\text{s}$ |
|            |                                              |                                                                                                                       | HCPL0530        |        |        |      |                        |
|            |                                              | $I_F = 16\text{mA}$ , $V_{CM} = 10V_{P-P}$ , $R_L = 1.9\text{k}\Omega$ (Note 4) (Fig. 10)                             | HCPL0452        | 1,000  | 10,000 |      |                        |
|            |                                              |                                                                                                                       | HCPL0501/31     |        |        |      |                        |
| $ICM_{LI}$ | Common Mode Transient Immunity at Logic LOW  | $I_F = 16\text{mA}$ , $V_{CM} = 10V_{P-P}$ , $R_L = 1.9\text{k}\Omega$ (Note 4) (Fig. 10)                             | HCPL0534        | 15,000 | 40,000 |      | $\text{V}/\mu\text{s}$ |
|            |                                              |                                                                                                                       | HCPL0453        | 15,000 | 40,000 |      |                        |
|            |                                              | $I_F = 16\text{mA}$ , $T_A = 25^\circ\text{C}$ , $V_{CM} = 1500V_{P-P}$ , $C_L = 15\text{pF}$ (Note 4) (Fig. 10)      | HCPL0453        | 15,000 | 40,000 |      |                        |
|            |                                              |                                                                                                                       | HCPL0453        | 15,000 | 40,000 |      |                        |

## **Isolation Characteristics**

| Symbol    | Characteristics                | Test Conditions                                                                      | Min.      | Typ.* | Max . | Unit        |
|-----------|--------------------------------|--------------------------------------------------------------------------------------|-----------|-------|-------|-------------|
| $V_{ISO}$ | Input-Output Isolation Voltage | $f = 60\text{ Hz}$ , $t = 1.0\text{ min.}$ , $I_{I-O} \leq 2\mu\text{A}$ (Note 5, 6) | 2500      |       |       | $V_{acRMS}$ |
| $R_{ISO}$ | Isolation Resistance           | $V_{I-O} = 500\text{V}$ (Note 5)                                                     | $10^{11}$ |       |       |             |
| $C_{ISO}$ | Isolation Capacitance          | $V_{I-O} = 0$ , $f = 1.0\text{MHz}$ (Note 5)                                         |           | 0.2   |       | $\text{pF}$ |

\*All typicals at  $T_A = 25^\circ\text{C}$

**Notes**

1. Current Transfer Ratio is designed as a ratio of output collector current,  $I_O$ , to the forward LED input current,  $I_F$  times 100%.
2. The 4.1 k $\Omega$  load represents 1 LSTTL unit load of 0.36 mA and 6.1k $\Omega$  pull-up resistor.
3. The 1.9 k $\Omega$  load represents 1 TTL unit load of 1.6 mA and 5.6 k $\Omega$  pull-up resistor.
4. Common mode transient immunity in logic high level is the maximum tolerable (positive)  $dV_{cm}/dt$  on the leading edge of the common mode pulse signal  $V_{CM}$ , to assure that the output will remain in a logic high state (i.e.,  $V_O > 2.0$  V). Common mode transient immunity in logic low level is the maximum tolerable (negative)  $dV_{cm}/dt$  on the trailing edge of the common mode pulse signal,  $V_{CM}$ , to assure that the output will remain in a logic low state (i.e.,  $V_O < 0.8$  V).
5. Device is considered a two terminal device: Pins 1, 2, 3 and 4 are shorted together and Pins 5, 6, 7 and 8 are shorted together.
6. 2500 VAC RMS for 1 minute duration is equivalent to 3000 VAC RMS for 1 second duration.

## Typical Performance Curves

Fig. 1 Normalized CTR vs. Forward Current




Fig. 2 Normalized CTR vs. Temperature




Fig. 3 Output Current vs. Output Voltage




Fig. 4 Logic High Output Current vs. Temperature




Fig. 5 Propagation Delay vs. Temperature







Fig. 6 Propagation Delay vs. Load Resistance





Test Circuit for HCPL0452, HCPL0453, HCPL0500 and HCPL0501



Test Circuit for HCPL0530, HCPL0531 and HCPL0534






Fig. 7 Switching Time Test Circuit



Test Circuit for HCPL0452, HCPL0453, HCPL0500 and HCPL0501



Test Circuit for HCPL0530, HCPL0531 and HCPL0534






Fig. 8 Common Mode Immunity Test Circuit

## Package Dimensions

### 8-pin SOIC Surface Mount



### Recommended Pad Layout



Dimensions in inches (mm).

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.


Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>

## Ordering Information


| Option | Order Entry Identifier | Description                                                                                           |
|--------|------------------------|-------------------------------------------------------------------------------------------------------|
| V      | V                      | VDE 0884 (approval pending for HCPL0530, HCPL0531 & HCPL0534)                                         |
| R2     | R2                     | Tape and reel (2500 units per reel)                                                                   |
| R2V    | R2V                    | VDE 0884 (approval pending for HCPL0530, HCPL0531 & HCPL0534),<br>Tape and reel (2500 units per reel) |

## Marking Information




| Definitions |                                                                                        |
|-------------|----------------------------------------------------------------------------------------|
| 1           | Fairchild logo                                                                         |
| 2           | Device number                                                                          |
| 3           | VDE mark (Note: Only appears on parts ordered with VDE option – See order entry table) |
| 4           | One digit year code, e.g., '3'                                                         |
| 5           | Two digit work week ranging from '01' to '53'                                          |
| 6           | Assembly package code                                                                  |

## Carrier Tape Specifications



## Reflow Profile



| Profile Feature                                                       | Pb-Free Assembly Profile |
|-----------------------------------------------------------------------|--------------------------|
| Temperature Min. (T <sub>smin</sub> )                                 | 150°C                    |
| Temperature Max. (T <sub>smax</sub> )                                 | 200°C                    |
| Time (t <sub>s</sub> ) from (T <sub>smin</sub> to T <sub>smax</sub> ) | 60–120 seconds           |
| Ramp-up Rate (t <sub>L</sub> to t <sub>p</sub> )                      | 3°C/second max.          |
| Liquidous Temperature (T <sub>L</sub> )                               | 217°C                    |
| Time (t <sub>L</sub> ) Maintained Above (T <sub>L</sub> )             | 60–150 seconds           |
| Peak Body Package Temperature                                         | 260°C +0°C / –5°C        |
| Time (t <sub>p</sub> ) within 5°C of 260°C                            | 30 seconds               |
| Ramp-down Rate (T <sub>p</sub> to T <sub>L</sub> )                    | 6°C/second max.          |
| Time 25°C to Peak Temperature                                         | 8 minutes max.           |



## TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

|                                                                                      |                                                                                     |                                                                                                    |                                                                                             |
|--------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|
| Auto-SPM™                                                                            | F-PFS™                                                                              | PowerTrench®                                                                                       | The Power Franchise®                                                                        |
| Build it Now™                                                                        | FRFET®                                                                              | PowerXS™                                                                                           | the power franchise                                                                         |
| CorePLUS™                                                                            | Global Power Resource™                                                              | Programmable Active Droop™                                                                         | TinyBoost™                                                                                  |
| CorePOWER™                                                                           | Green FPS™                                                                          | QFET®                                                                                              | TinyBuck™                                                                                   |
| CROSSVOLT™                                                                           | Green FPS™ e-Series™                                                                | QS™                                                                                                | TinyLogic®                                                                                  |
| CTL™                                                                                 | Gmax™                                                                               | Quiet Series™                                                                                      | TINYOPTO™                                                                                   |
| Current Transfer Logic™                                                              | GTO™                                                                                | RapidConfigure™                                                                                    | TinyPower™                                                                                  |
| EcoSPARK®                                                                            | IntelliMAX™                                                                         |  TM               | TinyPWM™                                                                                    |
| EfficientMax™                                                                        | ISOPLANAR™                                                                          | Saving our world, 1mW/W/kW at a time™                                                              | TinyWire™                                                                                   |
| EZSWITCH™*                                                                           | MegaBuck™                                                                           | SmartMax™                                                                                          | TriFault Detect™                                                                            |
|  ™* | MICROCOUPLER™                                                                       | SMART START™                                                                                       | TRUECURRENT™*                                                                               |
|  ®  | MicroFET™                                                                           | SPM®                                                                                               | µSerDes™                                                                                    |
| Fairchild®                                                                           | MicroPak™                                                                           | STEALTH™                                                                                           |  SerDes® |
| Fairchild Semiconductor®                                                             | MillerDrive™                                                                        | SuperFET™                                                                                          | UHC®                                                                                        |
| FACT Quiet Series™                                                                   | MotionMax™                                                                          | SuperSOT™-3                                                                                        | Ultra FRFET™                                                                                |
| FACT®                                                                                | Motion-SPM™                                                                         | SuperSOT™-6                                                                                        | UniFET™                                                                                     |
| FAST®                                                                                | OPTOLOGIC®                                                                          | SuperSOT™-8                                                                                        | VCX™                                                                                        |
| FAST®                                                                                | OPTOPLANAR®                                                                         | SupreMOS™                                                                                          | VisualMax™                                                                                  |
| FastvCore™                                                                           |  ® | SyncFET™                                                                                           | XS™                                                                                         |
| FETBench™                                                                            | PDP SPM™                                                                            | Sync-Lock™                                                                                         |                                                                                             |
| FlashWriter®*                                                                        | Power-SPM™                                                                          |  SYSTEM GENERAL®* |                                                                                             |
| FPS™                                                                                 |                                                                                     |                                                                                                    |                                                                                             |

\* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status        | Definition                                                                                                                                                                                          |
|--------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.                                               |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.                                                    |

Rev. 140