

Wet Tantalum Capacitors Surface Mount, Molded Case



PERFORMANCE CHARACTERISTICS

Operating Temperature: - 55 °C to + 85 °C
(to + 125 °C with voltage derating)

Capacitance Tolerance: At 120 Hz, + 25 °C, ± 20 %
standard, ± 10 %

DC Leakage Current (DCL Max.): At + 25 °C and above:
Leakage current shall not exceed the values listed in the
Standard Ratings table.

Life Test: Capacitors are capable of withstanding a 2000 h
life test at a temperature of + 85 °C or + 125 °C at the
applicable rated DC working voltage.

Following life test:

1. DCL, measured at + 85 °C rated voltage, shall not be in
excess of the original requirement.
2. The equivalent series resistance shall not exceed 150 %
of the initial requirement.
3. Change in capacitance shall not exceed 10 % from the
initial measurement.

FEATURES

- Terminations: standard tin/lead (SnPb),
100 % tin (RoHS compliant) terminations
available
- Very high capacitance, 10 µF to 470 µF
6 V to 125 V, - 55 °C to + 125 °C
- Very low ESR
- High ripple current capability
- Low DCL
- Model M34 wet tantalum electrolytic chip capacitors
incorporate the advantages of all the varieties of
electrolytic capacitors and eliminate most of the
disadvantages. These units have a transient reverse
voltage capability and a higher ripple current capability
than any other electrolytic type with similar combinations
of capacitance and case size.
- Compliant to RoHS Directive 2002/95/EC

Note

* Pb containing terminations are not RoHS compliant, exemptions
may apply



RoHS*
COMPLIANT

APPLICATION NOTES


- a) No continuous reverse voltage permissible.
- b) Transient reverse voltage surges are acceptable under
the following conditions:
The peak reverse voltage does not exceed 1.5 V and the
peak current times the duration of the reverse transient
does not exceed 0.05 A. In addition, the repetition
frequency of the reverse voltage surge is less than 10 Hz.
- c) The peak of the applied AC ripple and the applied DC
voltage must not exceed the DC voltage rating of
the capacitor.

ORDERING INFORMATION


M34	C	826	M	125	B	Z	S	S
MODEL	CASE CODE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT + 85 °C	TERMINATION AND PACKAGING	RELIABILITY LEVEL	TEMP	ESR
	See Ratings and Case Codes table	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	K = ± 10 % M = ± 20 %	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating.	A = 100 % tin (RoHS compliant), bulk B = Std, tin/lead, bulk	Z = Non-ER	S = Std	S = Std

Note

- Packaging: The use of formed plastic tubes for packing bulk components is standard

DIMENSIONS in inches [millimeters]


CASE CODE	L (MAX.)	W	H	P (MIN.)	T _W	T _H (MIN.)
C	0.835 [21.2]	0.315 ± 0.012 [8 ± 0.3]	0.295 ± 0.012 [7.5 ± 0.3]	0.118 [3.0]	0.236 ± 0.012 [6.0 ± 0.3]	0.075 [1.9]

RECOMMENDED REFLOW PROFILES


T _p Lead (Pb)-free	T _p Sn/Pb	t _p	T _L Lead (Pb)-free	T _L Sn/Pb	T _s MIN. Lead (Pb)-free	T _s MIN. Sn/Pb	T _s MAX. Lead (Pb)-free	T _s MAX. Sn/Pb	t _s Lead (Pb)-free	t _s Sn/Pb	t _L
245 °C	220 °C	10	217 °C	183 °C	150 °C	100 °C	200 °C	150 °C	60 to 150	60 to 90	60

MOUNTING

Due to the size and weight of these capacitors, we recommend that a supplemental mounting restraint to be used in printed circuit board attachment in addition to the reflowed solder.

One recommendation is to use an adhesive such as defined in the J-STD-001DS.

This is the Space Application Electronic Hardware Addendum to J-STD-001 (Requirements for Solder Electrical and Electronic Assemblies).

**STANDARD RATINGS**

CAPACITANCE (μF)	CASE CODE	PART NUMBER	MAX. ESR AT + 25 °C 120 Hz (Ω)	MAX. IMP. AT - 55 °C 120 Hz (Ω)	MAX. DCL (μA) AT		MAX. CAPACITANCE CHANGE (%) AT			MAX. RIPPLE 40 kHz RMS (mA)
					+ 25 °C	+ 85 °C + 125 °C	- 55 °C	+ 85 °C	+ 125 °C	
6 V _{DC} AT + 85 °C; 4 V _{DC} AT + 125 °C										
470	C	M34C477(1)006(2)ZSS	0.9	12	1.0	3.0	- 75	+ 10	+ 20	1500
10 V _{DC} AT + 85 °C; 7 V _{DC} AT + 125 °C										
330	C	M34C337(1)010(2)ZSS	1.0	15	1.0	3.0	- 70	+ 8	+ 20	1400
15 V _{DC} AT + 85 °C; 10 V _{DC} AT + 125 °C										
150	C	M34C157(1)015(2)ZSS	1.1	25	1.0	3.0	- 45	+ 8	+ 20	1400
25 V _{DC} AT + 85 °C; 15 V _{DC} AT + 125 °C										
120	C	M34C127(1)025(2)ZSS	1.3	25	1.0	5.0	- 42	+ 8	+ 12	1250
30 V _{DC} AT + 85 °C; 20 V _{DC} AT + 125 °C										
100	C	M34C107(1)030(2)ZSS	1.3	25	1.0	5.0	- 38	+ 8	+ 12	1200
50 V _{DC} AT + 85 °C; 30 V _{DC} AT + 125 °C										
68	C	M34C686(1)050(2)ZSS	1.5	35	1.0	5.0	- 25	+ 8	+ 15	1050
60 V _{DC} AT + 85 °C; 40 V _{DC} AT + 125 °C										
47	C	M34C476(1)060(2)ZSS	2.0	44	1.0	5.0	- 25	+ 8	+ 12	1050
75 V _{DC} AT + 85 °C; 50 V _{DC} AT + 125 °C										
33	C	M34C336(1)075(2)ZSS	2.5	66	1.0	5.0	- 25	+ 5	+ 9	1050
100 V _{DC} AT + 85 °C; 65 V _{DC} AT + 125 °C										
15	C	M34C156(1)100(2)ZSS	3.5	125	1.0	5.0	- 18	+ 3	+ 10	1050
125 V _{DC} AT + 85 °C; 85 V _{DC} AT + 125 °C										
10	C	M34C106(1)125(2)ZSS	5.5	175	1.0	5.0	- 15	+ 3	+ 10	1050

Note

- Part number definitions:
 - (1) Capacitance tolerance: K, M
 - (2) Termination/packaging: A = 100 % tin (RoHS compliant), bulk; B = Std, tin/lead, bulk
 - Reliability level: Z = Non-ER
 - Temperature: S = STD
 - ESR: S = STD

PERFORMANCE CHARACTERISTICS OF M34 CAPACITORS


ELECTRICAL CHARACTERISTICS	
ITEM	PERFORMANCE CHARACTERISTICS
Operating temperature range	- 55 °C to + 125 °C
Capacitor tolerance	± 20 %, ± 10 %, at 120 Hz
Capacitance change (maximum)	Limits per standard ratings table
ESR	Limits per standard ratings table
AC ripple current	Limits per standard ratings table
DCL (maximum leakage current)	Limits per standard ratings table
Impedance (maximum)	Limits per standard ratings table
Reverse voltage	Reverse voltage shall be in accordance with DSCC drawing 93026. There shall be no continuous reverse voltage. Transient reverse voltage surges are acceptable under the following conditions: a) Peak reverse voltage is equal to or less than 1.5 V and the product of the peak current times the duration of the reverse transient is 0.05 A or less. b) The repetition rate of the reverse voltage surges is less than 10 Hz.
Surge voltage	Surge voltage shall be in accordance with MIL-PRF-39006 and Table II of DSCC93026. The DC rated surge voltage is the maximum voltage to which the capacitors should be subjected under any conditions. This includes transients and ripple at the highest line voltage. The surge voltage is 115 % of rated DC working voltage.
Life test	The capacitors shall be capable of withstanding a 2000 h life test at 85 °C at rated voltage

**ENVIRONMENTAL CHARACTERISTICS**

ITEM	CONDITION	COMMENTS
Hermeticity	MIL-PRF-39006	There shall be no evidence of leakage after testing to MIL-PRF-39006 specifications.
Moisture resistance	MIL-PRF-39006	Tested in accordance to MIL-PRF-39006 for 30 cycles.
Altitude	MIL-STD-202G, method 105 D	100 000 feet test

MECHANICAL CHARACTERISTICS

ITEM	CONDITION	COMMENTS
Thermal shock	MIL-STD-202G, method 107 A	Per M39006 and DSCC93026, 30 cycles
Shock	MIL-STD-202G, method 213 I	Per M39006 and DSCC93026, 100 g
Vibration (high frequency)	MIL-STD-202G, method 204 D	Per M39006 and DSCC93026, 20 g
Resistance to solder heat	MIL-STD-202G, method 210 F	Terminals at 260 °C for 10 s. The capacitor must not be visibly damaged and the electrical characteristics must not be affected.
Solderability	ANSI J-STD-002	The terminations must be solderable per the MIL standard.
Terminals	MIL-STD-1276	All terminals shall be permanently secured internally and externally, as applicable. All external joints shall be welded.
Part markings	MIL-STD-1285	The part marking shall include Vishay name, trademark, capacitance, voltage, date code and lot symbol.
Weight (typical) in g	3.5	

PAD DIMENSIONS in millimeters

CASE CODE	A (MIN.)	B (NOM.)	C (NOM.)	D (NOM.)
C	22.7	14.7	4.0	6.4

STANDARD PACKAGING QUANTITY

SERIES	CASE CODE	BULK/TUBE
M34	C	10 pcs



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.