

## REVISIONS

| P | LTR | DESCRIPTION      | DATE      | DWN | APVD |
|---|-----|------------------|-----------|-----|------|
|   | W   | PRODUCTION ISSUE | 18JAN2019 | PNT | MT   |





TABLE OF DIMENSIONS


| PART NUMBER | H              |                | P               | W               |
|-------------|----------------|----------------|-----------------|-----------------|
|             | Min<br>a       | Max<br>b       | Min<br>b        | $\pm 20\%$<br>b |
| 101A011     | 5.1<br>[.20]   | 2.0<br>[.08]   | 22.9<br>[.90]   | 1.02<br>[.04]   |
| 101A021     | 7.4<br>[.29]   | 3.3<br>[.13]   | 25.4<br>[1.00]  | 1.27<br>[.05]   |
| 101A031     | 10.2<br>[.40]  | 4.6<br>[.18]   | 30.5<br>[1.20]  | 1.52<br>[.06]   |
| 101A041     | 15.2<br>[.60]  | 6.4<br>[.25]   | 40.6<br>[1.60]  | 1.78<br>[.07]   |
| 101A052     | 20.6<br>[.81]  | 9.4<br>[.37]   | 61.0<br>[2.40]  | 2.03<br>[.08]   |
| 101A062     | 25.4<br>[1.00] | 11.4<br>[.45]  | 68.6<br>[2.70]  | 2.29<br>[.09]   |
| 101A073     | 39.4<br>[1.55] | 18.0<br>[.71]  | 91.4<br>[3.60]  | 2.54<br>[.10]   |
| 101A083     | 50.8<br>[2.00] | 22.9<br>[.90]  | 101.6<br>[4.00] | 2.79<br>[.11]   |
| 101A094     | 83.8<br>[3.30] | 38.1<br>[1.50] | 114.3<br>[4.50] | 3.05<br>[.12]   |

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

|                                                                                                                                       |                       |           |                                                                                                           |                                          |
|---------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------|-----------------------------------------------------------------------------------------------------------|------------------------------------------|
| DIMENSIONS:<br>mm [INCHES]                                                                                                            | DWN<br>PRAVEEN N T    | 18JAN2019 | MATERIAL<br>SEE SHEET 2                                                                                   | FINISH<br>-                              |
|                                                                                                                                       | CHK<br>N NAGAR        | 18JAN2019 |  TE Connectivity Ltd. |                                          |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                                                                | APVD<br>M TAYLOR      | 18JAN2019 |                                                                                                           |                                          |
|                                                                                                                                       | PRODUCT SPEC<br>-     |           | SIZE<br>A4                                                                                                |                                          |
|                                                                                                                                       | APPLICATION SPEC<br>- |           | CAGE CODE<br>00779                                                                                        | DRAWING NO<br>G-101A011-XX-0THRU094-XX-0 |
|                                                                                                                                       | WEIGHT<br>-           |           | RESTRICTED TO<br>-                                                                                        |                                          |
| 0 PLC $\pm -$<br>1 PLC $\pm 0.50$ [.10]<br>2 PLC $\pm 0.25$ [.01]<br>3 PLC $\pm 0.13$ [.005]<br>4 PLC $\pm -$<br>ANGLES $\pm 1^\circ$ | CUSTOMER DRAWING      |           | SCALE<br>DNS                                                                                              | SHEET<br>1 OF 2                          |
|                                                    |                       | REV<br>W  |                                                                                                           |                                          |

| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|           | —   | SEE SHEET 1 | —    | —   | —    |

## COMPATIBILITY CHART

| MATERIAL DASH NO. | MATERIAL DESCRIPTION                 | RT SPEC | COATING SLASH NO. | COATING S NO.     |
|-------------------|--------------------------------------|---------|-------------------|-------------------|
| -3                | Polyolefin, Semi-rigid               | RT-301  | /42;/86;/180      | S1017;S1048;S1030 |
| -4                | Polyolefin, Flexible                 | RT-1304 | /42;/86;/180      | S1017;S1048;S1030 |
| -12               | Fluoroelastomer, Flexible            | RT-1312 | N/A               | N/A               |
| -25               | Elastomer, Fluid Resistant           | RW-2070 | /42;/86;/225      | S1017;S1048;S1206 |
| -100              | Polyolefin, Semi-flexible<br>Zerohal | RW-2082 | /86;/180          | S1048;S1030       |


## ORDERING INFORMATION

Diagram illustrating the breakdown of a part number into its components:

- Base part number: 101A021
- Material dash number (See Compatability Chart): -XX
- Modification number: -XX
- Adhesive slash number (If necessary, see Compatability Chart): /XX
- Color designator: -0

## NOTES

1. Dimensions appearing in table are as follows:
  - a - As Supplied
  - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Recovered parts may have angularity of 30° - 45°.

|                                                                                                                                                           |  |                       |           |                                                                                                                      |                    |                                          |                    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------|-----------|----------------------------------------------------------------------------------------------------------------------|--------------------|------------------------------------------|--------------------|
| DIMENSIONS:<br>mm [INCHES]                                                                                                                                |  | DWN<br>PRAVEEN N T    | 18JAN2019 | MATERIAL<br>—                                                                                                        |                    | FINISH<br>—                              |                    |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><br>0 PLC ± —<br>1 PLC ± 0,50 [.10]<br>2 PLC ± 0,25 [.01]<br>3 PLC ± 0,13 [.005]<br>4 PLC ± —<br>ANGLES ± 1° |  | CHK<br>N NAGAR        | 18JAN2019 | <div></div> TE Connectivity Ltd. |                    |                                          |                    |
|                                                                                                                                                           |  | APVD<br>M TAYLOR      | 18JAN2019 |                                                                                                                      |                    |                                          |                    |
|                                                                                                                                                           |  | PRODUCT SPEC<br>—     |           | NAME<br><br>CAP, ROUND END<br>—                                                                                      |                    |                                          |                    |
|                                                                                                                                                           |  | APPLICATION SPEC<br>— |           |                                                                                                                      |                    |                                          |                    |
|                                                                        |  | WEIGHT                |           | SIZE<br>A4                                                                                                           | CAGE CODE<br>00779 | DRAWING NO<br>C-101A011-XX-0THRU094-XX-0 | RESTRICTED TO<br>— |
|                                                                                                                                                           |  | CUSTOMER DRAWING      |           |                                                                                                                      |                    | SCALE<br>DNS                             | SHEET<br>2 of 2    |