
**VOLTAGE DETECTOR
WITH OUTPUT DELAY
RN5VD SERIES**

APPLICATION MANUAL



ELECTRONIC DEVICES DIVISION

NOTICE

1. The products and the product specifications described in this application manual are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, please refer to Ricoh sales representatives for the latest information thereon.
2. This application manual may not be copied or otherwise reproduced in whole or in part without prior written consent of Ricoh.
3. Please be sure to take any necessary formalities under relevant laws or regulations before exporting or otherwise taking out of your country the products or the technical information described herein.
4. The technical information described in this application manual shows typical characteristics of and example application circuits for the products. The release of such information is not to be construed as a warranty of or a grant of license under Ricoh's or any third party's intellectual property rights or any other rights.
5. The products listed in this application manual are intended and designed for use as general electronic components in standard applications (office equipment, computer equipment, measuring instruments, consumer electronic products, amusement equipment etc.). Those customers intending to use a product in an application requiring extreme quality and reliability, for example, in a highly specific application where the failure or misoperation of the product could result in human injury or death (aircraft, spacevehicle, nuclear reactor control system, traffic control system, automotive and transportation equipment, combustion equipment, safety devices, life support system etc.) should first contact us.
6. We are making our continuous effort to improve the quality and reliability of our products, but semiconductor products are likely to fail with certain probability. In order prevent any injury to persons or damages to property resulting from such failure, customers should be careful enough to incorporate safety measures in their design, such as redundancy feature, fire-containment feature and fail-safe feature. We do not assume any liability or responsibility for any loss or damage arising from misuse or inappropriate use of the products.
7. Anti-radiation design is not implemented in the products described in this application manual.
8. Please contact Ricoh sales representatives should you have any questions or comments concerning the products or the technical information.

June 1995

RN5VD SERIES

APPLICATION MANUAL

CONTENTS

OUTLINE	1
FEATURES	1
APPLICATIONS	1
BLOCK DIAGRAMS	2
SELECTION GUIDE	3
PIN CONFIGURATION	4
PIN DESCRIPTION	4
ABSOLUTE MAXIMUM RATINGS	5
ELECTRICAL CHARACTERISTICS	6
ELECTRICAL CHARACTERISTICS BY DETECTOR THRESHOLD	12
OPERATION	16
TEST CIRCUITS	18
TYPICAL CHARACTERISTICS	19
1) Supply Current vs. Input Voltage	19
2) Detector Threshold vs. Temperature	19
3) Output Voltage vs. Input Voltage	20
4) Nch Driver Output Current vs. V_{DS}	21
5) Nch Driver Output Current vs. Input Voltage	22
6) Pch Driver Output Current vs. Input Voltage	22
7) C_D pin Threshold Voltage vs. Temperature	23
8) C_D pin Current vs. Input Voltage	24
9) C_D pin Sink Current vs. C_D pin Voltage	24
10) Output Delay Time vs. External Capacitance	25
11) Delay Resietance vs. Temperature	25
TYPICAL APPLICATIONS	26
• RN5VD×A CPU Reset Circuit (Nch Open Drain Output)	26
• RN5VD×C CPU Reset Circuit (CMOS Output)	26
• Memory Back-up Circuit	26
PACKAGE DIMENSIONS	28
TAPING SPECIFICATION	28

RN5VD SERIES

OUTLINE

The RN5VD Series are voltage detector ICs with output delay functions and high detector threshold accuracy and ultra-low supply current by CMOS process, which can be operated at an extremely low voltage and is used, for instance, for system reset.

Each of these ICs consists of a voltage reference unit, a comparator, resistors for voltage detection, an output driver, a hysteresis circuit and an output delay generator. The detector threshold is fixed with high accuracy in the IC and requires no adjustment.

The RN5VD Series are operable by a lower voltage than that for the R5VL Series, and can be driven by a single battery.

Two output types, Nch open drain type and CMOS type, are available. Since the package for these ICs are SOT-23-5(Mini-mold)package, high density mounting of the ICs on board is possible.

FEATURES


- Output DelayTYP. 100ms with external capacitor : 0.15 μ F
- Ultra-low supply currentTYP. 1.0 μ A (RN5VD15 $\times$ V_{DD}=3.5V)
- Broad Operating Voltage Range0.7V to 10.0V
- Detector ThresholdStepwise setting with a step of 0.1V in the range of 0.9V to 6.0V is possible. (refer to Selection Guide) .
- High accuracy detector threshold $\pm 2.5\%$
- Low Temperature-Drift Coefficient of Detector ThresholdTYP. ± 100 ppm/ $^{\circ}$ C
- Two Output TypesNch Open Drain and CMOS
- Small PackageSOT-23-5(Mini-mold)

APPLICATIONS


- CPU & Logic Circuit Reset
- Battery Checker
- Window Comparator
- Wave Shaping Circuit
- Battery Back-Up Circuit
- Power Failure Detector

BLOCK DIAGRAMS

• Nch Open Drain Output (RN5VD×A)



• CMOS Output (RN5VD×C)



SELECTION GUIDE


The detector threshold, the output type, the packing type, and the taping type of RN5VD Series can be designating at the user's request by specifying the part number as follows :

RN5VDxxx-xx ←Part Number
 ↑ ↑↑ ↑
 a b c d

Code	Contents
a	Setting Detector Threshold ($-V_{DET}$) : Stepwise setting with a step of 0.1V in the range of 0.9V to 6.0V is possible.
b	Designation of Output Type A: Nch Open Drain C: CMOS
c	Designation of Packing Type A: Taping C: Antistatic bag for samples
d	Designation of Taping Type: Ex. SOT-23-5: TR, TL (refer to Taping Specification) "TR" is prescribed as a standard.

For example, the Product with Detector Threshold 3.5V, Output Type Nch Open Drain and Taping Type TR, is designated by Part Number RN5VD35AA-TR.

PIN CONFIGURATION



PIN DESCRIPTION

Pin No.	Symbol	Description
1	OUT	Output Pin
2	V _{DD}	Input and power source for device itself
3	GND	Ground Pin
4	NC	No Connection
5	C _D	Pin for external capacitor (for setting output delay)

ABSOLUTE MAXIMUM RATINGS

Symbol	Item	Rating		Unit
V _{DD}	Supply Voltage	12		V
V _{OUT}	Output Voltage	CNOS	V _{SS} –0.3 to V _{DD} +0.3	V
		Nch	V _{SS} –0.3 to 12	
I _{OUT}	Output Current	70		mA
P _D	Power Dissipation	150		mW
T _{opt}	Operating Temperature Range	–30 to +80		°C
T _{stg}	Storage Temperature Range	–55 to +125		°C
T _{solder}	Lead Temperature (Soldering)	260°C, 10s		

ABSOLUTE MAXIMUM RATINGS

Absolute Maximum ratings are threshold limit values that must not be exceeded even for an instant under any conditions. Moreover, such values for any two items must not be reached simultaneously. Operation above these absolute maximum ratings may cause degradation or permanent damage to the device. These are stress ratings only and do not necessarily imply functional operation below these limits.

ELECTRICAL CHARACTERISTICS

• RN5VD09A/C

T_{opt}=25°C

Symbol	Item	Conditions	MIN.	TYP.	MAX.	Unit.
-V _{DET}	Detector Threshold		0.878	0.900	0.922	V
V _{HYS}	Detector Threshold Hysteresis		0.027	0.045	0.063	V
I _{SS}	Supply Current	V _{DD} =0.8V		1.5	3.7	μA
		V _{DD} =2.9V		0.9	2.7	
V _{DDH}	Maximum Operating Voltage				10	V
V _{DDL}	Minimum Operating Voltage (Note 1)	T _{opt} =25°C		0.55	0.70	V
		-30°C≤T _{opt} ≤80°C		0.65	0.80	
I _{OUT}	Output Current	Nch V _{DS} =0.05V, V _{DD} =0.7V	0.01	0.05		mA
		V _{DS} =0.5V, V _{DD} =0.85V	0.05	0.50		
		Pch V _{DS} =-2.1V, V _{DD} =4.5V	1.0	2.0		mA
V _{TCD}	CD pin Threshold Voltage	V _{DD} =0.99V	0.297	0.495	0.693	V
I _{CD}	CD pin Sink Current	V _{DS} =0.1V, V _{DD} =0.7V	2.0	30		μA
		V _{DS} =0.5V, V _{DD} =0.85V	10.0	100.0		
R _D	Delay Resistance		0.5	1.0	2.0	MΩ
$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$	Detector Threshold Temperature Coefficient	-30°C≤T _{opt} ≤80°C		±100		ppm/°C

(Note 1) Minimum Operating Voltage means the value of input voltage when output voltage maintains 0.1V or less, provided that in the case of Nch Open Drain Type Products, the pull-up resistance is set at 470kΩ, and the pull-up voltage is set at 5.0V.

• RN5VD18A/C

T_{opt}=25°C

Symbol	Item	Conditions		MIN.	TYP.	MAX.	Unit.
-V _{DET}	Detector Threshold			1.755	1.800	1.845	V
V _{HYS}	Detector Threshold Hysteresis			0.054	0.090	0.126	V
I _{SS}	Supply Current	V _{DD} =1.7V			2.5	5.0	μA
		V _{DD} =3.8V			1.0	3.0	
V _{DDH}	Maximum Operating Voltage					10	V
V _{DDL}	Minimum Operating Voltage (Note 1)	T _{opt} =25°C -30°C≤T _{opt} ≤80°C			0.55 0.65	0.70 0.80	V
I _{OUT}	Output Current	Nch	V _{DS} =0.05V, V _{DD} =0.7V	0.01	0.05		mA
			V _{DS} =0.5V, V _{DD} =1.5V	1.0	2.0		
		Pch	V _{DS} =-2.1V, V _{DD} =4.5V	1.0	2.0		mA
V _{TCD}	CD pin Threshold Voltage	V _{DD} =1.98V		0.693	0.990	1.287	V
I _{CD}	CD pin Sink Current	V _{DS} =0.1V, V _{DD} =0.7V		2.0	30		μA
		V _{DS} =0.5V, V _{DD} =1.5V		200.0	800.0		
R _D	Delay Resistance			0.5	1.0	2.0	MΩ
$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$	Detector Threshold Temperature Coefficient	-30°C≤T _{opt} ≤80°C			±100		ppm/°C

(Note 1) Minimum Operating Voltage means the value of input voltage when output voltage maintains 0.1V or less, provided that in the case of Nch Open Drain Type Products, the pull-up resistance is set at 470kΩ, and the pull-up voltage is set at 5.0V.

RN5VD

• RN5VD27A/C

T_{opt}=25°C

Symbol	Item	Conditions	MIN.	TYP.	MAX.	Unit.
-V _{DET}	Detector Threshold		2.633	2.700	2.767	V
V _{HYS}	Detector Threshold Hysteresis		0.081	0.135	0.189	V
I _{SS}	Supply Current	V _{DD} =2.6V		3.5	7.0	μA
		V _{DD} =4.7V		1.1	3.3	
V _{DDH}	Maximum Operating Voltage				10	V
V _{DDL}	Minimum Operating Voltage (Note 1)	T _{opt} =25°C -30°C≤T _{opt} ≤80°C		0.55 0.65	0.70 0.80	V
I _{OUT}	Output Current	Nch V _{DS} =0.05V, V _{DD} =0.7V	0.01	0.05		mA
		Nch V _{DS} =0.5V, V _{DD} =1.5V	1.0	2.0		
		Pch V _{DS} =-2.1V, V _{DD} =4.5V	1.0	2.0		mA
V _{TCD}	CD pin Threshold Voltage	V _{DD} =2.97V	1.188	1.485	1.782	V
I _{CD}	CD pin Sink Current	V _{DS} =0.1V, V _{DD} =0.7V	2.0	30		μA
		V _{DS} =0.5V, V _{DD} =1.5V	200.0	800.0		
R _D	Delay Resistance		0.5	1.0	2.0	MΩ
$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$	Detector Threshold Temperature Coefficient	-30°C≤T _{opt} ≤80°C		±100		ppm/°C

(Note 1) Minimum Operating Voltage means the value of input voltage when output voltage maintains 0.1V or less, provided that in the case of Nch Open Drain Type Products, the pull-up resistance is set at 470kΩ, and the pull-up voltage is set at 5.0V.

• RN5VD36A/C

T_{opt}=25°C

Symbol	Item	Conditions	MIN.	TYP.	MAX.	Unit.
-V _{DET}	Detector Threshold		3.510	3.600	3.690	V
V _{HYS}	Detector Threshold Hysteresis		0.108	0.180	0.252	V
I _{SS}	Supply Current	V _{DD} =3.47V		4.5	9.0	μA
		V _{DD} =5.6V		1.2	3.6	
V _{DDH}	Maximum Operating Voltage				10	V
V _{DDL}	Minimum Operating Voltage (Note 1)	T _{opt} =25°C -30°C≤T _{opt} ≤80°C		0.55 0.65	0.70 0.80	V
I _{OUT}	Output Current	Nch V _{DS} =0.05V, V _{DD} =0.7V	0.01	0.05		mA
		V _{DS} =0.5V, V _{DD} =1.5V	1.0	2.0		
		Pch V _{DS} =-2.1V, V _{DD} =4.5V	1.0	2.0		mA
V _{TCD}	CD pin Threshold Voltage	V _{DD} =3.96V	1.584	1.980	2.376	V
I _{CD}	CD pin Sink Current	V _{DS} =0.1V, V _{DD} =0.7V	2.0	30		μA
		V _{DS} =0.5V, V _{DD} =1.5V	200.0	800.0		
R _D	Delay Resistance		0.5	1.0	2.0	MΩ
$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$	Detector Threshold Temperature Coefficient	-30°C≤T _{opt} ≤80°C		±100		ppm/°C

(Note 1) Minimum Operating Voltage means the value of input voltage when output voltage maintains 0.1V or less, provided that in the case of Nch Open Drain Type Products, the pull-up resistance is set at 470kΩ, and the pull-up voltage is set at 5.0V.

RN5VD

• RN5VD45A/C

T_{opt}=25°C

Symbol	Item	Conditions	MIN.	TYP.	MAX.	Unit.
-V _{DET}	Detector Threshold		4.388	4.500	4.612	V
V _{HYS}	Detector Threshold Hysteresis		0.135	0.225	0.315	V
I _{SS}	Supply Current	V _{DD} =4.34V		5.5	11.0	μA
		V _{DD} =6.5V		1.3	3.9	
V _{DDH}	Maximum Operating Voltage				10	V
V _{DDL}	Minimum Operating Voltage (Note 1)	T _{opt} =25°C -30°C≤T _{opt} ≤80°C		0.55 0.65	0.70 0.80	V
I _{OUT}	Output Current	Nch V _{DS} =0.05V, V _{DD} =0.7V	0.01	0.05		mA
		V _{DS} =0.5V, V _{DD} =1.5V	1.0	2.0		
		Pch V _{DS} =-2.1V, V _{DD} =8.0V	1.5	3.0		mA
V _{TCD}	CD pin Threshold Voltage	V _{DD} =4.95V	1.980	2.475	2.970	V
I _{CD}	CD pin Sink Current	V _{DS} =0.1V, V _{DD} =0.7V	2.0	30		μA
		V _{DS} =0.5V, V _{DD} =1.5V	200.0	800.0		
R _D	Delay Resistance		0.5	1.0	2.0	MΩ
$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$	Detector Threshold Temperature Coefficient	-30°C≤T _{opt} ≤80°C		±100		ppm/°C

(Note 1) Minimum Operating Voltage means the value of input voltage when output voltage maintains 0.1V or less, provided that in the case of Nch Open Drain Type Products, the pull-up resistance is set at 470kΩ, and the pull-up voltage is set at 5.0V.

• RN5VD54A/C

T_{opt}=25°C

Symbol	Item	Conditions	MIN.	TYP.	MAX.	Unit.
-V _{DET}	Detector Threshold		5.265	5.400	5.535	V
V _{HYS}	Detector Threshold Hysteresis		0.162	0.270	0.378	V
I _{SS}	Supply Current	V _{DD} =5.2V		6.0	12.0	μA
		V _{DD} =7.4V		1.4	4.2	
V _{DDH}	Maximum Operating Voltage				10	V
V _{DDL}	Minimum Operating Voltage (Note 1)	T _{opt} =25°C -30°C≤T _{opt} ≤80°C		0.55 0.65	0.70 0.80	V
I _{OUT}	Output Current	Nch V _{DS} =0.05V, V _{DD} =0.7V	0.01	0.05		mA
		V _{DS} =0.5V, V _{DD} =1.5V	1.0	2.0		
		Pch V _{DS} =-2.1V, V _{DD} =8.0V	1.5	3.0		mA
V _{TCd}	CD pin Threshold Voltage	V _{DD} =5.94V	2.376	2.970	3.564	V
I _{CD}	CD pin Sink Current	V _{DS} =0.1V, V _{DD} =0.7V	2.0	30		μA
		V _{DS} =0.5V, V _{DD} =1.5V	200.0	800.0		
R _D	Delay Resistance		0.5	1.0	2.0	MΩ
$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$	Detector Threshold Temperature Coefficient	-30°C≤T _{opt} ≤80°C		±100		ppm/°C

(Note 1) Minimum Operating Voltage means the value of input voltage when output voltage maintains 0.1V or less, provided that in the case of Nch Open Drain Type Products, the pull-up resistance is set at 470kΩ, and the pull-up voltage is set at 5.0V.

ELECTRICAL CHARACTERISTICS BY DETECTOR THRESHOLD

• RN5VD09A/C to RN5VD39A/C

Part Number.	Detector Threshold			Hysteresis			Supply Current 1			Supply Current 2			Output Current 1			Output Current 2							
	-V _{DET} (V)			V _{HYS} (V)			I _{SS1} (μA)			I _{SS2} (μA)			I _{OUT1} (mA)			I _{OUT2} (mA)							
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	conditions	TYP.	MAX.	conditions	TYP.	MAX.	conditions	MIN.	TYP.	conditions	MIN.	TYP.					
RN5VD09A/C	0.878	0.900	0.922	0.027	0.045	0.063	V _{DD} = (-V _{DET}) -0.10V	1.5	3.7	V _{DD} = (-V _{DET}) +2.0V	0.9	2.7	N _{ch} V _{DS} = 0.05V V _{DD} = 0.7V	0.01	0.05	N _{ch} V _{DS} = 0.5V	V _{DD} = 0.85V	0.05	0.5				
RN5VD10A/C	0.975	1.000	1.025	0.030	0.050	0.070		V _{DD} = (-V _{DET}) -0.13V	1.8		4.5	1.0					3.0	V _{DD} = 1.0V	0.2	1.0			
RN5VD11A/C	1.073	1.100	1.127	0.033	0.055	0.077			2.0		5.0	V _{DD} = (-V _{DET}) -0.13V					1.1	3.3	V _{DD} = 1.5V	1.0	2.0		
RN5VD12A/C	1.170	1.200	1.230	0.036	0.060	0.084			2.5		5.0						1.2	3.6					
RN5VD13A/C	1.268	1.300	1.332	0.039	0.065	0.091			3.0		6.0						1.2	3.6					
RN5VD14A/C	1.365	1.400	1.435	0.042	0.070	0.098			3.5		7.0						1.2	3.6					
RN5VD15A/C	1.463	1.500	1.537	0.045	0.075	0.105			4.0		8.0						1.2	3.6					
RN5VD16A/C	1.560	1.600	1.640	0.048	0.080	0.112			4.5		9.0						1.2	3.6					
RN5VD17A/C	1.658	1.700	1.742	0.051	0.085	0.119			4.5		9.0						1.2	3.6					
RN5VD18A/C	1.755	1.800	1.845	0.054	0.090	0.126			4.5		9.0						1.2	3.6					
RN5VD19A/C	1.853	1.900	1.947	0.057	0.095	0.133			4.5		9.0						1.2	3.6					
RN5VD20A/C	1.950	2.000	2.050	0.060	0.100	0.140			4.5		9.0						1.2	3.6					
RN5VD21A/C	2.048	2.100	2.152	0.063	0.105	0.147			4.5		9.0						1.2	3.6					
RN5VD22A/C	2.145	2.200	2.255	0.066	0.110	0.154			4.5		9.0						1.2	3.6					
RN5VD23A/C	2.243	2.300	2.357	0.069	0.115	0.161			4.5		9.0						1.2	3.6					
RN5VD24A/C	2.340	2.400	2.460	0.072	0.120	0.168			4.5		9.0						1.2	3.6					
RN5VD25A/C	2.438	2.500	2.562	0.075	0.125	0.175			4.5		9.0						1.2	3.6					
RN5VD26A/C	2.535	2.600	2.665	0.078	0.130	0.182			4.5		9.0						1.2	3.6					
RN5VD27A/C	2.633	2.700	2.767	0.081	0.135	0.189			4.5		9.0						1.2	3.6					
RN5VD28A/C	2.730	2.800	2.870	0.084	0.140	0.196			4.5		9.0						1.2	3.6					
RN5VD29A/C	2.828	2.900	2.972	0.087	0.145	0.203			4.5		9.0						1.2	3.6					
RN5VD30A/C	2.925	3.000	3.075	0.090	0.150	0.210	V _{DD} = (-V _{DET}) -0.13V		4.0	8.0	V _{DD} = (-V _{DET}) +2.0V		1.2	3.6	N _{ch} V _{DS} = 0.05V V _{DD} = 0.7V	0.01	0.05	N _{ch} V _{DS} = 0.5V				V _{DD} = 1.5V	1.0
RN5VD31A/C	3.023	3.100	3.177	0.093	0.155	0.217		4.0	8.0	1.2			3.6										
RN5VD32A/C	3.120	3.200	3.280	0.096	0.160	0.224		4.0	8.0	1.2		3.6											
RN5VD33A/C	3.218	3.300	3.382	0.099	0.165	0.231		4.0	8.0	1.2		3.6											
RN5VD34A/C	3.315	3.400	3.485	0.102	0.170	0.238		4.0	8.0	1.2		3.6											
RN5VD35A/C	3.413	3.500	3.587	0.105	0.175	0.245		4.0	8.0	1.2		3.6											
RN5VD36A/C	3.510	3.600	3.690	0.108	0.180	0.252		4.0	8.0	1.2		3.6											
RN5VD37A/C	3.608	3.700	3.792	0.111	0.185	0.259		4.0	8.0	1.2		3.6											
RN5VD38A/C	3.705	3.800	3.895	0.114	0.190	0.266		4.0	8.0	1.2		3.6											
RN5VD39A/C	3.803	3.900	3.997	0.117	0.195	0.273		4.0	8.0	1.2		3.6											

(Note) Refer to the previously defined "Minimum Operating Voltage".

Condition 1 : T_{opt}=25°CCondition 2 : -30°C≤T_{opt}≤80°C

T_{opt}=25°C

Output Current 3			Minimum Operating Voltage		C _D Pin Threshold Voltage				C _D Pin Output Current 1			C _D Pin Output Current 2			Delay Resistance			Detector Threshold Tempco.		
I _{OUT3} (mA)			V _{DDL} (V)		V _{TC_D} (V)				I _{CD1} (μA)			I _{CD2} (μA)			R _D (MΩ)			$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$ (ppm/°C)		
conditions	MIN.	TYP.	TYP.	MAX.	conditions	MIN.	TYP.	MAX.	conditions	MIN.	TYP.	conditions	MIN.	TYP.	MIN.	TYP.	MAX.	conditions	TYP.	
P _{ch} V _{DS} = -2.1V V _{DD} = 4.5V	1.0	2.0	(Note1) Condition1 0.55 Condition2 0.65	(Note1) Condition1 0.70 Condition2 0.80	V _{DD} = (-V _{DET}) ×1.1V	V _{DD} ×	V _{DD} ×	V _{DD} ×	V _{DS} = 0.1V V _{DD} = 0.7V	2.0	30	V _{DS} = 0.5V V _{DD} = 1.5V	V _{DD} = 0.85V	10	100	0.5	1.0	2.0	-30°C≤ T _{opt} ≤80°C	±100
													V _{DD} = 1.0V	50	200					
						V _{DD} ×	V _{DD} ×	V _{DD} ×												
						V _{DD} ×	V _{DD} ×	V _{DD} ×												
						V _{DD} ×	V _{DD} ×	V _{DD} ×						200	800					

RN5VD

• RN5VD40A/C to RN5VD60A/C

Part Number.	Detector Threshold			Hysteresis			Supply Current 1			Supply Current 2			Output Current 1			Output Current 2		
	-V _{DET} (V)			V _{HYS} (V)			I _{SS1} (μA)			I _{SS2} (μA)			I _{OUT1} (mA)			I _{OUT2} (mA)		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	conditions	TYP.	MAX.	conditions	TYP.	MAX.	conditions	MIN.	TYP.	conditions	MIN.	TYP.
RN5VD40A/C	3.900	4.000	4.100	0.120	0.200	0.280	V _{DD} = (-V _{DET}) -0.16V	5.0	10.0	V _{DD} = (-V _{DET}) +2.0V	1.3	3.9	N _{ch} V _{DS} = 0.05V V _{DS} = 0.7V	0.01	0.05	N _{ch} V _{DS} = 0.5V V _{DS} = 1.5V	1.0	2.0
RN5VD41A/C	3.998	4.100	4.202	0.123	0.205	0.287												
RN5VD42A/C	4.095	4.200	4.305	0.126	0.210	0.294												
RN5VD43A/C	4.193	4.300	4.407	0.129	0.215	0.301												
RN5VD44A/C	4.290	4.400	4.510	0.132	0.220	0.308												
RN5VD45A/C	4.388	4.500	4.612	0.135	0.225	0.315		5.5	11.0									
RN5VD46A/C	4.485	4.600	4.715	0.138	0.230	0.322												
RN5VD47A/C	4.583	4.700	4.817	0.141	0.235	0.329												
RN5VD48A/C	4.680	4.800	4.920	0.144	0.240	0.336												
RN5VD49A/C	4.778	4.900	5.022	0.147	0.245	0.343	V _{DD} = (-V _{DET}) -0.20V	6.0	12.0	1.4	4.2							
RN5VD50A/C	4.875	5.000	5.125	0.150	0.250	0.350												
RN5VD51A/C	4.973	5.100	5.227	0.153	0.255	0.357												
RN5VD52A/C	5.070	5.200	5.330	0.156	0.260	0.364												
RN5VD53A/C	5.168	5.300	5.432	0.159	0.265	0.371												
RN5VD54A/C	5.265	5.400	5.535	0.162	0.270	0.378												
RN5VD55A/C	5.363	5.500	5.637	0.165	0.275	0.385		6.5	13.0									
RN5VD56A/C	5.460	5.600	5.740	0.168	0.280	0.392												
RN5VD57A/C	5.558	5.700	5.842	0.171	0.285	0.399												
RN5VD58A/C	5.655	5.800	5.945	0.174	0.290	0.406												
RN5VD59A/C	5.753	5.900	6.047	0.177	0.295	0.413												
RN5VD60A/C	5.850	6.000	6.150	0.180	0.300	0.420												

(Note) Refer to the previously defined "Minimum Operating Voltage".

Condition 1 : T_{opt}=25°C

Condition 2 : -30°C≤T_{opt}≤80°C

T_{opt}=25°C

Output Current 3			Minimum Operating Voltage		C _D Pin Threshold Voltage				C _D Pin Output Current 1			C _D Pin Output Current 2			Delay Resistance			Detector Threshold Tempco.	
I _{OUT3} (mA)			V _{DDL} (V)		V _{TCD} (V)				I _{CD1} (μA)			I _{OUT1} (mA)			I _{OUT2} (mA)			$\frac{\Delta-V_{DET}}{\Delta T_{opt}}$ (ppm/°C)	
conditions	MIN.	TYP.	TYP.	MAX.	conditions	MIN.	TYP.	MAX.	conditions	MIN.	TYP.	conditions	MIN.	TYP.	conditions	TYP.	MAX.	conditions	TYP.
P _{ch} V _{DS} = -2.1V V _{DD} = 8.0V	1.5	3.0	(Note1) Condition1 0.55 Condition2 0.65	(Note1) Condition1 0.70 Condition2 0.80	V _{DD} = (-V _{DET}) 1.1V	V _{DD} × 0.4	V _{DD} × 0.5	V _{DD} × 0.6V	V _{DS} = 0.1V V _{DD} = 0.7V	2.0	30	V _{DS} = 0.5V V _{DD} = 1.5V	200	800	0.5	1.0	2.0	-30°C ≤ T _{opt} ≤ 80°C	±100

OPERATION




FIG. 1 Block Diagram




FIG. 2 Operation Diagram

Step	Step 1	Step 2	Step 3	Step 4	Step 5
Comparator (–) Pin Input Voltage	I	II	II	II	I
Comparator Output	L	H	Indefinite	H	L
Tr. 1, 2	OFF	ON	Indefinite	ON	OFF
Output Tr.	Nch	OFF	ON	Indefinite	ON
	Pch	ON	OFF	Indefinite	OFF

I. $\frac{R_b + R_c}{R_a + R_b + R_c} \cdot V_{DD}$

II. $\frac{R_b}{R_a + R_b} \cdot V_{DD}$

- Step 1. Output Voltage is equal to Pull-up Voltage.


Step 2. When Input Voltage (V_{DD}) reaches the state of $V_{ref} \geq V_{DD} \cdot (R_b + R_c) / (R_a + R_b + R_c)$ at Point A (Detected Voltage $-V_{DET}$), the output of Comparator is reserved, so that Output Voltage becomes GND. Discharging is performed from C_D pin connected to External Capacitor. No delay time is generated.

Step 3. Output Voltage becomes indefinite when Power Source Voltage (V_{DD}) is smaller than Minimum Operating Voltage. When the output is pulled up, V_{DD} is output.

Step 4. Output Voltage becomes equal to GND.

Step 5. When Input Voltage (V_{DD}) reaches the state of $V_{ref} \leq V_{DD} \cdot R_b / (R_a + R_b)$ at Point B (Released Voltage $+V_{DET}$), the output of Comparator is reversed, and the External Capacitor is charged through C_D pin, so that Output Voltage becomes equal to Pulled-up Voltage after a delay time $t_D (=0.69 \times 1.0 \times C_D)$.

• Output Delay Operation



When the Supply Voltage crosses the Released Voltage (+V_{DET}) from a low value to a value higher than the Released Voltage (+V_{DET}), the CD pin Voltage starts to increase (starts to charge the external capacitor).

The Output Voltage is maintained at "L" level until the CD pin Voltage reaches to V_{TCD} (CD pin Threshold Voltage) after that the Output Voltage is reversed to "H" state.

The time period from beginning of charging capacitor to Output Voltage reversing represents the Output Delay (t_D).

• Output Delay Time

Delay time (t_D) can be set accordance with the capacitance C_D of external capacitor as below

$$t_D = 0.69 \times 10^6 \times C_D \text{ (s)}$$

TEST CIRCUITS




FIG. 3 Supply Current test Circuit




FIG. 4 Detector Threshold Test Circuit




FIG. 5 Nch Driver Output Current Test Circuit




FIG. 6 Pch Driver Output Current Test Circuit




FIG. 7 C_D pin Threshold Voltage Test Circuit




FIG. 8 C_D pin Sink Current Test Circuit








FIG. 9 Output Delay Time Test Circuit



*) at FIG.4,7,9. CMOS Output Type does not need pull-up resistor.


TYPICAL CHARACTERISTICS

1) Supply Current vs. Input Voltage









2) Detector Threshold vs. Temperature








3) Output Voltage vs. Input Voltage










4) Nch Driver Output Current vs. V_{DS}




5) Nch Driver Output Current vs. Input Voltage






6) Pch Driver Output Current vs. Input Voltage










7) Co pin Threshold Voltage vs. Temperature




8) Cd pin Sink Current vs. Input Voltage






9) Cd pin Sink Current vs. Cd pin Voltage






10) Output delay Time vs. External Capacitance




11) Delay Resistance vs. Temperature




TYPICAL APPLICATIONS

• RN5VDxA CPU Reset Circuit (Nch Open Drain Output)


(1) Input Voltage to RN5VDxA is the same as the input voltage to CPU.




(2) Input Voltage to RN5VDxA is different from the input voltage to CPU.





• RN5VDxC CPU Reset Circuit (CMOS Output)



• Memory Back-up Circuit



• Manual Reset Circuit



APPLICATION HINTS




FIG.10





FIG.11

1. When RN5VD×C (CMOS Output) is used in FIG.10, this IC may oscillate by the through-type current at the detection when impedance is connected between Power Source VDD and RN5VD VDD Pin. When RN5VD×A (Nch Open Drain Output) is used in FIG.10, and R becomes excessively large, Detector Threshold may be varied because of the voltage drop of the supply current in the IC itself.
2. The connection as shown in FIG. 11 may cause the oscillation in both RN5VD×C (CMOS Output) and RN5VD×A (Nch Open Drain Output)


PACKAGE DIMENSIONS (Unit: mm)

- SOT-23-5



TAPING SPECIFICATION (Unit: mm)

- SOT-23-5





RICOH COMPANY, LTD.
ELECTRONIC DEVICES DIVISION

HEADQUARTERS

13-1, Himemuro-cho, Ikeda City, Osaka 563-8501, JAPAN
Phone 81-727-53-1111 Fax 81-727-53-6011

YOKOHAMA OFFICE (International Sales)

3-2-3, Shin-Yokohama, Kohoku-ku, Yokohama City, Kanagawa 222-8530,
JAPAN
Phone 81-45-477-1697 Fax 81-45-477-1694 · 1695
<http://www.ricoh.co.jp/LSI/english/>

RICOH CORPORATION
ELECTRONIC DEVICES DIVISION

SAN JOSE OFFICE

3001 Orchard Parkway, San Jose, CA 95134-2088, U.S.A.
Phone 1-408-432-8800 Fax 1-408-432-8375