




Features

- Multiturn / Wirewound / Industrial / Sealed
- Listed on the QPL for style RT24 per MIL-R-27208 and RTR24 per High-Rel MIL-R-39015
- Panel mount option available
- RoHS compliant*

- For trimmer applications/processing guidelines, [click here](#)

3290 - 3/8" Square Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range 10 to 50K ohms
(see standard resistance table)
Resistance Tolerance $\pm 5\%$ std.
(tighter tolerance available)
Absolute Minimum Resistance 0.1 % or 1 ohm max.
(whichever is greater)
Noise 100 ohms ENR max.
Resolution (see standard resistance table)
Insulation Resistance 500 vdc.
1,000 megohms min.
Dielectric Strength
Sea Level 1,000 vac
80,000 Feet 350 vac
Adjustment Travel 25 turns nom.

Environmental Characteristics

Power Rating @ 85 °C 1.0 watt
Power Rating @ 150 °C 0 watt
Temperature Range ... -65 °C to +150 °C
Temperature Coefficient ± 50 ppm/°C
Seal Test 85 °C Fluorinert†
Humidity MIL-STD-202 Method 106
96 hours (2 % Δ TR; 100 Megohms IR)
Vibration 30 G
(1 % Δ TR; 0.5 % + resolution Δ VR)
Shock 100 G
(1 % Δ TR; 0.5 % + resolution Δ VR)
Load Life ..1,000 hours 1.0 watt @ 85 °C
(2 % Δ TR; 500 ohms ENR)
Rotational Life 200 cycles
(2 % Δ TR; 500 ohms ENR)


Physical Characteristics

Torque 5.0 oz-in. max.
Mechanical Stops Wiper idles
Terminals Solderable printed circuit pins
Weight 0.025 oz.
Marking Manufacturer's trademark,
resistance code, wiring diagram,
date code, manufacturer's model
number and style
Wiper 50 % (Actual TR) $\pm 10\%$
Flammability U.L. 94V-0
Standard Packaging 50 pcs. per tube
Adjustment Tool H-90


Product Dimensions

3290H



Common Dimensions



3290P



3290W



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$
TOLERANCES: $\pm \frac{0.25}{(.010)}$ EXCEPT WHERE NOTED

How To Order

Model **3290 H - 1 - 103 M**
Style _____
Standard or Modified _____
Product Indicator _____
-1 = Standard Product
Resistance Code _____
Optional Suffix Letter _____
M = Panel Mount
(Factory Installed)

Consult factory for other available options.

Standard Resistance Table

Resistance (Ohms)	Resistance Code	Nominal Resolution (Percent)
10	100	1.11
20	200	0.93
50	500	0.62
100	101	0.60
200	201	0.54
500	501	0.42
1,000	102	0.33
2,000	202	0.26
5,000	502	0.20
10,000	103	0.17
20,000	203	0.14
25,000	253	0.13
50,000	503	0.11

Popular values listed in boldface. Special resistances available.