


10		9		8		7		6		5		4		3		2		19003	
	LOOSE PIECE MATERIAL NUMBER	LOOSE PIECE ENGRNG NUMBER	CONTINUOUS STRIP MATERIAL NUMBER	CONTINUOUS STRIP ENGRNG NUMBER	MYLAR TAPE MATERIAL NUMBER	MYLAR TAPE ENGRNG NUMBER	WIRE RANGE AWG	FITS MALE TAB SIZE		INSULATION COLOR	STOCK THICK.	"A" MAX.	"B" MIN.	"C" MAX.	"D" MWID	"E" MAX.	"H" ±.02/0.5		
F	I90030071	M-2212	I90030106	M-2212C	I90030073	M-2212T	26-24	.250x.032 (6.35x0.81)		YELLOW	.016/0.41	.86/21.8	.028/0.71	.38/9.7	.075/1.90	.18/4.6	1.42/35.9		
	I90030064	M-2210	I90030103	M-2210C	I90030067	M-2210T	26-24	.187x.020 (4.75x0.51)		YELLOW	.016/0.41	.78/19.8	.028/0.71	.32/8.1	.075/1.90	.16/4.1	1.38/34.9		
	I90030068	M-2211	I90030104	M-2211C	I90030070	M-2211T	26-24	.187x.032 (4.75x0.81)		DK YELLOW	.016/0.41	.78/19.8	.028/0.71	.32/8.1	.075/1.90	.16/4.1	1.38/34.9		
	I90030001	AA-2201	I90030105	AA-2201C	I90030003	AA-2201T	22-18	.250x.032 (6.35x0.81)		SALMON	.016/0.41	.86/21.8	.056/1.42	.38/9.7	.135/3.43	.18/4.6	1.42/35.9		
	I90030036	AA-2213	I90030109	AA-2213C	I90030074	AA-2213T	22-18	.205x.020 (5.21x0.51)		SALMON	.016/0.41	.78/19.8	.056/1.42	.32/8.1	.135/3.43	.16/4.1	1.38/34.9		
E	I90030038	AA-2214	I90030110	AA-2214C	I90030075	AA-2214T	22-18	.205x.032 (5.21x0.81)		PINK	.016/0.41	.78/19.8	.056/1.42	.32/8.1	.135/3.43	.16/4.1	1.38/34.9		
	I90030011	AA-2202	I90030107	AA-2202C	I90030013	AA-2202T	22-18	.187x.020 (4.75x0.51)		SALMON	.016/0.41	.78/19.8	.056/1.42	.32/8.1	.135/3.43	.16/4.1	1.38/34.9		
	I90030017	AA-2203	I90030108	AA-2203C	I90030020	AA-2203T	22-18	.187x.032 (4.75x0.81)		PINK	.016/0.41	.78/19.8	.056/1.42	.32/8.1	.135/3.43	.16/4.1	1.38/34.9		
	I90030024	AA-2204	I90030097	AA-2204C	I90030026	AA-2204T	22-18	.110x.020 (2.79x0.51)		SALMON	.012/0.30	.78/19.8	.056/1.42	.23/5.9	.135/3.43	.15/3.8	1.39/35.3		
	I90030030	AA-2205	I90030098	AA-2205C	I90030032	AA-2205T	22-18	.110x.032 (2.79x0.81)		PINK	.012/0.30	.78/19.8	.056/1.42	.23/5.9	.135/3.43	.15/3.8	1.39/35.3		
	I90030040	BB-2206	I90030041	BB-2206C	I90030042	BB-2206T	16-14	.250x.032 (6.35x0.81)		BLUE	.016/0.41	.86/21.8	.079/2.00	.38/9.7	.160/4.06	.18/4.6	1.42/35.9		
	I90030062	BB-2215	I90030085	BB-2215C	I90030077	BB-2215T	16-14	.205x.020 (5.21x0.51)		BLUE	.016/0.41	.78/19.8	.079/2.00	.32/8.1	.160/4.06	.17/4.3	1.41/35.7		
	I90030063	BB-2216	I90030086	BB-2216C	I90030078	BB-2216T	16-14	.205x.032 (5.21x0.81)		AQUA	.016/0.41	.78/19.8	.079/2.00	.32/8.1	.160/4.06	.17/4.3	1.41/35.7		
	I90030050	BB-2207	I90030051	BB-2207C	I90030052	BB-2207T	16-14	.187x.020 (4.75x0.51)		BLUE	.016/0.41	.78/19.8	.079/2.00	.32/8.1	.160/4.06	.17/4.3	1.41/35.7		
	I90030056	BB-2208	I90030057	BB-2208C	I90030058	BB-2208T	16-14	.187x.032 (4.75x0.81)		AQUA	.016/0.41	.78/19.8	.079/2.00	.32/8.1	.160/4.06	.17/4.3	1.41/35.7		
	I96060002	C-2293	I96060001	C-2293C	I96060003	C-2293T	12-10	.250x.032 (6.35x0.81)		YELLOW	.018/0.46	1.03/26.1	.117/2.97	.38/9.7	.235/5.97	.22/5.6	1.53/38.9		



NOTES:

1. MATERIAL: TERMINAL: BRASS
PLATING: ELECTRO-TIN
FERRULE: BRASS
PLATING: ELECTRO-TIN
INSULATION: NYLON 6/6 94V-2.
COLOR: SEE CHART
2. MWID = MAXIMUM WIRE INSULATION DIAMETER
3. PARTS ARE ROHS COMPLIANT.

SALES DRAWING

DWG UPDATED EC NO: WNA2011-0481 13/03/21 CHKD: JMACNEIL APPR: JMACNEIL 2013/04/19 2013/05/01	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
				IN/MM		---	INCH					
					mm	INCH	DRAWN BY	DATE	TITLE INSULKRIMP FEMALE FIQD STANDARD FLARE			
				4 PLACES	± ---	± ---	BRE	02/03/20				
				3 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX MOLEX INCORPORATED			
				2 PLACES	± ---	± ---	HEB	02/03/20				
				1 PLACE	± ---	± ---	APPROVED BY	DATE				
				ANGULAR ± ---°			RWD	02/03/20	MATERIAL NO. DOCUMENT NO. SHEET NO. SD-19003-005 1 OF 1			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART					
				REV	F3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						