



**ATTENTION**  
OBSERVE PRECAUTIONS  
FOR HANDLING  
ELECTROSTATIC  
DISCHARGE  
SENSITIVE  
DEVICES

### Features

- Single color.
- Suitable for all SMT assembly and solder process.
- Available on tape and reel.
- Ideal for backlighting.
- Package : 1500pcs / reel.
- Moisture sensitivity level : level 4.
- Low current IF=2mA operating.
- RoHS compliant.

### Description




The Blue source color devices are made with InGaN Light Emitting Diode.

Static electricity and surge damage the LEDs.

It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.

All devices, equipment and machinery must be electrically grounded.

### Package Dimensions



#### Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is  $\pm 0.25(0.01)$  unless otherwise noted.
3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
4. The device has a single mounting surface. The device must be mounted according to the specifications.



## Selection Guide

| Part No.            | Dice         | Lens Type   | Iv (mcd) [2]<br>@ 2mA |      | Viewing<br>Angle [1] |
|---------------------|--------------|-------------|-----------------------|------|----------------------|
|                     |              |             | Min.                  | Typ. | 2θ1/2                |
| AA3528LQBC/D-3.0VFU | Blue (InGaN) | WATER CLEAR | 5                     | 15   | 120°                 |

Notes:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
2. Luminous intensity/ luminous Flux: +/-15%.

## Electrical / Optical Characteristics at TA=25°C

| Symbol | Parameter                | Device | Typ. | Max. | Units | Test Conditions |
|--------|--------------------------|--------|------|------|-------|-----------------|
| λpeak  | Peak Wavelength          | Blue   | 468  |      | nm    | If=2mA          |
| λD [1] | Dominant Wavelength      | Blue   | 470  |      | nm    | If=2mA          |
| Δλ1/2  | Spectral Line Half-width | Blue   | 25   |      | nm    | If=2mA          |
| C      | Capacitance              | Blue   | 100  |      | pF    | Vf=0V;f=1MHz    |
| Vf [2] | Forward Voltage          | Blue   | 2.65 | 3    | V     | If=2mA          |
| Ir     | Reverse Current          | Blue   |      | 50   | uA    | VR=5V           |

Notes:


- 1.Wavelength: +/-1nm.
2. Forward Voltage: +/-0.1V.

## Absolute Maximum Ratings at TA=25°C

| Parameter                | Blue           | Units |
|--------------------------|----------------|-------|
| Power dissipation        | 90             | mW    |
| DC Forward Current       | 30             | mA    |
| Peak Forward Current [1] | 150            | mA    |
| Reverse Voltage          | 5              | V     |
| Operating Temperature    | -40°C To +85°C |       |
| Storage Temperature      | -40°C To +85°C |       |






Note:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.



Blue

AA3528LQBC/D-3.0V FU



## AA3528LQBC/D-3.0VFU

Reflow soldering is recommended and the soldering profile is shown below.  
Other soldering methods are not recommended as they might cause damage to the product.


Reflow Soldering Profile For Lead-free SMT Process.




### NOTES:

1. We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.
2. Don't cause stress to the epoxy resin while it is exposed to high temperature.
3. Number of reflow process shall be 2 times or less.


### Recommended Soldering Pattern (Units : mm; Tolerance: $\pm 0.1$ )



### Reel Dimension




### Tape Dimensions (Units : mm)



PACKING & LABEL SPECIFICATIONS

AA3528LQBC/D-3.0VFU



|                                                                                                                      |                                                                                                                    |
|----------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|
| <b>Kingbright</b>                                                                                                    |                                                                                                                    |
| P/NO: AA3528xxx                                                                                                      |                                                                                                                    |
| QTY: 1,500 pcs                                                                                                       | Q.C. <span style="border: 1px solid black; border-radius: 50%; padding: 2px;">Q C<br/>XX XX XXXX<br/>PASSED</span> |
| S/N: XXXX                                                                                                            |                                                                                                                    |
| CODE: XXX                                                                                                            |                                                                                                                    |
| LOT NO:                                                                                                              |                                                                                                                    |
| <br>XXXXXXXXXXXXXXXXXXXXXXXXXXXX |                                                                                                                    |
| RoHS Compliant                                                                                                       |                                                                                                                    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kingbright:](#)

[AA3528LQBC/D3.0VFU](#)