





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
SM0640L	6.0	.040	.048	0.60	5,000	C-2R
SM0650L	6.0	.050	.080	1.01	5,000	C-2R
SM06200L	6.0	.200	.344	4.20	5,000	C-2V
SM1220L	12.0	.020	.032	0.40	5,000	C-2V
SM1240L	12.0	.040	.088	1.11	5,000	C-2V
SM1250L	12.0	.050	.159	2.00	5,000	C-2V
SM12100L	12.0	.100	.255	3.21	5,000	C-2V
SM2420L	24.0	.020	.064	0.80	5,000	C-2F
SM2430L	24.0	.030	.159	2.00	5,000	C-2F
SM2440L	24.0	.040	.239	3.00	5,000	C-2F
SM2450L	24.0	.050	.279	3.51	5,000	C-2F
SM2480L	24.0	.080	.374	4.70	5,000	C-2F
SM2840L	28.0	.040	.303	3.81	5,000	C-2F
SM2850L	28.0	.050	.279	3.51	5,000	C-2F
SM3020L	30.0	.020	.104	1.31	5,000	C-2F
SM3040L	30.0	.040	.287	3.61	5,000	C-2F
SM3620L	36.0	.020	.143	1.80	5,000	C-2F
SM3640L	36.0	.040	.358	4.50	5,000	C-2F
SM3650L	36.0	.050	.400	5.10	5,000	C-2F
SM4820L	48.0	.020	.127	1.60	5,000	CC-2F
SM6020L	60.0	.020	.191	2.40	5,000	CC-2F

METRIC



THIRD ANGLE
PROJECTION

DRAWN BY
L. WENGSTROM

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED
1 PL +/- 0.2
2 PL +/-
ANGLE +/- 0

APPV'D BY DATE
QC 8/16/00

JKL

COMPONENTS CORPORATION

TITLE
T-1 1/2 TELEPHONE SLIDE BASE
LILIPUT T5.5

SIZE
A

FSCM NO.
55335

DRAWING
NO.
SLIDE BASE LILIPUT T5.5

SCALE
NONE

RELEASED
DATE 8/16/00

REVISION
DATE

REV.
NO.

SHEET
1 OF 1

REV. NO. DESCRIPTION/ECO NUMBER

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

8/16/00
APPV'D DATE

RELEASED