



	13	12	11	10	9	8	7	6	5	4	3	2	1	
J	PART NUMBER	ENGINEERING NUMBER	FINISH LENGTH											J
	1300060422	103001A01F030	3.00' +1.75" -0 [.9M +44.5 -0]											J
	1300060426	103001A01F060	6.00' +2.19" -0 [1.8M +55.6 -0]											J
I	1300060430	103001A01F120	12.00' +3.50" -0 [3.7M +88.9 -0]											I
	1300060433	103001A01F150	15.00' +6.50" -0 [4.6M +165.1 -0]											I
	1300060436	103001A01F200	20.00' +6.50" -0 [6.1M +165.1 -0]											I
H	1300060440	103001A01F250	25.00' +12.50" -0 [7.6M +317.5 -0]											H
	1300060442	103001A01F300	30.00' +12.50" -0 [9.1M +317.5 -0]											H

NOTE

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) WRAP LABEL IS MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE
- 4) MATES WITH: MINI CHANGE, 3 POLE RECEPTACLE
- 5) ELECTRICAL DATA:
 INLINE CORDSET
 FEMALE A-SIZE WITH FLYING LEADS
 16AWG UNSHIELDED
 POLES: 3
 MAX. VOLTAGE: 600V
 MAX. CURRENT 13A
 PROTECTION IP67
 TEMPERATURE RANGE: -20°C TO 105°C
- 6) PACKAGING:
 CABLE ASSEMBLIES ARE BAGGED SEPERATELY
 IN POLY BAGS WITH BAR CODE LABEL ATTACHED
 TO OUTSIDE OF BAG.
- 7) ASSEMBLY IS RoHS COMPLIANT.
- 8) CERTIFICATION
 UL RECOGNIZED, FILE NO. E152210
 CSA CERTIFIED, FILE NO. LR6837

6	1	LABEL	PLASTIC FILM	BLACK/YELLOW
5	3	CONTACT SOCKET	COPPER ALLOY	GOLD PLATED
4	1	INSERT	PVC	YELLOW
3	1	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
2	1	OVERMOLD	PVC	YELLOW
1	1	CABLE, 16AWG-3 TYPE ST00W	PVC	YELLOW
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH



RELEASE EC NO: WNA2010-0397 DRWN: BWOODMAN 12/22/09 CHKD: - APPR: JFMURPHY 2010/01/05	DESCRIPTION	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY DATE		TITLE MINI CHANGE ASSEMBLY 3-POLE FEMALE 90D 16/3AWG PVC  MOLEX INCORPORATED					
			4 PLACES	±----	±---	TWOLDEGE 2009/07/29							
			3 PLACES	±.005	±.005	CHECKED BY DATE							
			2 PLACES	±.013	±.010	BWOODMAN 2009/07/29							
			1 PLACE	±.025	±.020	APPROVED BY DATE		 MOLEX INCORPORATED					
			ANGULAR ±1/2°			JFMURPHY 2010/01/05							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130006-015		SHEET NO. 1 OF 1			
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						