

Model 6733, 6734
Test Lead Wire with Silicone or PVC Insulation

Features

- Same wire as used with the Pomona test leads and patch cords.
- Make your own “Extra Long” test leads, jumpers or patch cords.
- Fits Pomona “Do-It-Yourself” banana plugs and jacks.
- High temperature and voltage ratings.
- Silicone insulation with high wire strand count allows for superb flexibility.
- Wear indication with double insulated (dual extruded) silicone leads shows white inner layer for increased safety.
- Wire will comply with International Safety Standard CAT III, IEC61010-031 requirements when correctly terminated with other components designed to meet CAT III, IEC61010-031 requirements.



| Specifications: | 6733 | 6734 |
|---------------------|---------------------------------|--------------------------------|
| Insulation: | Silicone | PVC |
| Length: | 50 FT (15.2 meters) | 50 FT (15.2 meters) |
| Wire size: | 18 AWG | 18 AWG |
| Wire: | 192 X 41 bare copper | 65 X 36 tinned copper |
| Diameter (OD): | .144" (3.60mm) | .144" (3.60mm) |
| Temperature: | -58° to +302°F (-50° to +150°C) | -4° to +221°F (-20° to +105°C) |
| Wire Rated Voltage: | 10,000 DC * | 5,000 DC * |
| Current: | 20 A | 15 A |

| Ordering Information: | | |
|-----------------------|--------|--------|
| Black Wire: | 6733-0 | 6734-0 |
| Red Wire: | 6733-2 | 6734-2 |

* Hands free testing in controlled voltage environment: For CE compliance: not intended for hand held use at voltages above 30 Vrms /42.2 Vpk / 60 Vdc or when current exceeds 8A maximum.

USA: Sales: 800-490-2361
 Technical Support: technicalsupport@pomonatest.com
 Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ± .02" (.51 mm), .xxx = ± .005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.