





- 1 POST TO WITHSTAND 13 NEWTONS (3LBS.) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2 TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3 MEASURED AT SURFACE -A-
- 4 PLASTIC FLASH PERMITTED IN THIS AREA.
- 5 PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- 6 ONE HOLE MAY BE UNDERSIZED (.065/.060 DIA.) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7 MATERIAL: HEADER-THERMOPLASTIC POLYESTER GLASS-FILLED 94V-0(NATURAL) POST-COPPER ALLOY (TIN PLATED)
- 8 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 9 PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10 POST TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11 POST MUST WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12 DIMENSION SHOULD BE .175 MIN WHEN MATING WITH A MTA 156 CONNECTOR ASSEMBLY OR A SL-156 CONNECTOR ASSEMBLY.
- 13 PIN BURR OF .005 MAX. VERTICAL AND .003 MAX. HORIZONTAL PERMITTED AT POST TIPS ON BOTH ENDS.
- 14 PRELIMINARY- NOT FOR PRODUCTION.

641936-1 SHOWN

7	1-641936-0
3, 7, 8	641936-9
4, 8	641936-8
2, 5, 7	641936-7
8	641936-6
2, 4	641936-5
2,4,6,8	641936-3
3	641936-1
POST NUMBER OMITTED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 17JUN04		TE Connectivity	
DIMENSIONS: INCHES		CHK D. BOSSI 17JUN04		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVED D. BOSSI 17JUN04		PRODUCT SPEC	
0. PLC ± .005		APPLICATION SPEC		SIZE	
1. PLC ± .005		WEIGHT		CAGE CODE	
2. PLC ± .005		CUSTOMER DRAWING		DRAWING NO.	
3. PLC ± .005		SCALE 5:1		SHEET 1 OF 1	
4. PLC ± .005		REV AD		REV	
ANGLES		REV		REV	