


TINA2-MX-6 lenses for CREE MX-6 LEDs




- Designed & optimized for Cree MX-6 series of LEDs
- Lens material optical grade PC with high UV and temperature resistance (130°C/220°F). Allows use of high current and temperature conditions
- Best available optical efficiency, over 90%, with an extremely good cutoff of light
- Fastening to heat sink with a PU foam adhesive tape of automotive grade (included)
- Compact dimensions 16.1 x 11 mm.

LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Tina-MX-6 REAL SPOT	CA11171 Tina2-RS-MX6	±9°
Tina-MX-6 DIFFUSER	CA11172 Tina2-D-MX6	±12°
Tina-MX-6 MEDIUM	CA11174 Tina2-M-MX6	±15°
Tina-MX-6 OVAL	CA11173 Tina2-O-MX6	±12°x±17°
Tina-MX-6 WIDE	CA11175 Tina2-W-MX6	±20°
Tina-MX-6 WW	CA11176 Tina2-WW-MX6	±28°


MEASUREMENTS

Relative Intensity of CA11171_Tina2-RS-MX6




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of CA11172_Tina2-D-MX6




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of CA11174_Tina2-M-MX6




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of CA11173_Tina2-O-MX6





© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of CA11175_Tina2-W-MX6




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of CA11176_Tina2-WW-MX6



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWINGS



© Ledit Oy – PRELIMINARY - Subject to change without prior notice