


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		E	EC 0G3B 0215 05	16SEP05	BSV	RCJ






- 1

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2

WIRE RANGE: 0.2–1mm² [24–18 AWG].
INSULATION RANGE: 1.02–2.54[.040–.100] DIA.
- 3

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.



GOLD 4	0.30 [.012] PH BRZ	1-770010-0
GOLD 1	0.30 [.012] PH BRZ	770010-4
PRE-TIN	0.30 [.012] PH BRZ	770010-3
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 20JAN93	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK R. SWING 20JAN93				
		APVD M. TRULL 01APR93	NAME SOCKET, UNIVERSAL MATE-N-LOK(TM) II			
		PRODUCT SPEC				
MATERIAL SEE TABLE		APPLICATION SPEC				
		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=770010	RESTRICTED TO -
SEE TABLE		FINISH SEE TABLE	CUSTOMER DRAWING			
			SCALE 4:1	SHEET 1 of 1	REV E	

