


**TEMA**®

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,  
WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED  
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC  
TECHNOLOGY.

SPC-F005.DWG



REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1453	A	Released	JWM	1/9/04	HO	1/13/04	JC	1/23/04

NOTES:

- General purpose bead probe
- 3 foot PVC insulated cable
- Temperature range -50°C to 200°C [-58°F ~ 392°F]
- Can be used with all standard K-Type thermometers and multimeters with temperature function

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED  
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE  
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE  
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE  
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT  
FOR THE INTENDED USE AND ASSUME ALL RISK AND  
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:		DRAWN BY:	DATE:	DRAWING TITLE:		ELECTRONIC FILE		
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		Jeff McVicker	1/9/04	SIZE	DWG. NO.	84N2123.dwg	REV	A
		CHECKED BY:	DATE:					
		Hisham Odish	1/13/04		72-2061			
		APPROVED BY:	DATE:	SCALE:	U.O.M.: INCHES [mm]	SHEET:	1 OF 1	John Cole
			1/23/04	NTS				