

	13	12	11	10	9	8	7	6		2145	4	3	2	1	
J	ENG. NO.		HOUSING NO.		TERMINAL NO.		DIM. C		EDP ON SHT/COL						J
	A-2145-AANA(I02)-*		2145-N-AN		2144-AA-A IAA-I02B		(3.68) / .145		7 / 1						
	A-2145-AANA(I22)-*		2145-N-AN		2144-AA-A IAA-I22B		(3.68) / .145		7 / 2						
	A-2145-AANA(505)-*		2145-N-AN		2144-AA-A IAA-505B		(3.68) / .145		7 / 3						
	A-2145-AANA(507)-*		2145-N-AN		2144-AA-A IAA-507B		(3.68) / .145		7 / 4						
I	A-2145-AANB(558)-*		2145-N-AN		2144-BA-A IAA-558B		(3.68) / .145		8 / 1						I
	A-2145-AANA(P913)-*		2145-N-AN		2144-AA-A IAA-P913B		(3.68) / .145		8 / 2						
	A-2145-ABNA(I22)-*		2145-NBK-AN		2144-AA-A IAA-I22B		(3.68) / .145		8 / 3						
	A-2145-ABNA(P913)-*		2145-NBK-AN		2144-AA-A IAA-P913B		(3.68) / .145		8 / 4						
	A-2145-AANA(587)-*		2145-N-AN		2144-AA-A IAA-587B		(3.68) / .145		9 / 1						
	A-2145-AGNA(P913)-*		2145-N-CN		2144-AA-A IAA-587B		(3.68) / .145		9 / 2						
H	A-2145-BANH(I02)-*		2145-N-AN		2188-(I02)		(4.06) / .160		9 / 3						H
	A-2145-BANH(I22)-*		2145-N-AN		2188-(I22)		(4.06) / .160		9 / 4						
	A-2145-BANL(P913)-*		2145-N-AN		6298-(P913)		(4.06) / .160		10 / 1						
	A-2145-BANL(565)-*		2145-N-AN		6298-(565)		(4.06) / .160		10 / 2						
	A-2145-BBNH(I22)-*		2145-NBK-AN		2188-(I22)		(4.06) / .160		10 / 3						
G	A-2145-CANA(I02)-*		2145-N-AN		2144-AA-A IAA-I02B		(3.05) / .120		10 / 4						G
	A-2145-CANA(I22)-*		2145-N-AN		2144-AA-A IAA-I22B		(3.05) / .120		11 / 1						
	A-2145-CANB(565)-*		2145-N-AN		2144-BA-A IAA-565B		(3.05) / .120		11 / 2						
	A-2145-CANC(P913)-*		2145-N-AN		2144-AA-A2AA-P913B		(4.80) / .189		11 / 3						
	A-2145-FGNA(587)-*		2145-N-CN		2144-AA-A IAA-587B		(3.05) / .120		11 / 4						
	A-2145-FANA(P913)-*		2145-N-AN		2144-AA-A IAA-P913B		(3.05) / .120		12 / 1						
F	A-2145-DANC(P913)-*		2145-N-AN		2144-AA-A2AA-P913B		(4.80) / .189		12 / 2						F
	A-2145-BBNH(P913)-*		2145-NBK-AN		2188-(P913)		(4.06) / .160		12 / 3						
	A-2145-CBNA(P913)-*		2145-NBK-AN		2144-AA-A IAA-P913B		(3.05) / .120		12 / 4						
	A-2145-FGNA(550)-*		2145-N-CN		2144-AA-A IAA-550B		(3.05) / .120		13 / 1						
	A-2145-BANH(P913)-*		2145-N-AN		2188-(P913)		(4.06) / .160		13 / 2						
E	A-2145-BANH(587)-*		2145-N-AN		2188-(587)		(4.06) / .160		13 / 3						E
	A-2145-FANA(503)-*		2145-N-AN		2144-AA-A IAA-503B		(3.05) / .120		13 / 4						
	A-2145-EANH(P913)-*		2145-N-AN		2188-(P913)		(4.06) / .160		14 / 1						
	A-2145-AANK(P913)-*		2145-N-AN		4244-(P913)		(3.68) / .145		14 / 2						
	A-2145-ABNK(P913)-*		2145-NBK-AN		4244-(P913)		(3.68) / .145		14 / 3						
D	A-2145-ABNA(587)-*		2145-NBK-AN		2144-AA-A IAA-587B		(3.68) / .145		14 / 4						D
	A-2145-AANA-(I09)-*		2145-N-AN		2144-AA-A IAA-I09B		(3.68) / .145		15 / 1						
	A-2145-CANA(P913)-*		2145-N-AN		2144-AA-A IAA-P913B		(3.05) / .120		15 / 2						
	A-2145-AANB(I22)-*		2145-N-AN		2144-BA-A IAA(I22)B		(3.68) / .145		15 / 3						
	A-2145-BANL(I22)-*		2145-N-AN		6298-(I22)		(4.06) / .160		15 / 4						
	A-2145-CANB(I22)-*		2145-N-AN		2144-BA-A IAA(I22)B		(3.05) / .120		16 / 1						
C	A-2145-EGNH(P913)-*		2145-N-CN		2188-(P913)		(4.06) / .160		16 / 2						C
	A-2145-FGNA(P913)-*		2145-N-CN		2144-AA-A IAA-P913B		(3.05) / .120		16 / 3						
	A-2145-CANA(587)-*		2145-N-AN		2144-AA-A IAA-587B		(3.05) / .120		16 / 4						
	A-2145-BHNH(I22)-*		2145-NGN-AN		2188-(I22)		(4.06) / .160		17 / 1						
	A-2145-BJNH(I22)-*		2145-NYW-AN		2188-(I22)		(4.06) / .160		17 / 2						
B	A-2145-BKNH(I22)-*		2145-NRD-AN		2188-(I22)		(4.06) / .160		17 / 3						B
							/		/						

13			12			11			10			9			8			7			6			2145			4			3			2			1		
A-2145-CANA(122)-*												A-2145-CANB(565)-*						A-2145-CANC(P913)-*						A-2145-FGNA(587)-*														
PART NO.			ENG. NO(SUFFIX ONLY)			VOID CKT.			PART NO.			ENG. NO(SUFFIX ONLY)			VOID CKT.			PART NO.			ENG. NO(SUFFIX ONLY)			VOID CKT.			PART NO.			ENG. NO(SUFFIX ONLY)			VOID CKT.					
			-CA2A(122)									-CA2B(565)						09-52-1029			-CA2C(P913)									-FG2A(587)								
			-CA3A(122)									-CA3B(565)						09-52-1039			-CA3C(P913)									-FG3A(587)								
09-86-3043			-CA4A(122)									-CA4B(565)						09-52-1049			-CA4C(P913)									-FG4A(587)								
			-CA5A(122)									-CA5B(565)						09-52-1059			-CA5C(P913)									-FG5A(587)								
			-CA6A(122)			09-62-3066						-CA6B(565)						09-52-1069			-CA6C(P913)									-FG6A(587)								
09-86-3083			-CA7A(122)									-CA7B(565)						09-52-1079			-CA7C(P913)									-FG7A(587)								
			-CA8A(122)									-CA8B(565)						09-52-1089			-CA8C(P913)									-FG8A(587)								
			-CA9A(122)			09-62-3096						-CA9B(565)						09-52-1099			-CA9C(P913)			09-62-4094						-FG9A(587)								
09-86-3103			-CA10A(122)						09-62-3106			-CA10B(565)						09-52-1109			-CA10C(P913)									-FG10A(587)								
			-CA11A(122)									-CA11B(565)						09-52-1119			-CA11C(P913)									-FG11A(587)								
09-86-3123			-CA12A(122)									-CA12B(565)						09-52-1129			-CA12C(P913)									-FG12A(587)								
			-CA13A(122)									-CA13B(565)						09-52-1139			-CA13C(P913)									-FG13A(587)								
			-CA14A(122)									-CA14B(565)						09-52-1149			-CA14C(P913)									-FG14A(587)								
			-CA15A(122)									-CA15B(565)						09-52-1159			-CA15C(P913)			09-62-4154						-FG15A(587)								
			-CA16A(122)									-CA16B(565)									-CA16C(P913)									-FG16A(587)								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-62-4094](#)