

Sta-Kon®

Terminals



These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (re commended for solid wire). Serrated barrel increases grip on wire. Wire range identification is stamped on the tongue of each terminal.

Stock Thickness:

G & H = .05

J & K = .06

L & M = .07


Non-Insulated Ring – Tubular

Cat. No.	Pkg. Qty.	Wire Range	Bolt Hole	Wt./Lbs. Per 1000	Dimensions			
					A	B	C	M
D10161	200	8	#8	12	1.15	.41	.28	.95
D10361	200	8	#10	12	1.15	.41	.28	.95
D10711	200	8	1/4"	12	1.20	.45	.36	.97
D10721	200	8	5/16"	12	1.28	.56	.36	1.00
D10731	200	8	3/8"	12	1.28	.56	.36	1.00
D975*	200	8	1/2"	12	1.46	.83	.49	1.06
E10261	200	6	#10	14	1.26	.49	.24	1.02
E10711	200	6	1/4"	14	1.26	.49	.27	.99
E10721	200	6	5/16"	14	1.38	.60	.34	1.04
E10731	200	6	3/8"	14	1.38	.60	.34	1.04
F10261	100	4	#10	20	1.37	.55	.30	1.07
F10711	100	4	1/4"	20	1.37	.55	.30	1.07
F10721	100	4	5/16"	20	1.42	.62	.34	1.08
F10731	100	4	3/8"	20	1.42	.62	.34	1.08
F975*	200	4	1/2"	20	1.49	.83	.45	1.10
G2-14	10	2	1/4"	50	1.59	.69	.40	1.26
G2-516	10	2	5/16"	50	1.59	.69	.40	1.26
G2-38	10	2	3/8"	50	1.59	.69	.40	1.26
G2-12	10	2	1/2"	50	1.79	.80	.49	1.36
G926	100	2	#10	40	1.59	.69	.40	1.26
G971	100	2	1/4"	40	1.59	.69	.40	1.26
G972	100	2	5/16"	40	1.59	.69	.40	1.26
G973	100	2	3/8"	40	1.59	.69	.40	1.26
G975	100	2	1/2"	40	1.79	.80	.49	1.36
H971	100	1AN-1/0	1/4"	50	1.65	.77	.43	1.32
H972	100	1AN-1/0	5/16"	50	1.65	.77	.43	1.32
H973	100	1AN-1/0	3/8"	50	1.65	.77	.43	1.32
H975	100	1AN-1/0	1/2"	50	1.85	.77	.54	1.41
H10-14	10	1/0	1/4"	50	1.65	.77	.43	1.32
J971	50	1/0AN-2/0	1/4"	60	1.94	.84	.48	1.53
J972	50	1/0AN-2/0	5/16"	60	1.94	.84	.48	1.53
J973	50	1/0AN-2/0	3/8"	60	1.99	.84	.53	1.58
J974	50	1/0AN-2/0	7/16"	60	1.99	.89	.51	1.56
J975	50	1/0AN-2/0	1/2"	60	1.99	.89	.51	1.56
J20-38	10	2/0	3/8"	70	1.84	.83	.46	1.46
K971	50	2/0AN-3/0	1/4"	76	2.08	.93	.54	1.69
K972	50	2/0AN-3/0	5/16"	76	2.08	.93	.54	1.69
K973	50	2/0AN-3/0	3/8"	76	2.08	.93	.54	1.69
K974	50	2/0AN-3/0	7/16"	76	2.08	.93	.54	1.70
K975	50	2/0AN-3/0	1/2"	76	2.08	.93	.54	1.70
K30-38	5	3/0	3/8"	82	2.08	.93	.54	1.69
L973	50	3/0AN-4/0	3/8"	92	2.25	1.04	.57	1.77
L974	50	3/0AN-4/0	7/16"	92	2.25	1.04	.57	1.77
L975	50	3/0AN-4/0	1/2"	92	2.25	1.04	.57	1.77
L40-38	5	4/0	3/8"	100	2.25	1.04	.57	1.77
M972	50	4/0AN-250MCM	5/16"	112	2.28	1.12	.62	1.90
M973	50	4/0AN-250MCM	3/8"	112	2.40	1.12	.65	1.91
M974	50	4/0AN-250MCM	7/16"	112	2.40	1.12	.65	1.91
M975	50	4/0AN-250MCM	1/2"	112	2.40	1.12	.65	1.91
M250-38	5	250MCM	3/8"	135	2.40	1.12	.65	1.91

AN – Aircraft Wire

Installing tools: TBM6/TBM6S, WT3185 (G, H, J Series only)

Note: Not available on Mylar Tape.



Thomas & Betts