





LEAD FINISH:	SOLDER
BUSHING FINISH:	SILVER
CAPACITANCE	100pF
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 300VDC MAX. 125°C 200VDC MAX.
D.C. RESISTANCE	.005ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	

FREQ. MHz	I.L. (db)
10	--
30	--
100	3
1 GHz	20
10 GHz	28



MARKING:

PART: S101P
 BAG:
 SCI 9900-381-6020
 DATE CODE
 LOT NO.
 QTY./BAG (100 MAX.)

- NOTES:
1. SUGGESTED MOUNTING HOLE = ϕ .120
 2. HARDWARE IS INCLUDED.

	11	10	09	08	07	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC. ERIE, FAIRVIEW PENNSYLVANIA		
	CN 211524	CN 197243	CN 190641	CN 189484	CN 187040	CHANGE NOTICE	Fractions $\pm 1/64$		Dwn. JKAUFFMAN	Description FEED THRU RESIN SEAL FILTER
							Dec. .xx $\pm$			
							Dec. .xxx $\pm$.010			
							Angles $\pm 0^{\circ} 30'$			
							CODE IDENT. NO. DLSP2			
							Engr. T. Taylor	9900-381-6020		
							Scale NONE			