




REVISIONS				DATE	APPD
NO	LOC	QTY	ZONE	LTR	DESCRIPTION
1	BD	37		6	REDRAWN WITHOUT CHANGE



RECOMMENDED PC BOARD LAYOUT

- 1 NYLON, RED.
- 2 PHOSPHOR BRONZE.
- 3 3.81µm [L.000150] MIN TIN-LEAD OVER 1.27µm [L.000050] MIN NICKEL.
- 4 0.76µm [L.000030] MIN GOLD FOR A LENGTH OF 5.08 [L.200] MIN FROM MATING END, 3.81µm [L.000150] MIN TIN-LEAD FOR A LENGTH OF 5.36 [L.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [L.000050] MIN NICKEL.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING DOCUMENT MUST BE USED. SHOULD BE CONSULTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.25 [L.010] 3 PLC DEC ± ANGLES		DR 08/07/92 L.SIPE	NAME	
MATERIAL HOUSING: 1 CONTACTS: 2		CHK 8-25-92 R. STONE	AMP AMP Incorporated Harrisburg, PA 17105-3608	
PRODUCT SPEC		APPD 8-25-92 A. TRAVIS	SOCKET HEADER ASSEMBLY, 16 POSN, IN-LINE, METRIMATE	
FINISH CONTACTS: SEE TABLE		APPLICATION SPEC	SIZE CAGE CODE 00779	DRAWING NO 207615
WEIGHT		SCALE 2:1	SHEET 1 OF 1	

CUSTOMER DRAWING