





B	CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:			DRAWN		GJW		12APR05		Honeywell				B		
	OPERATING FORCE----- 91 GRAMS MAX		CONTACT ARRANGEMENT S P N O		NO PLACE X ±.040 ±1			CHECK		MDM		7MAY01								
A	RELEASE FORCE----- 9 GRAMS MIN		L278 6A, 1/8HP 125, <u>250</u> OR 277 VAC P 		ONE PLACE .X ±.030 ±0,4			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH, BASIC				A				
	TWO PLACE .XX ±.015 ±0,15																			
	DIFFERENTIAL TRAVEL----- .025 MAX				THREE PLACE .XXX ±.005 ±			DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED												
	OVERTRAVEL----- .064 MIN				ANGLES ± ±															
RELEASE TRAVEL----- .015 MIN				RAW MATERIAL-COMMERCIAL STANDARD			THIRD ANGLE PROJECTION				PTC 2D		ASME Y14.5M-1994		SCALE 2:1		WEIGHT		SHEET 1 OF 1	
																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1X2AE9-292](#)