




Part Number: 91525-8217

0.50mm Pitch LaneLink™ I/O Latch Receptacle, 12 Lane, Cx4 Ethernet, 24 Circuits, 2 Screw Holes, Panel Mount, Metal Gasket, Tape and Reel Packaging



Series image - Reference only

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	91525
Category:	I/O Connectors

Mates With Part(s):
[915340020](#), [915340021](#), [915340022](#), [916351010](#), [916351011](#), [916351012](#)

Product Environmental Compliance

EU RoHS:

ELV and RoHS Compliant

China RoHS:

REACH SVHC:

Low-Halogen Status:

Not Reviewed

Part Detail

General	
Status	Obsolete
Category	I/O Connectors
Series	91525
Application	Wire-to-Board
Comments	Metal Gasket
Component Type	Receptacle
Product Name	InfiniBand* , LaneLink™
Type	N/A
Physical	

Boot Color	N/A
Circuits (Loaded)	73
Circuits (maximum)	73
Circuits Detail	24 Differential Pair
Color - Resin	Black
Durability (mating cycles max)	250
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 2.10mm
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
Pitch - Mating Interface	1.50mm
Pitch - Termination Interface	1.50mm
Plating min - Mating	0.102µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20°C to +60°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	Yes
Wire Size AWG	N/A

Electrical

(Please review the Product Specification for specific details.)	
Current - Maximum per Contact	0.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

UPC	822350628051
-----	--------------

Reference - Drawing Numbers

Application Specification	AS-91803-001
Packaging Specification	PK-91803-001
Sales Drawing	SD-91525-004

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)