

NPN - MPS6601; PNP - MPS6651, MPS6652

MPS6652 is a Preferred Device

Amplifier Transistors

Features

- Voltage and Current are Negative for PNP Transistors
- Pb-Free Packages are Available*

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector - Emitter Voltage MPS6601/6651 MPS6652	V_{CEO}	25 40	Vdc
Collector - Base Voltage MPS6601/6651 MPS6652	V_{CBO}	25 30	Vdc
Emitter - Base Voltage	V_{EBO}	4.0	Vdc
Collector Current - Continuous	I_C	1000	mAdc
Total Device Dissipation @ $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D	625 5.0	W mW/ $^\circ\text{C}$
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	1.5 12	W mW/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-55 to +150	$^\circ\text{C}$

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient (Note 1)	$R_{\theta JA}$	200	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	83.3	$^\circ\text{C/W}$


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. $R_{\theta JA}$ is measured with the device soldered into a typical printed circuit board.




ON Semiconductor®


<http://onsemi.com>



TO-92
CASE 29
STYLE 1




STRAIGHT LEAD
BULK PACK



BENT LEAD
TAPE & REEL
AMMO PACK

MARKING DIAGRAM



MPS66xy = Device Code
x = 0 or 5
y = 1 or 2

A = Assembly Location
Y = Year

WW = Work Week
■ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

Preferred devices are recommended choices for future use and best overall value.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NPN – MPS6601; PNP – MPS6651, MPS6652

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Max	Unit
OFF CHARACTERISTICS					
Collector–Emitter Breakdown Voltage (I _C = 1.0 mAdc, I _B = 0)	MPS6601/6651 MPS6652	V _{(BR)CEO}	25 40	– –	Vdc
Collector–Base Breakdown Voltage (I _C = 100 µAdc, I _E = 0)	MPS6601/6651 MPS6652	V _{(BR)CBO}	25 40	– –	Vdc
Emitter–Base Breakdown Voltage (I _E = 10 µAdc, I _C = 0)		V _{(BR)EBO}	4.0	–	Vdc
Collector Cutoff Current (V _{CE} = 25 Vdc, I _B = 0) (V _{CE} = 30 Vdc, I _B = 0)	MPS6601/6651 MPS6652	I _{CES}	– –	0.1 0.1	µAdc
Collector Cutoff Current (V _{CB} = 25 Vdc, I _E = 0) (V _{CB} = 30 Vdc, I _E = 0)	MPS6601/6651 MPS6652	I _{CBO}	– –	0.1 0.1	µAdc

ON CHARACTERISTICS

DC Current Gain (I _C = 100 mAdc, V _{CE} = 1.0 Vdc) (I _C = 500 mAdc, V _{CE} = 1.0 Vdc) (I _C = 1000 mAdc, V _{CE} = 1.0 Vdc)		h _{FE}	50 50 30	– – –	–
Collector–Emitter Saturation Voltage (I _C = 1000 mAdc, I _B = 100 mAdc)		V _{CE(sat)}	–	0.6	Vdc
Base–Emitter On Voltage (I _C = 500 mAdc, V _{CE} = 1.0 Vdc)		V _{BE(on)}	–	1.2	Vdc

SMALL–SIGNAL CHARACTERISTICS

Current–Gain — Bandwidth Product (I _C = 50 mAdc, V _{CE} = 10 Vdc, f = 100 MHz)		f _T	100	–	MHz
Output Capacitance (V _{CB} = 10 Vdc, I _E = 0, f = 1.0 MHz)		C _{obo}	–	30	pF

SWITCHING CHARACTERISTICS

Delay Time	(V _{CC} = 40 Vdc, I _C = 500 mAdc, I _{B1} = 50 mAdc, t _p ≥ 300 ns Duty Cycle)	t _d	–	25	ns
Rise Time		t _r	–	30	ns
Storage Time		t _s	–	250	ns
Fall Time		t _f	–	50	ns

ORDERING INFORMATION

Device	Package	Shipping [†]
MPS6601RLRAG	TO–92 (TO–226) (Pb–Free)	2000 Units / Tape & Reel
MPS6651G	TO–92 (TO–226) (Pb–Free)	5000 Units / Bulk
MPS6652	TO–92 (TO–226)	
MPS6652G	TO–92 (TO–226) (Pb–Free)	
MPS6652RLRAG	TO–92 (TO–226) (Pb–Free)	2000 Units / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NPN – MPS6601; PNP – MPS6651, MPS6652





Figure 1. Thermal Response



*Total Shunt Capacitance of Test Jig and Connectors
For PNP Test Circuits, Reverse All Voltage Polarities

Figure 2. Switching Time Test Circuits

NPN – MPS6601; PNP – MPS6651, MPS6652

NPN




Figure 3. MPS6601/6602 DC Current Gain

PNP




Figure 4. MPS6651/6652 DC Current Gain




Figure 5. Current Gain Bandwidth Product




Figure 6. Current Gain Bandwidth Product




Figure 7. On Voltages




Figure 8. On Voltages

NPN – MPS6601; PNP – MPS6651, MPS6652

NPN




Figure 9. Capacitance

PNP




Figure 10. Capacitance




Figure 11. MPS6601/6602 Noise Figure




Figure 12. MPS6651/6652 Noise Figure




Figure 13. MPS6601/6602 Switching Times




Figure 14. MPS6651/6652 Switching Times

NPN – MPS6601; PNP – MPS6651, MPS6652

NPN




Figure 15. Base-Emitter Temperature Coefficient

PNP




Figure 16. Base-Emitter Temperature Coefficient




Figure 17. Safe Operating Area




Figure 18. Safe Operating Area




Figure 19. MPS6601/6602 Saturation Region





Figure 20. MPS6651/6652 Saturation Region


NPN – MPS6601; PNP – MPS6651, MPS6652

PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 29-11 ISSUE AM



STRAIGHT LEAD
BULK PACK




SECTION X-X


NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
H	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500	---	12.70	---
L	0.250	---	6.35	---
N	0.080	0.105	2.04	2.66
P	---	0.100	---	2.54
R	0.115	---	2.93	---
V	0.135	---	3.43	---



BENT LEAD
TAPE & REEL
AMMO PACK



SECTION X-X

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	MILLIMETERS	
	MIN	MAX
A	4.45	5.20
B	4.32	5.33
C	3.18	4.19
D	0.40	0.54
G	2.40	2.80
J	0.39	0.50
K	12.70	---
N	2.04	2.66
P	1.50	4.00
R	2.93	---
V	3.43	---

STYLE 1:

1. EMITTER
2. BASE
3. COLLECTOR

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ON Semiconductor:](#)

[MPS6652RLRAG](#)