



JKL PART NUMBER	LENGTH A +/- 2mm	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF350-20B	50mm	RGB HIGH OUTPUT WHITE 5400° KELVIN (REF.)	500	195	5 ± 1	28000 ± 2800	20,000
BF375-20B	75mm		525	210	5 ± 1	28000 ± 2800	20,000
BF386-20B	86mm		540	220	5 ± 1	28000 ± 2800	20,000
BF3100-20B	100mm		665	270	5 ± 1	28000 ± 2800	20,000
BF3115-20B	115mm		685	287	5 ± 1	28000 ± 2800	20,000
BF3130-20B	130mm		705	305	5 ± 1	28000 ± 2800	20,000
BF3160-20B	160mm		850	345	5 ± 1	28000 ± 2800	20,000
BF3180-20B	180mm		940	380	5 ± 1	28000 ± 2800	20,000
BF3216-20B	216mm		1100	440	5 ± 1	28000 ± 2800	20,000
BF3240-20B	240mm		1150	480	5 ± 1	28000 ± 2800	20,000
BF3250-20B	250mm		1200	520	5 ± 1	28000 ± 2800	20,000
BF3275-20B	275mm		1275	593	5 ± 1	28000 ± 2800	20,000
BF3300-20B	300mm		1350	665	5 ± 1	28000 ± 2800	20,000
BF3360-20B	360mm		1500	785	5 ± 1	28000 ± 2800	20,000
BF3380-20B	380mm		1590	825	5 ± 1	28000 ± 2800	20,000

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC	DIMENSIONS ARE IN MILLIMETERS	JKL COMPONENTS CORPORATION				
F	ADD PART NUMBER BF3115-20B	12/19/02	 THIRD ANGLE PROJECTION	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	MINIATURE COLD CATHODE FLUORESCENT LAMP				
E	ADD PART NUMBER BF3180-20B & BF3380-20B	11/30/01							
D	ADD PART NUMBER BF3240-20B	4/28/01			BF 3-20B				
C	ADD PART NUMBER BF3130-20B	9/11/00							
B	ADD PART NUMBER BF375-20B	4/21/00	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	
A	LENGTH ±5 TO ±2	2/25/00	L. WENGSTROM	F.D.	12/19/02	A	55335		
	RELEASED - CANCEL BF-3mm DIA DRAWING	2/21/00	- CAD DRAWING -			SCALE	RELEASED DATE	REVISION DATE	REV. NO.
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	MANUAL REVISIONS NOT PERMITTED			NONE	2/21/00	12/19/02	F
									SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF3380-20B](#)