




1. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. CABLE ASSEMBLY SHALL BE WIRED PER WIRING DIAGRAM.
3. MATERIAL:
- CONNECTOR HOUSINGS- POLYCARBONATE, UL 94V-0 RATED, WHITE.
 - STRAIN RELIEFS- CARBON STEEL WITH NICKEL PLATING 5.08µm [.000200] MINIMUM THICK.
 - CONTACTS- COPPER ALLOY WITH SILVER PLATED STRIP 3.81µm [.000150] MINIMUM THICK.
4. DIMENSION A SHALL BE MEASURED WITH CONDUIT IN THE RELAXED POSITION.
5. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
6. MANUFACTURING LOCATION, DATE CODE, PART NUMBER AND LENGTH SHALL BE INK STAMPED WHERE INDICATED.
7. APPLICATION: AMPINNERGY - MODULAR POWER DISTRIBUTION SYSTEM, A MANUFACTURED WIRING SYSTEM.
8. USE GROUND WIRE INSPECTION WINDOW TO VERIFY BONDING AND GROUNDING CONDUCTOR.

LOC		DIST		REVISONS			
HM	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
		U		REV ECO-12-020241	26NOV2012	JM	MS

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	J MCNEAL	11AUG2005	 TE Connectivity						
				CHK	F LINCOLN	11AUG2005							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	F LINCOLN	11AUG2005	NAME						
mm [INCHES]				PRODUCT SPEC		CABLE ASSEMBLY, POWER ENTRY, 5 WIRE							
		1 PLC ±		-		-							
		2 PLC ±		-		-							
		3 PLC ±		-		-							
		4 PLC ±		-		-							
		ANGLES		±		APPLICATION SPEC		-					
FINISH		-		WEIGHT		-		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		-		-		A1		100779		C=555858		-	
CUSTOMER DRAWING						SCALE		1:1		SHEET		OF	REV
													U