



	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--




A	Male							
---	-----------------	--	--	--	--	--	--	--



- Product Specification
 Material
 Insulator : Glass-Filled Thermoplastic PBT, UL94V-0,Black
 Contact : Copper alloy, plating gold flash selective gold
 Shell : Steel, 1000µ" Tin Over 500µ" min Copper
- Electrical
 Contact Resistance : 20 milliohms Max at 1 AMP DC.
 Insulation Resistance : 1000 megohms at 500 VDC
 Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
 Current Rating : 3 AMP
 Voltage Rating : 250 VAC/rms 60Hz
 Wire Spec : 26 AWG-28 AWG
 Operating Temperature:-20°C--+85°C
- ⑤ UL E No #E198287

C	Cover							
---	------------------	--	--	--	--	--	--	--

Order Code:
 A-DXF xx LP111/Z
 Contact style:
 F - Female
 S - Male
 No. of Contacts
 09 / 15 / 25 / 37
 Standard Quality class III



E	Without Insulator Support							
---	--------------------------------------	--	--	--	--	--	--	--

Strain Relief

Dimensions		A	B	C	E	F
Positions						
9		30.81	24.99	16.92	11.08	13.10
15		39.20	33.30	25.25	19.39	20.70
25		53.04	47.04	38.96	33.24	33.68
37		69.40	63.50	55.42	49.86	50.30

F								
---	--	--	--	--	--	--	--	--

G	RoHS compliant							
	Unit:mm							
	Scale	Free	⑤	Correct the UL-File number	03.04.2014	Winnie	Customer-No.	G
	TOLERANCE		④	Update 17.58&17.28 into 17.40&17.10mm	07.03.2014	Winnie		
	X.	±0.38	③	Update the wire specification	28.06.2013	Winnie	ASSMANN WSW-No. A-DXF xx LP111/Z	
	X.X	±0.25	②	Add the wire specification	06.03.2013	Winnie		

Scale	Free	⑤	Correct the UL-File number	03.04.2014	Winnie	Customer-No.		
TOLERANCE		④	Update 17.58&17.28 into 17.40&17.40mm	07.03.2014	Winnie	ASSMANN WSW-No. A-DXF xx LP111/Z		
X.	±0.38							
X.X	±0.25	③	Update the wire specification	28.06.2013	Winnie	Approved	03.04.2014	Winnie
X.XX	±0.13	②	Add the wire specification	06.03.2013	Winnie			
DIM	TOL	①	Add the UL file No.	18.10.2012	Winnie	Drawing-No.		
X.°	±3°							
X.X°	±1.0°	①	Drawn	15.08.2012	Lucas	ASSMANN WSW/ components		
Angle	TOL	Id.	Modification	Date	Name			
						Replace	Sheet 1/2	

	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

