




UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN JEKY.C	DATE 21-May-14	TITLE AFI STR JACK PCB MOUNT		Amphenol RF www.amphenolrf.com	
		ENGINEER T. SMITH	DATE 07-Feb-13				
	REFERENCE EAR # 3289	APPROVED S.HSIEH	DATE 21-May-14	SCALE: 10.0:1.0		SHEET	2 OF 2
	CONFIGURATION LEVEL: ☐ ☐ ☐ ☐	CAD FILE	DWG SIZE B		REV A		ITEM NO.920-266J-51P
	FINISH						PART NO.920-266J-51P