

TLC2801Z, TLC2801Y

Advanced LinCMOS™ LOW-NOISE PRECISION OPERATIONAL AMPLIFIERS

SLOS116B – JULY 1982 – REVISED SEPTEMBER 1996

- **Low Input Noise Voltage:**
35 nV/√Hz Max at f = 10 Hz
15 nV/√Hz Max at f = 1 kHz
- **Low Input Offset Voltage:**
500 μV Max at T_A = 25°C
1.5 mV Max at T_A = Full Range
- **Excellent Offset Voltage Stability With Temperature . . . 4 μV/°C Typ**
- **Low Input Bias Current:**
1 pA Typ at T_A = 25°C
250 pA Typ at T_A = 150°C
- **Specified for Both Single-Supply and Split-Supply Operation**
- **Common-Mode Input Voltage Range Includes the Negative Rail**


description

The TLC2801 is a precision, low-noise operational amplifier manufactured using Texas Instruments Advanced LinCMOS™ process. The TLC2801 combines the noise performance of the lowest-noise JFET amplifiers with the dc precision available previously only in bipolar amplifiers. The Advanced LinCMOS™ process uses silicon-gate technology to obtain input offset voltage stability with temperature and time that far exceeds that obtainable using metal-gate technology. In addition, this technology makes possible input impedance levels that meet or exceed levels offered by top-gate JFET and expensive dielectric-isolated devices.


The combination of excellent dc and noise performance with a common-mode input voltage range that includes the negative rail makes the TLC2801 an ideal choice for high-impedance, low-level signal conditioning applications in either single-supply or split-supply configurations.

The device inputs and output are designed to withstand –100-mA surge currents without sustaining latch-up. In addition, internal ESD-protection circuits prevent functional failures at voltages up to 2000 V as tested under MIL-STD-883C, Method 3015.2; however, care should be exercised in handling these devices as exposure to ESD may result in degradation of the device parametric performance.

The TLC2801 is characterized for operation over the temperature range of –40°C to 150°C.



LARGE-SIGNAL DIFFERENTIAL VOLTAGE AMPLIFICATION vs FREE-AIR TEMPERATURE



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Advanced LinCMOS is a trademark of Texas Instruments Incorporated.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1996, Texas Instruments Incorporated

TLC2801Z, TLC2801Y
Advanced LinCMOS™ LOW-NOISE PRECISION
OPERATIONAL AMPLIFIERS

SLOS116B – JULY 1982 – REVISED SEPTEMBER 1996


AVAILABLE OPTIONS

T _A	V _{IO} max AT 150°C	PACKAGED DEVICES		CHIP FORM (Y)
		SMALL OUTLINE (D)	PLASTIC DIP (P)	
–40°C to 150°C	1.5 mV	TLC2801ZD	TLC2801ZP	TLC2801Y


The D packages are available taped and reeled. Add R suffix to the device type when ordering (e.g., TLC2801ZDR).

TLC2801Y chip information

This chip, properly assembled, displays characteristics similar to the TLC2801. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.



equivalent schematic



TLC2801Z, TLC2801Y

Advanced LinCMOS™ LOW-NOISE PRECISION

OPERATIONAL AMPLIFIERS

SLOS116B – JULY 1982 – REVISED SEPTEMBER 1996

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

Supply voltage, V_{DD+} (see Note 1)	8 V
Supply voltage, V_{DD-} (see Note 1)	–8 V
Differential input voltage, V_{ID} (see Note 2)	±16 V
Input voltage range, V_I (any input, see Note 1)	±8 V
Input current, I_I (each input)	±5 mA
Output current, I_O	±50 mA
Duration of short-circuit current at (or below) 25°C (see Note 3)	unlimited
Operating free-air temperature range, T_A	–40°C to 150°C
Storage temperature range	–65°C to 175°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C

[†] Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. All voltage values, except differential voltages, are with respect to the midpoint between V_{DD+} and V_{DD-} .

2. Differential voltages are at the noninverting input with respect to the inverting point.

3. The output may be shorted to either supply. Temperature and/or supply voltages must be limited to ensure that the maximum dissipation rating is not exceeded.

recommended operating conditions

	MIN	MAX	UNIT
Supply voltage, $V_{DD\pm}$	±2.3	±8	V
Common-mode input voltage, V_{IC}	V_{DD-}	$V_{DD+} - 2.3$	V
Operating free-air temperature, T_A	–40	150	°C



TLC2801Z, TLC2801Y
Advanced LinCMOS™ LOW-NOISE PRECISION
OPERATIONAL AMPLIFIERS

SLOS116B – JULY 1982 – REVISED SEPTEMBER 1996

electrical characteristics at specified free-air temperature, $V_{DD\pm} = \pm 5$ V (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLC2801Z			UNIT
			MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0, \quad R_S = 50 \, \Omega$	25°C		100	500	μV
		Full range			1500	
α_{VIO} Temperature coefficient of input offset voltage		–55°C to 150°C		4		$\mu V/^\circ C$
Input offset voltage long-term drift (see Note 4)		25°C		0.001	0.005	$\mu V/mo$
I_{IO} Input offset current		25°C		0.5		pA
		Full range			3	nA
I_{IB} Input bias current		25°C		1		pA
		Full range			30	nA
V_{ICR} Common-mode input voltage range	$R_S = 50 \, \Omega$	Full range	–5 to 2.7			V
V_{OM+} Maximum positive peak output voltage swing	$R_L = 10 \, k\Omega$	25°C	4.7	4.8		V
		Full range	4.5			
V_{OM-} Maximum negative peak output voltage swing		25°C	–4.7	–4.9		V
		Full range	–4.5			
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 4 \, V, \quad R_L = 500 \, k\Omega$	25°C	300	460		V/mV
		Full range	100			
	$V_O = \pm 4 \, V, \quad R_L = 10 \, k\Omega$	25°C	50	100		
		Full range	15			
CMRR Common-mode rejection ratio	$V_O = 0, \quad R_S = 50 \, \Omega, \quad V_{IC} = V_{ICRmin}$	25°C	90	115		dB
		Full range	85			
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{DD\pm}/\Delta V_{IO}$)	$V_{DD\pm} = \pm 2.3 \, V$ to $\pm 8 \, V$	25°C	90	110		dB
		Full range	85			
I_{DD} Supply current	$V_O = 0, \quad \text{No load}$	25°C		1.1	1.5	mA
		Full range			1.5	

operating characteristics at specified free-air temperature, $V_{DD\pm} = \pm 5$ V

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLC2801Z			UNIT
			MIN	TYP	MAX	
SR Slew rate unity gain	$V_O = \pm 2.3 \, V, \quad R_L = 10 \, k\Omega, \quad C_L = 100 \, pF$	25°C	2	2.7		V/ μs
		Full range	1			
V_n Equivalent input noise voltage	$f = 10 \, Hz$	25°C		18	35	nV/ $\sqrt{Hz}$
	$f = 1 \, kHz$			8	15	
$V_{N(PP)}$ Peak-to-peak equivalent input noise voltage	$f = 0.1$ to $1 \, Hz$	25°C		0.5		μV
	$f = 0.1$ to $10 \, Hz$			0.7		
I_n Equivalent input noise current		25°C		0.6		fA/ $\sqrt{Hz}$
Gain-bandwidth product	$f = 10 \, kHz, \quad R_L = 10 \, k\Omega, \quad C_L = 100 \, pF$	25°C		1.9		MHz
ϕ_m Phase margin at unity gain	$R_L = 10 \, k\Omega, \quad C_L = 100 \, pF$	25°C		48°		

† Full range is –40°C to 150°C.

NOTE 4: Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ C$ extrapolated to $T_A = 25^\circ C$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.



TLC2801Z, TLC2801Y
Advanced LinCMOS™ LOW-NOISE PRECISION
OPERATIONAL AMPLIFIERS

SLOS116B – JULY 1982 – REVISED SEPTEMBER 1996

electrical characteristics at specified free-air temperature, $V_{DD} = 5\text{ V}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLC2801Z			UNIT
			MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0, \quad R_S = 50\ \Omega$	25°C		100	500	μV
		Full range			1500	
α_{VIO} Temperature coefficient of input offset voltage		Full range		4		$\mu\text{V}/^\circ\text{C}$
Input offset voltage long-term drift (see Note 4)		25°C		0.001	0.005	$\mu\text{V}/\text{mo}$
I_{IO} Input offset current		25°C		0.5		pA
		Full range			3	
I_{IB} Input bias current		25°C		1		pA
		Full range			30	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	Full range		–5 to 2.7		V
V_{OH} Maximum high-level output voltage	$R_L = 10\ \text{k}\Omega$	25°C		4.7	4.8	V
		Full range		4.4		
V_{OL} Maximum low-level output voltage		25°C		0	50	mV
		Full range			50	
A_{VD} Large-signal differential voltage amplification	$V_O = 1\text{ V to }4\text{ V},$ $R_L = 500\ \text{k}\Omega$	25°C		150	315	V/mV
		Full range		50		
	$V_O = 1\text{ V to }4\text{ V},$ $R_L = 10\ \text{k}\Omega$	25°C		25	55	
		Full range		5		
CMRR Common-mode rejection ratio	$V_O = 0, \quad V_{IC} = V_{ICR\text{min}},$ $R_S = 50\ \Omega$	25°C		90	110	dB
		Full range		85		
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{DD\pm}/\Delta V_{IO}$)	$V_{DD} = 4.6\text{ V to }16\text{ V}$	25°C		90	110	dB
		Full range		85		
I_{DD} Supply current	$V_O = 0, \quad \text{No load}$	25°C		1.1	1.5	mA
		Full range			1.5	

operating characteristics at specified free-air temperature, $V_{DD} = 5\text{ V}$

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLC2801Z			UNIT
			MIN	TYP	MAX	
SR Slew rate unity gain	$V_O = 0.5\text{ V to }2.5\text{ V},$ $R_L = 10\ \text{k}\Omega, \quad C_L = 100\ \text{pF}$	25°C		1.8	2.5	$\text{V}/\mu\text{s}$
		Full range		0.8		
V_n Equivalent input noise voltage	$f = 10\ \text{Hz}$	25°C		18	35	$\text{nV}/\sqrt{\text{Hz}}$
	$f = 1\ \text{kHz}$	25°C		8	15	
$V_{N(PP)}$ Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ to }1\ \text{Hz}$	25°C		0.5		μV
	$f = 0.1\text{ to }10\ \text{Hz}$	25°C		0.7		
I_n Equivalent input noise current		25°C		0.6		$\text{fA}/\sqrt{\text{Hz}}$
Gain-bandwidth product	$f = 10\ \text{kHz}, \quad R_L = 10\ \text{k}\Omega,$ $C_L = 100\ \text{pF}$	25°C		1.8		MHz
ϕ_m Phase margin at unity gain	$R_L = 10\ \text{k}\Omega, \quad C_L = 100\ \text{pF}$	25°C		45°		

† Full range is -40°C to 150°C .

NOTE 4: Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.



electrical characteristics at $V_{DD} = 5\text{ V}$, $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		TLC2801Z			UNIT
				MIN	TYP	MAX	
V_{IO}	Input offset voltage	$V_{IC} = 0$, $R_S = 50\ \Omega$			100	500	μV
	Input offset voltage long-term drift (see Note 4)				0.001	0.005	$\mu\text{V}/\text{mo}$
I_{IO}	Input offset current				0.5		pA
I_{IB}	Input bias current				1		pA
V_{ICR}	Common-mode input voltage range	$R_S = 50\ \Omega$	$R_S = 50\ \Omega$	0 to 2.7			V
V_{OH}	Maximum high-level output voltage	$R_L = 10\ \text{k}\Omega$	$R_L = 10\ \text{k}\Omega$	4.7	4.8		V
V_{OL}	Maximum low-level output voltage	$I_O = 0$	$I_O = 0$		0	50	mV
A_{VD}	Large-signal differential voltage amplification	$V_O = 1\text{ V to }4\text{ V}$,	$R_L = 500\ \text{k}\Omega$	150	315		V/mV
		$V_O = 1\text{ V to }4\text{ V}$,	$R_L = 10\ \text{k}\Omega$	25	55		
CMRR	Common-mode rejection ratio	$V_O = 0$, $R_S = 50\ \Omega$	$V_{IC} = V_{ICR\text{min}}$, $R_S = 50\ \Omega$	90	110		dB
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD\pm}/\Delta V_{IO}$)	$V_{DD} = 4.6\text{ V to }16\text{ V}$	$V_{DD} = 4.6\text{ V to }16\text{ V}$	90	110		dB
I_{DD}	Supply current	$V_O = 2.5\text{ V}$,	No load		1	1.5	mA

operating characteristics at $V_{DD} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLC2801Z			UNIT
				MIN	TYP	MAX	
SR	Positive slew rate at unity gain	$V_O = 0.5\text{ V to }2.5\text{ V}$, $C_L = 100\ \text{pF}$	$R_L = 10\ \text{k}\Omega$,	1.8	2.5		$\text{V}/\mu\text{s}$
V_n	Equivalent input noise voltage	$f = 10\ \text{Hz}$			18		$\text{nV}/\sqrt{\text{Hz}}$
		$f = 1\ \text{kHz}$			8		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ to }1\ \text{Hz}$			0.5		μV
		$f = 0.1\text{ to }10\ \text{Hz}$			0.7		
I_n	Equivalent input noise current				0.6		$\text{pA}/\sqrt{\text{Hz}}$
	Gain-bandwidth product	$f = 10\ \text{kHz}$, $C_L = 100\ \text{pF}$	$R_L = 10\ \text{k}\Omega$,		1.8		MHz
ϕ_m	Phase margin at unity gain	$R_L = 10\ \text{k}\Omega$,	$C_L = 100\ \text{pF}$		45°		

NOTE 4: Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

PARAMETER MEASUREMENT INFORMATION






Figure 1. Noise-Voltage Test Circuit



NOTE A: C_L includes fixture capacitance.

Figure 2. Phase-Margin Test Circuit



NOTE A: C_L includes fixture capacitance.

Figure 3. Slew-Rate Test Circuit




Figure 4. Input-Bias and Offset-Current Test Circuit

typical values

Typical values as presented in this data sheet represents the median (50% point) of device parametric performance.

input bias and offset current

At the picoamp bias-current level typical of the TLC2801, accurate measurement of the bias current becomes difficult. Not only does this measurement require a picoammeter, but test socket leakages can easily exceed the actual device bias currents. To measure these small currents, Texas Instruments uses a two-step process. The socket leakage is measured using picoammeters with bias voltage applied but with no device in the socket. The device is then inserted in the socket and a second test measuring both the socket leakage and the device input bias current is performed. The two measurements are then subtracted algebraically to determine the bias current of the device.

TYPICAL CHARACTERISTICS

Table of Graphs

			FIGURE
I_{IB}	Input bias current	vs Free-air temperature	5
V_{OM}	Maximum peak output voltage	vs Free-air temperature	6
V_{OH}	High-level output voltage	vs Free-air temperature	7
V_{OL}	Low-level output voltage	vs Free-air temperature	8
A_{VD}	Differential voltage amplification	vs Free-air temperature	9
I_{OS}	Short-circuit output current	vs Free-air temperature	10
I_{DD}	Supply current	vs Free-air temperature	11
SR	Slew rate	vs Free-air temperature	12
Gain-bandwidth product		vs Free-air temperature	13




Figure 5




Figure 6

TLC2801Z, TLC2801Y

Advanced LinCMOS™ LOW-NOISE PRECISION OPERATIONAL AMPLIFIERS

SLOS116B – JULY 1982 – REVISED SEPTEMBER 1996

TYPICAL CHARACTERISTICS




Figure 7




Figure 8




Figure 9




Figure 10

TYPICAL CHARACTERISTICS




Figure 11




Figure 12




Figure 13

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.