

## CMOS Logic MN4000B Series

MN4082B/MN4082BS

6932852 PANASONIC INDL. ELECTRONIC

66C 05058 D T-43-21

**MN4082B / MN4082BS**


## Dual 4-Input AND Gates

## ■ Description


The MN4082B/S are dual 4-input AND gates. The outputs are fully buffered to improve the propagation characteristics between the input and output which are affected by increasing load capacitance and minimizes propagation delay time. Their primary use is where low power dissipation and/or high noise immunity is desired.

The MN4082B/S are equivalent to MOTOROLA MC14082B and RCA CD4082B.

## ■ Schematic Diagram (1/2)



P-1




14-Pin • Plastic DIL Package

P-2



14-Pin • Pinflat Package (SO-14D)

## Pin Configuration

■ Maximum Ratings ( $T_a = 25^\circ\text{C}$ )

| Item                                    | Symbol    | Ratings                                                    | Unit             |
|-----------------------------------------|-----------|------------------------------------------------------------|------------------|
| Supply Voltage                          | $V_{DD}$  | $-0.5 \sim +18$                                            | V                |
| Input Voltage                           | $V_I$     | $-0.5 \sim V_{DD} + 0.5^*$                                 | V                |
| Output Voltage                          | $V_O$     | $-0.5 \sim V_{DD} + 0.5^*$                                 | V                |
| Peak Input • Output Current             | $\pm I_I$ | max. 10                                                    | mA               |
| Power Dissipation (per package)         | $P_D$     | max. 400                                                   | mW               |
|                                         |           | Decrease up to 200mW rating at $8\text{mW}/^\circ\text{C}$ |                  |
| Power Dissipation (per output terminal) | $P_D$     | max. 100                                                   | mW               |
| Operating Ambient Temperature           | $T_{opr}$ | $-40 \sim +85$                                             | $^\circ\text{C}$ |
| Storage Temperature                     | $T_{stg}$ | $-65 \sim +150$                                            | $^\circ\text{C}$ |

\*  $V_{DD} + 0.5\text{V}$  should be under 18V

**CMOS Logic MN4000B Series**  
 6932852 PANASONIC INDL, ELECTRONIC

 MN4082B/MN4082BS  
 66C 05059 D T-43-21


**■ DC Characteristics ( $V_{SS}=0V$ )**

| Item                              | $V_{DD}$<br>(V) | Sym-<br>bol | Conditions                                                                                      | $T_a=-40^\circ C$ |      | $T_a=25^\circ C$ |      | $T_a=85^\circ C$ |      | Unit    |
|-----------------------------------|-----------------|-------------|-------------------------------------------------------------------------------------------------|-------------------|------|------------------|------|------------------|------|---------|
|                                   |                 |             |                                                                                                 | min.              | max. | min.             | max. | min.             | max. |         |
| Quiescent Power<br>Supply Current | 5               | $I_{DD}$    | $V_I=V_{SS}$ or $V_{DD}$                                                                        | —                 | 1    | —                | 1    | —                | 7.5  | $\mu A$ |
|                                   | 10              |             |                                                                                                 | —                 | 2    | —                | 2    | —                | 15   |         |
|                                   | 15              |             |                                                                                                 | —                 | 4    | —                | 4    | —                | 30   |         |
| Output Voltage<br>Low Level       | 5               | $V_{OL}$    | $V_I=V_{SS}$ or $V_{DD}$<br>$ I_O  < 1\mu A$                                                    | —                 | 0.05 | —                | 0.05 | —                | 0.05 | V       |
|                                   | 10              |             |                                                                                                 | —                 | 0.05 | —                | 0.05 | —                | 0.05 |         |
|                                   | 15              |             |                                                                                                 | —                 | 0.05 | —                | 0.05 | —                | 0.05 |         |
| Output Voltage<br>High Level      | 5               | $V_{OH}$    | $V_I=V_{SS}$ or $V_{DD}$<br>$ I_O  < 1\mu A$                                                    | 4.95              | —    | 4.95             | —    | 4.95             | —    | V       |
|                                   | 10              |             |                                                                                                 | 9.95              | —    | 9.95             | —    | 9.95             | —    |         |
|                                   | 15              |             |                                                                                                 | 14.95             | —    | 14.95            | —    | 14.95            | —    |         |
| Input Voltage<br>Low Level        | 5               | $V_{IL}$    | $ I_O  < 1\mu A$<br>$V_O=0.5V$ or $4.5V$<br>$V_O=1V$ or $9V$<br>$V_O=1.5V$ or $13.5V$           | —                 | 1.5  | —                | 1.5  | —                | 1.5  | V       |
|                                   | 10              |             |                                                                                                 | —                 | 3    | —                | 3    | —                | 3    |         |
|                                   | 15              |             |                                                                                                 | —                 | 4    | —                | 4    | —                | 4    |         |
| Input Voltage<br>High Level       | 5               | $V_{IH}$    | $ I_O  < 1\mu A$<br>$V_O=0.5V$ or $4.5V$<br>$V_O=1V$ or $9V$<br>$V_O=1.5V$ or $13.5V$           | 3.5               | —    | 3.5              | —    | 3.5              | —    | V       |
|                                   | 10              |             |                                                                                                 | 7                 | —    | 7                | —    | 7                | —    |         |
|                                   | 15              |             |                                                                                                 | 11                | —    | 11               | —    | 11               | —    |         |
| Output Current<br>Low Level       | 5               | $I_{OL}$    | $V_O=0.4V$ , $V_I=0$ or $5V$<br>$V_O=0.5V$ , $V_I=0$ or $10V$<br>$V_O=1.5V$ , $V_I=0$ or $15V$  | 0.52              | —    | 0.44             | —    | 0.36             | —    | mA      |
|                                   | 10              |             |                                                                                                 | 1.3               | —    | 1.1              | —    | 0.9              | —    |         |
|                                   | 15              |             |                                                                                                 | 3.6               | —    | 3                | —    | 2.4              | —    |         |
| Output Current<br>High Level      | 5               | $-I_{OH}$   | $V_O=4.6V$ , $V_I=0$ or $5V$<br>$V_O=9.5V$ , $V_I=0$ or $10V$<br>$V_O=13.5V$ , $V_I=0$ or $15V$ | 0.52              | —    | 0.44             | —    | 0.36             | —    | mA      |
|                                   | 10              |             |                                                                                                 | 1.3               | —    | 1.1              | —    | 0.9              | —    |         |
|                                   | 15              |             |                                                                                                 | 3.6               | —    | 3                | —    | 2.4              | —    |         |
| Output Current High Level         | 5               | $-I_{OH}$   | $V_O=2.5V$ , $V_I=0$ or $5V$                                                                    | 1.7               | —    | 1.4              | —    | 1.1              | —    | mA      |
| Input Leakage Current             | 15              | $\pm I_I$   | $V_I=0$ or $15V$                                                                                | —                 | 0.3  | —                | 0.3  | —                | 1    | $\mu A$ |


**■ Switching Characteristics ( $T_a=25^\circ C$ ,  $V_{SS}=0V$ ,  $C_L=50pF$ )**

| Item                   | $V_{DD}$ (V) | Symbol    | min. | typ. | max. | Unit |
|------------------------|--------------|-----------|------|------|------|------|
| Output Rise Time       | 5            | $t_{TLH}$ | —    | 60   | 180  | ns   |
|                        | 10           |           | —    | 30   | 90   |      |
|                        | 15           |           | —    | 20   | 60   |      |
| Output Fall Time       | 5            | $t_{THL}$ | —    | 60   | 180  | ns   |
|                        | 10           |           | —    | 30   | 90   |      |
|                        | 15           |           | —    | 20   | 60   |      |
| Propagation Delay Time | 5            | $t_{PLH}$ | —    | 65   | 195  | ns   |
|                        | 10           |           | —    | 30   | 90   |      |
|                        | 15           |           | —    | 25   | 75   |      |
| Propagation Delay Time | 5            | $t_{PHL}$ | —    | 65   | 195  | ns   |
|                        | 10           |           | —    | 30   | 90   |      |
|                        | 15           |           | —    | 25   | 75   |      |
| Input Capacitance      |              | $C_I$     | —    | —    | 7.5  | pF   |

1. Switching Time Test Circuit



2. Waveforms



Panasonic

— 168 —