

## 74LCXP16245

# Low Voltage 16-Bit Bidirectional Transceiver with 5V Tolerant Inputs/Outputs and Pull-Down Resistors

### General Description

The LCXP16245 contains sixteen non-inverting bidirectional buffers with 3-STATE outputs and is intended for bus oriented applications. The device is designed for low voltage (2.5V or 3.3V)  $V_{CC}$  applications with capability of interfacing to a 5V signal environment. The device is byte controlled. Each byte has separate control inputs which could be shorted together for full 16-bit operation. The T/R inputs determine the direction of data flow through the device. The OE inputs disable both the A and B ports by placing them in a high impedance state.

In addition, A and B port datapath pins have built-in resistors to GND allowing the pins to float without any increase in  $I_{CC}$  current. This feature is intended to address modular and space constrained applications where additional space consumed by external resistors is not available.

The LCXP16245 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining CMOS low power dissipation.

### Features

- 5V tolerant inputs and outputs
- 2.3V–3.6V  $V_{CC}$  specifications provided
- I/O pull-down resistors terminate inactive busses ensuring a stable bus state
- 5.5 ns  $t_{PD}$  max ( $V_{CC} = 3.3V$ ,  $20\mu A$ ,  $I_{CC}$  max)
- Power down high impedance inputs and outputs
- Supports live insertion/removal (Note 1)
- $\pm 24$  mA output drive ( $V_{CC} = 2.5V$ )
- Implements proprietary noise/EMI reduction circuitry
- Pin compatible with 74 series 16245
- Switching performance exceeds 500 nA
- ESD performance:
  - Human body model > 2000V
  - Machine model > 200V


**Note 1:** To ensure the high-impedance state during power up or down OE should be tied to  $V_{CC}$  through a pull-up resistor; the minimum value or the resistor is determined by the current-sourcing capability of the driver.

### Ordering Code

| Order Number  | Package | Number | Package Description                                                         |
|---------------|---------|--------|-----------------------------------------------------------------------------|
| 74LCXP16245A  | SSOP    | 8A     | 48-Lead Small Shrink Outline Package (SSOP), JEDEC MO-118, 0.300" Wide      |
| 74LCXP16245MT | TSSOP   | 48     | 48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide |

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.


### Logic Symbol



### Pin Descriptions

| Pin Names          | Description                      |
|--------------------|----------------------------------|
| $\overline{OE}_n$  | Output Enable Input              |
| $T/\overline{R}_n$ | Transmit/Receive Input           |
| $A_0$ – $A_{15}$   | Side A Inputs or 3-STATE Outputs |
| $B_0$ – $B_{15}$   | Side B Inputs or 3-STATE Outputs |

## Connection Diagram



## Truth Tables

| Inputs            |         | Outputs                                                                                  |
|-------------------|---------|------------------------------------------------------------------------------------------|
| $\overline{OE}_1$ | $T/R_1$ |                                                                                          |
| L                 | L       | Bus B <sub>0</sub> –B <sub>7</sub> Data to Bus A <sub>0</sub> –A <sub>7</sub>            |
| L                 | H       | Bus A <sub>0</sub> –A <sub>7</sub> Data to Bus B <sub>0</sub> –B <sub>7</sub>            |
| H                 | X       | HIGH Z State on A <sub>0</sub> –A <sub>7</sub> , B <sub>0</sub> –B <sub>7</sub> (Note 2) |

| Inputs            |         | Outputs                                                                                    |
|-------------------|---------|--------------------------------------------------------------------------------------------|
| $\overline{OE}_2$ | $T/R_2$ |                                                                                            |
| L                 | L       | Bus B <sub>8</sub> –B <sub>15</sub> Data to Bus A <sub>8</sub> –A <sub>15</sub>            |
| L                 | H       | Bus A <sub>8</sub> –A <sub>15</sub> Data to Bus B <sub>8</sub> –B <sub>15</sub>            |
| H                 | X       | HIGH Z State on A <sub>8</sub> –A <sub>15</sub> , B <sub>8</sub> –B <sub>15</sub> (Note 2) |

H = HIGH Voltage Level

L = LOW Voltage Level

X = Immaterial

Z = High Impedance


**Note 2:** A and B port inputs are tri-state.

## Functional Descriptions

The LCXP16245 contains sixteen non-inverting functional buffers with 3-STATE outputs. The device is byte controlled. Each byte has separate control inputs, which can be shorted together for full 16-bit operation. The T/R inputs determine the direction of data flow through the device.

The OE inputs disable both the A and B ports by placing them in a high impedance state. The pulldown resistor (30K $\Omega$  normal) to GND is active only when the outputs are 3-STATE ( $\overline{OE}$  = HIGH). When the outputs become active ( $\overline{OE}$  = LOW) the resistor is removed from the circuit.

## Logic Diagram



| Absolute Maximum Ratings <sup>(Note 3)</sup> |                                  |                                               |                                                           |       |
|----------------------------------------------|----------------------------------|-----------------------------------------------|-----------------------------------------------------------|-------|
| Symbol                                       | Parameter                        | Value                                         | Conditions                                                | Units |
| V <sub>CC</sub>                              | Supply Voltage                   | −0.5 to +7.0                                  |                                                           | V     |
| V <sub>I</sub>                               | DC Input Voltage                 | −0.5 to +7.0                                  |                                                           | V     |
| V <sub>O</sub>                               | DC Output Voltage                | −0.5 to +7.0<br>−0.5 to V <sub>CC</sub> + 0.5 | Output in 3-STATE<br>Output in HIGH or LOW State (Note 4) | V     |
| I <sub>IK</sub>                              | DC Input Diode Current           | −50                                           | V <sub>I</sub> < GND                                      | mA    |
| I <sub>OK</sub>                              | DC Output Diode Current          | −50<br>+50                                    | V <sub>O</sub> < GND<br>V <sub>O</sub> > V <sub>CC</sub>  | mA    |
| I <sub>O</sub>                               | DC Output Source/Sink Current    | ±50                                           |                                                           | mA    |
| I <sub>CC</sub>                              | DC Supply Current per Supply Pin | ±100                                          |                                                           | mA    |
| I <sub>GND</sub>                             | DC Ground Current per Ground Pin | ±100                                          |                                                           | mA    |
| T <sub>STG</sub>                             | Storage Temperature              | −65 to +150                                   |                                                           | °C    |

| Recommended Operating Conditions |                                                                      |                                                                                                 |                        |       |
|----------------------------------|----------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|------------------------|-------|
| Symbol                           | Parameter                                                            | Min                                                                                             | Max                    | Units |
| V <sub>CC</sub>                  | Supply Voltage                                                       | Operating: 2.3<br>Data Retention: 1.5                                                           | 3.6<br>3.6             | V     |
| V <sub>I</sub>                   | Input Voltage                                                        | 0                                                                                               | 5.5                    | V     |
| V <sub>O</sub>                   | Output Voltage                                                       | HIGH: 0<br>3-STATE: 0                                                                           | V <sub>CC</sub><br>5.5 | V     |
| I <sub>OH</sub> /I <sub>OL</sub> | Output Current                                                       | V <sub>CC</sub> = 3.0V – 3.6V<br>V <sub>CC</sub> = 2.7V – 3.0V<br>V <sub>CC</sub> = 2.3V – 2.7V | ±24<br>±12<br>±8       | mA    |
| T <sub>A</sub>                   | Free-Air Operating Temperature                                       | −40                                                                                             | 85                     | °C    |
| Δt/ΔV                            | Input Edge Rate, V <sub>IN</sub> = 1.8V–2.0V, V <sub>CC</sub> = 3.0V | 0                                                                                               | 10                     | ns/V  |

**Note 3:** The Absolute Maximum Ratings are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the Absolute Maximum Ratings. The “Recommended Operating Conditions” will define the conditions for actual device operation.

**Note 4:** I<sub>O</sub> Absolute Maximum Rating must be observed.

| DC Electrical Characteristics |                           |                                                                                                                                          |                                       |                                                   |                                  |       |
|-------------------------------|---------------------------|------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------|---------------------------------------------------|----------------------------------|-------|
| Symbol                        | Parameter                 | Conditions                                                                                                                               | V <sub>CC</sub><br>(V)                | T <sub>A</sub> = −40°C to +85°C                   |                                  | Units |
|                               |                           |                                                                                                                                          |                                       | Min                                               | Max                              |       |
| V <sub>IH</sub>               | HIGH Level Input Voltage  |                                                                                                                                          | 2.3 – 2.7<br>2.7 – 3.6                | 1.7<br>2.0                                        |                                  | V     |
| V <sub>IL</sub>               | LOW Level Input Voltage   |                                                                                                                                          | 2.3 – 2.7<br>2.7 – 3.6                |                                                   | 0.7<br>0.8                       | V     |
| V <sub>OH</sub>               | HIGH Level Output Voltage | I <sub>OH</sub> = −100 μA<br>I <sub>OH</sub> = −8 mA<br>I <sub>OH</sub> = −12 mA<br>I <sub>OH</sub> = −18 mA<br>I <sub>OH</sub> = −24 mA | 2.3 – 3.6<br>2.3<br>2.7<br>3.0<br>3.0 | V <sub>CC</sub> − 0.2<br>1.8<br>2.2<br>2.4<br>2.2 |                                  | V     |
| V <sub>OL</sub>               | LOW Level Output Voltage  | I <sub>OL</sub> = 100 μA<br>I <sub>OL</sub> = 8 mA<br>I <sub>OL</sub> = 12 mA<br>I <sub>OL</sub> = 16 mA<br>I <sub>OL</sub> = 24 mA      | 2.3 – 3.6<br>2.3<br>2.7<br>3.0<br>3.0 |                                                   | 0.2<br>0.6<br>0.4<br>0.4<br>0.55 | V     |
| I <sub>I</sub>                | Input Leakage Current     | 0 ≤ V <sub>I</sub> ≤ 5.5V                                                                                                                | 2.3 – 3.6                             |                                                   | ±5.0                             | μA    |
| I <sub>OZ(L)</sub>            | 3-STATE I/O Leakage       | V <sub>I</sub> or V <sub>O</sub> = 0.0V                                                                                                  | 2.3 – 3.6                             |                                                   | ±5.0                             | μA    |
| I <sub>OZ(H)</sub>            | 3-STATE I/O Leakage       | V <sub>I</sub> or V <sub>O</sub> = 5.5V                                                                                                  | 2.3 – 3.6                             | 50                                                | 500                              | μA    |
| I <sub>OFF</sub>              | Power-Off Leakage Current | V <sub>I</sub> or V <sub>O</sub> = 5.5V                                                                                                  | 0                                     |                                                   | 10                               | μA    |
| I <sub>CC</sub>               | Quiescent Supply Current  | V <sub>I</sub> = V <sub>CC</sub> or GND<br>3.6V ≤ V <sub>I</sub> , V <sub>O</sub> ≤ 5.5V (Note 5)                                        | 2.3 – 3.6<br>2.3 – 3.6                |                                                   | 20<br>±20                        | μA    |

**DC Electrical Characteristics** (Continued)

| Symbol          | Parameter                             | Conditions                               | V <sub>CC</sub><br>(V) | T <sub>A</sub> = -40°C to +85°C |     | Units |
|-----------------|---------------------------------------|------------------------------------------|------------------------|---------------------------------|-----|-------|
|                 |                                       |                                          |                        | Min                             | Max |       |
| $\Delta I_{CC}$ | Increase in I <sub>CC</sub> per Input | V <sub>IH</sub> = V <sub>CC</sub> - 0.6V | 2.3 - 3.6              |                                 | 500 | μA    |

Note 5: Outputs disabled or 3-STATE only.

**AC Electrical Characteristics**

| Symbol            | Parameter                                                            | T <sub>A</sub> = -40°C to +85°C, R <sub>L</sub> = 500Ω |     |                        |     |                               |     | Units |
|-------------------|----------------------------------------------------------------------|--------------------------------------------------------|-----|------------------------|-----|-------------------------------|-----|-------|
|                   |                                                                      | V <sub>CC</sub> = 3.3V ± 0.3V                          |     | V <sub>CC</sub> = 2.7V |     | V <sub>CC</sub> = 2.5V ± 0.2V |     |       |
|                   |                                                                      | C <sub>L</sub> = 50 pF                                 |     | C <sub>L</sub> = 50 pF |     | C <sub>L</sub> = 50 pF        |     |       |
|                   |                                                                      | Min                                                    | Max | Min                    | Max | Min                           | Max |       |
| t <sub>PHL</sub>  | Propagation Delay                                                    | 1.5                                                    | 5.5 | 1.5                    | 6.0 | 1.5                           | 6.6 | ns    |
| t <sub>PLH</sub>  | A <sub>n</sub> to B <sub>n</sub> or B <sub>n</sub> to A <sub>n</sub> | 1.5                                                    | 5.5 | 1.5                    | 6.0 | 1.5                           | 6.6 |       |
| t <sub>PZL</sub>  | Output Enable Time                                                   | 1.5                                                    | 7.0 | 1.5                    | 8.0 | 1.5                           | 9.1 | ns    |
| t <sub>PZH</sub>  |                                                                      | 1.5                                                    | 7.0 | 1.5                    | 8.0 | 1.5                           | 9.1 |       |
| t <sub>PLZ</sub>  | Output Disable Time                                                  | 1.5                                                    | 7.0 | 1.5                    | 8.0 | 1.5                           | 8.4 | ns    |
| t <sub>PHZ</sub>  |                                                                      | 1.5                                                    | 7.0 | 1.5                    | 7.0 | 1.5                           | 8.4 |       |
| t <sub>OSHL</sub> | Output to Output Skew (Note 6)                                       |                                                        | 1.0 |                        |     |                               |     | ns    |
| t <sub>OSLH</sub> |                                                                      |                                                        | 1.0 |                        |     |                               |     |       |


Note 6: Skew is defined as the absolute value of the difference between the actual propagation delays of any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t<sub>OSHL</sub>) or LOW-to-HIGH (t<sub>OSLH</sub>). Parameter guaranteed by design.

**Dynamic Switching Characteristics**







| Symbol           | Parameter                           | Conditions                                                           | V <sub>CC</sub><br>(V) | T <sub>A</sub> = 25°C | Units |
|------------------|-------------------------------------|----------------------------------------------------------------------|------------------------|-----------------------|-------|
|                  |                                     |                                                                      |                        | Typical               |       |
| V <sub>OLP</sub> | Quiet Output Dynamic Peak Voltage   | C <sub>L</sub> = 50 pF, V <sub>IH</sub> = 3.3V, V <sub>IL</sub> = 0V | 3.3                    | 0.8                   | V     |
|                  |                                     | C <sub>L</sub> = 30 pF, V <sub>IH</sub> = 2.5V, V <sub>IL</sub> = 0V | 2.5                    | 0.6                   |       |
| V <sub>OLV</sub> | Quiet Output Dynamic Valley Voltage | C <sub>L</sub> = 50 pF, V <sub>IH</sub> = 3.3V, V <sub>IL</sub> = 0V | 3.3                    | -0.8                  | V     |
|                  |                                     | C <sub>L</sub> = 30 pF, V <sub>IH</sub> = 2.5V, V <sub>IL</sub> = 0V | 2.5                    | -0.6                  |       |

**Capacitance**

| Symbol           | Parameter                     | Conditions                                                                  | Typical | Units |
|------------------|-------------------------------|-----------------------------------------------------------------------------|---------|-------|
| C <sub>IN</sub>  | Input Capacitance             | V <sub>CC</sub> = Open, V <sub>I</sub> = 0V or V <sub>CC</sub>              | 7       | pF    |
| C <sub>I/O</sub> | Input/Output Capacitance      | V <sub>CC</sub> = 3.3V, V <sub>I</sub> = 0V or V <sub>CC</sub>              | 8       | pF    |
| C <sub>PD</sub>  | Power Dissipation Capacitance | V <sub>CC</sub> = 3.3V, V <sub>I</sub> = 0V or V <sub>CC</sub> , f = 10 MHz | 20      | pF    |


**AC LOADING and WAVEFORMS** Generic for LCX Family**FIGURE 1. AC Test Circuit ( $C_L$  includes probe and jig capacitance)**


| Test                  | Switch                                                                        |
|-----------------------|-------------------------------------------------------------------------------|
| $t_{PLH}$ , $t_{PHL}$ | Open                                                                          |
| $t_{PZL}$ , $t_{PLZ}$ | 6V at $V_{CC} = 3.3 \pm 0.3V$<br>$V_{CC} \times 2$ at $V_{CC} = 2.5 \pm 0.2V$ |
| $t_{PZH}$ , $t_{PHZ}$ | GND                                                                           |

**Waveform for Inverting and Non-Inverting Functions****3-STATE Output High Enable and Disable Times for Logic****Propagation Delay, Pulse Width and  $t_{rec}$  Waveforms****Setup Time, Hold Time and Recovery Time for Logic****3-STATE Output Low Enable and Disable Times for Logic****FIGURE 2. Waveforms**  
(Input Characteristics;  $f = 1\text{MHz}$ ,  $t_r = t_f = 3\text{ns}$ )

| Symbol   | $V_{CC}$        |                 |                  |
|----------|-----------------|-----------------|------------------|
|          | $3.3V \pm 0.3V$ | $2.7V$          | $2.5V \pm 0.2V$  |
| $V_{mi}$ | 1.5V            | 1.5V            | $V_{CC}/2$       |
| $V_{mo}$ | 1.5V            | 1.5V            | $V_{CC}/2$       |
| $V_x$    | $V_{OL} + 0.3V$ | $V_{OL} + 0.3V$ | $V_{OL} + 0.15V$ |
| $V_y$    | $V_{OH} - 0.3V$ | $V_{OH} - 0.3V$ | $V_{OH} - 0.15V$ |


# Schematic Diagram Generic for LCX Family



**Physical Dimensions** inches (millimeters) unless otherwise noted


**48-Lead Small Shrink Outline Package (SSOP), JEDEC MO-116, 0.300" Wide**  
**Package Number MS48A**

## Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide  
Package Number MTD48

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)

**DISCONTINUED**  
THIS DEVICE IS NOT RECOMMENDED FOR NEW DESIGN  
PLEASE CONTACT YOUR onsemi  
REPRESENTATIVE FOR INFORMATION

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910  
**Japan Customer Focus Center**  
Phone: 81-3-5817-1050

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)

**Order Literature:** <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative