


LOC		DIST		REVISIONS					
J				变更					
P	LTR	DESCRIPTION						DATE	APVD
	B	REVISED ECR-11-019335						20SEP2011	C.W



NON	AVAILABLE	△4	3	18	70	48.7	280	2-912071-1	2-6123098-0
NON	NOT AVAILABLE	△2	3	18	70	48.7	280	2-912071-1	1-6123098-0
SEALANT	TOOLING STATUS	FINISH	ROW	QTY	B	A	POS.	TRAY P/N	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL
材料

GENERAL TOLERANCE
一般公差

10≥:±0.2
30≥ >10:±0.25
100≥ >30:±0.3
ANGLES:±3°

DWN HAWKING HE 13DEC04
CHK STEVEN YAO 13DEC04
APVD I.ENOMOTO 13DEC04
PRODUCT SPEC
製品規格
108-60047
APPLICATION SPEC
取付適用規格
114-5255
WEIGHT

STE TE Connectivity

HARD TRAY ASSY
FH 0.6BTB CONNECTOR
PLUG 12H W/G-PLATE 2ROW TYPE

SIZE CAGE CODE DRAWING NO
A300779C-6123098


RESTRICTED TO

CUSTOMER DRAWING

SCALE 1:2

SHEET 1 OF 2

REV B




① MATERIAL ; HOUSING : HIGH TEMP THERMO PLASTIC
UL94V-0
CONTACT : COPPER ALLOY

② FINISH ; UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002 MIN Au PL.
SOLDERING AREA 0.001 MIN TIN PL.

③ ■ THIS POSITION IS GROUND CIRCUIT.

④ FINISH ; UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.00076 MIN Au PL.
SOLDERING AREA 0.001 MIN TIN PL.

45.8	44.6	41.4	44	48.7	48.7	280	1-1123097-0
F	E	D	C	B	A	POS	CAP P/N



GENERAL TOLERANCE
一般公差

10 $\geq$: ± 0.2
30 $\geq$ >10: ± 0.25
100 $\geq$ >30: ± 0.3
ANGLES: $\pm 3^\circ$



0	PLC	$\pm$ -
1	PLC	$\pm$ -
2	PLC	$\pm$ -
3	PLC	$\pm$ -
4	PLC	$\pm$ -
ANGLES		$\pm$ -

MATERIAL	材料
----------	----

CUSTOMER DRAWING

TE Connectivity

A

HARD TRAY ASSY
WITH 0.6BTB CONNECTOR
2H W/G-PLATE 2ROW TYPE

A

SCALE	2:1
尺碼	

SHEET 2 OF 2

REV	
-----	--