

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [87437-1042](#)
Status: **Active**
Overview: [Pico-Spox™](#)
Description: 1.50mm Pitch Pico-SPOX™ Wire-to-Board Header, Surface Mount, Vertical, Shrouded, 10 Circuits, Tube Packaging, Lead-Free

Documents:

- [3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-87437 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	87437
Application	Signal, Wire-to-Board
Overview	Pico-Spox™
Product Literature Order No	USA-235
Product Name	Pico-SPOX™
UPC	822348438747

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	474.000/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	1.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Surface Mount

Electrical




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[87437Series](#)

Mates With

[87439](#) Pico-SPOX™ Wire-to-Board Housing,
[87421](#) Pico-SPOX™ Crimp Terminal

Current - Maximum per Contact1.5A, 2A, 3A

Voltage - Maximum350V

Material Info

Reference - Drawing Numbers

Product SpecificationPS-87437, RPS-87437, RPS-87437-001,
RPS-87437-200

Sales DrawingSD-87437-**31

This document was generated on 01/16/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

87437-1042