

DC - DC Converters



Features:


- Low Cost
- 4 : 1 wide input range
- I / O Isolation
- Input Pi Filter
- Short Circuit Protection
- High Performance
- 2 Years Warranty

Model List

Model No.	Input Voltage	Output Wattage	Output Voltage	Output Current	EFF. (Minimum)
Single Output Models					
FDD12-05S4	10 to 36 V dc	12 W	+5 V dc	2,400 mA	77%
FDD12-12D4			±12 V dc	±500 mA	


Circuit Schematic

Block diagram for FDD12 series with single output



Model No.	Input Voltage	Output Wattage	Output Voltage	Output Current	EFF. (Minimum)
Dual Output Model					
FDD12-12S4	10 to 36 V dc	12 W	+12 V dc	1,000 mA	77%

Block diagram for FDD12 series with dual output



DC - DC Converters



Specifications

All specifications typical at nominal line, full load, 25°C unless otherwise noticed

General					
Characteristics	Conditions	Minimum	Typical	Maximum	Unit
Switching Frequency	Vi nom, Io nom	-	200	-	KHz
Isolation Voltage	Input / Output	1,500	-	-	V dc
Isolation Resistance	Input / Output, at 500 V dc	100	-	-	MΩ
Ambient Temperature	Operating at Vi nom, Io nom	-25	-	+71	°C
Case Temperature	Operating at Vi nom, Io nom	-	-	+100	
Derating	Vi nom	See derating curve			% / °C
Storage Temperature	Non operational	-40	-	+100	°C
M.T.B.F.	According to MIL-HDBK-217F, GF40	-	661,000	-	Hours
Dimension	L50.8 × W50.8 × H11.9				mm
Cooling	Free air convection				
Case Material	Metal				

Input Specifications

Characteristics	Conditions		Minimum	Typical	Maximum	Unit
Input Voltage Range	Ta minimum to Ta maximum, Io nom		10	24	36	V dc
			18	48	72	
No Load Input Current	Vi nom, Io = 0	24 V Models	-	-	20	mA
		48 V Models	-	-	15	
Input Voltage w/o Damage	Io nom	24 V Models	-	-	40	V dc
		48 V Models	-	-	75	
Input Filter	Pi type					

Output Specifications


Characteristics	Conditions		Minimum	Typical	Maximum	Unit
Output Voltage Accuracy	Vi nom, Io nom		-	-	±2	%
Minimum load	Vi nom	Single output model	0	-	-	
		Dual output model (each output)	20	-	-	
Line Regulation	Io nom, Vi minimum to Vi maximum		-	-	±1	
Load Regulation	Vi nom, Io 0 to Io nom, single output models		-	-	±2	
	Vi nom, Io minimum to Io nom, dual output models		-	-	±5	
Transient Recovery Time	Vi nom, Io nom to 1/2 Io nom		-	500	-	µs
Temperature Coefficient	Vi nom, Io nom		-	-	±0.02	% / °C
Ripple and Noise	Vi nom, Io nom, BW = 20 MHz	3.3 V model 5 V, 12 V and dual	-	-	100	mV
			-	-	Vout × 1%	
Efficiency	Vi nom, Io nom, Po / Pi		Up to 77%, see model list			

DC - DC Converters



Control and Protection	
Input Reversed	Shunt diode built in, external fuse recommended
Output Short Circuit	Continuous

Mechanism and Pin Configuration



Bottom View

Dimensions : Millimetres (Inches)


Physical Characteristics

Case Size	50.8 × 50.8 × 11.9 mm 2 × 2 × 0.47 inches
Case Material	Metal
Weight	65 g (type)

Pin Assignment

General		
Pin No.	Single	Dual
1	Vi+	Vi+
2	Vi-	Vi-
3	Vo+	Vo+
4	NO PIN	com
5	Vo-	Vo-

Derating



Part Number Table

Description	Part Number
Converter, DC / DC, 12 W, 5 V	FDD12-05S4
Converter, DC / DC, 12 W, ±12 V	FDD12-12D4
Converter, DC / DC, 12 W, 12 V	FDD12-12S4

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

