


C14 IEC Fused Inlet - Vertical

VERTICAL MODULE ARRANGEMENT



- Fused Inlet with 2.8mm or 6.3mm tabs
- Double Pole Switch or Indicator Variations
- Filtered Inlet Option
- Options of I/O marked switches



How to Order

BZV **xx** / **xxxxx** / **xx**

Type of Inlet / Outlet

Single Fused C14 Power Inlet (cold condition),
6.3 or 2.8mm tabs:

01 = PF0011/63
02 = PF0011/28

Twin Fused C14 Power Inlet (cold condition),
6.3 or 2.8mm tabs:

15 = PF0033/63
16 = PF0033/28

Filtered or Non Filtered Inlet

Z0000 = Non Filtered

Axxxx = Standard

Bxxxx = Medical

Cxxxx = High Performance Standard
(Single Fuse Version only)

For Filtered inlet use 6th to 9th characters from filter
ordering code see pages 97-100.

E.g. BZV01/**A0620**/10

Combination of Other Components

Neon Indicator:

D3 = Red Neon Indicator

Double Pole Switch:

10 = D.P. Switch

Double Pole Neon Switch:

11 = D.P. Red Neon Switch

12 = D.P. Green Neon Switch

Double Pole High Inrush Switch:

13 = D.P. High Inrush Switch

Double Pole Switch Marked I/O:

70 = D.P. Switch (I/O)

Double Pole Neon Switch Marked (I/O):

76 = D.P. Red Neon Switch (I/O)

77 = D.P. Green Neon Switch (I/O)

Double Pole High Inrush Switch Marked
(I/O):

78 = D.P. High Inrush Switch (I/O)

B1 = D.P. High Inrush Green Neon Switch
(I/O)

Note: For technical details of individual components please see page 74