






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		C	REVISED PER ECO-11-019758	14FEB2012	CJV	CWR



SECTION J-J

- 1 LCP, UL 94V-0 RATED, BLACK.
- 2 PHOSPHOR BRONZE.
- 3 2.54μm [.000100] MIN BRIGHT TIN.
- 4 3.81μm [.000150] MIN MATTE TIN ON SOLDER END, 1.27μm [.000050] MIN GOLD ON MATING END FOR A LENGTH OF 2.54 [.100] MIN ON MATING SURFACE, ALL OVER 1.27μm [.000050] MIN NICKEL.
- 5 KEY IDENTIFICATION LETTER AND DATE CODE HOT STAMPED ON HOUSING, THIS SURFACE, LOCATED APPROXIMATELY AS SHOWN.
- 6 DIMENSION INDICATES CONTACT MATING AREA.
- 7 PLATING MEASUREMENT POINT.

OBSOLETE	E	5-1761205-1
	D	4-1761205-1
	KEY IDENT LETTER	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN B. MCMASTER 30APR04	 TE Connectivity			
		CHK C. ROHDE 30APR04				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY 30APR04	NAME RECEPTACLE ASSEMBLY, 4 POSITION, SIDE ENTRY GND, SDL			
		PRODUCT SPEC 108-2047				
	0 PLC ± -	APPLICATION SPEC 114-2081	SIZE A2	CAGE CODE 00779	DRAWING NO C-1761205	RESTRICTED TO -
	1 PLC ± -	WEIGHT -				
MATERIAL 	FINISH 	2 PLC ± 0,13 [.005]				
		3 PLC ± -				
		4 PLC ± -				
		ANGLES ± ±				