

Heli-Coil insert specifications – inch

Nominal Thread Size	Type		Size Designation	"Q" Nominal Length					Outside Diameter		Number of Coils Nominal Length				
	Standard Insert No.	Screw-Lock Insert No.		1 Dia.	1-1/2 Dia.	2 Dia.	2-1/2 Dia.	3 Dia.	Min.	Max.	1 Dia.	1-1/2 Dia.	2 Dia.	2-1/2 Dia.	3 Dia.
UNIFIED COARSE															
1 (.073)-64	1185	3585	01CN	0.073	0.110	0.146	0.182	0.219	.095	.103	2-3/4	4-7/8	6-7/8	8-7/8	10-7/8
2 (.086)-56	1185	3585	02CN	0.086	0.129	0.172	0.215	0.258	.110	.119	3	5-1/4	7-3/8	9-5/8	11-7/8
3 (.099)-48	1185	3585	03CN	0.099	0.148	0.198	0.248	0.297	.128	.139	2-7/8	5	7-1/4	9-3/8	11-1/2
4 (.112)-40	1185	3585	04CN	0.112	0.168	0.224	0.280	0.336	.144	.159	2-3/4	4-3/4	6-3/4	8-7/8	10-7/8
5 (.125)-40	1185	3585	05CN	0.125	0.188	0.250	0.312	0.375	.158	.173	3-1/4	5-1/2	7-3/4	10	12-1/4
6 (.138)-32	1185	3585	06CN	0.138	0.207	0.276	0.345	0.414	.178	.193	2-3/4	4-3/4	6-7/8	8-7/8	10-7/8
8 (.164)-32	1185	3585	2CN	0.164	0.246	0.328	0.410	0.492	.205	.220	3-1/2	6	8-3/8	10-3/4	13-1/4
10 (.190)-24	1185	3585	3CN	0.190	0.285	0.380	0.475	0.570	.244	.259	2-7/8	5	7-1/8	9-1/4	11-3/8
12 (.216)-24	1185	3585	1CN	0.216	0.324	0.432	0.540	0.648	.270	.285	3-1/2	6	8-3/8	10-5/8	13-1/8
1/4 (.2500)-20	1185	3585	4CN	0.250	0.375	0.500	0.625	0.750	.310	.330	3-3/8	5-3/4	8	10-3/8	12-3/4
5/16 (.3125)-18	1185	3585	5CN	0.312	0.469	0.625	0.781	0.938	.380	.400	4	6-5/8	9-1/4	11-7/8	14-5/8
3/8 (.3750)-16	1185	3585	6CN	0.375	0.562	0.750	0.938	1.125	.452	.472	4-3/8	7-1/4	10	12-7/8	15-3/4
7/16 (.4375)-14	1185	3585	7CN	0.438	0.656	0.875	1.094	1.312	.526	.551	4-1/2	7-3/8	10-1/4	13-1/8	16-1/8
1/2 (.5000)-13	1185	3585	8CN	0.500	0.750	1.000	1.250	1.500	.597	.622	4-7/8	7-7/8	11	14-1/8	17-1/8
9/16 (.5625)-12	1185	3585	9CN	0.562	0.844	1.125	1.406	1.688	.669	.694	5-1/8	8-1/4	11-1/2	14-3/4	17-7/8
5/8 (.6250)-11	1185	3585	10CN	0.625	0.938	1.250	1.562	1.875	.742	.767	5-1/4	8-1/2	11-3/4	15	18-3/8
3/4 (.7500)-10	1185	3585	12CN	0.750	1.125	1.500	1.875	2.250	.881	.906	5-7/8	9-3/8	13	16-1/2	20-1/8
7/8 (.8750)-9	1185	3585	14CN	0.875	1.312	1.750	2.188	2.625	1.022	1.052	6-1/4	10	13-3/4	17-1/2	21-1/4
1 (1.000)-8	1185	3585	16CN	1.000	1.500	2.000	2.500	3.000	1.166	1.196	6-3/8	10-1/8	14	17-3/4	21-5/8
1-1/8 (1.1250)-7	1185	3585	18CN	1.125	1.688	2.250	2.812	3.375	1.315	1.355	6-1/8	9-7/8	13-5/8	17-1/2	21-1/4
1-1/4 (1.2500)-7	1185	3585	20CN	1.250	1.875	2.500	3.125	3.750	1.443	1.483	7	11-1/4	15-3/8	19-1/2	23-3/4
1-3/8 (1.3750)-6	1185	3585	22CN	1.375	2.062	2.750	3.438	4.125	1.598	1.643	6-1/2	10-1/2	14-3/8	18-3/8	22-1/4
1-1/2 (1.5000)-6	1185	3585	24CN	1.500	2.250	3.000	3.750	4.500	1.727	1.772	7-1/4	11-1/2	15-7/8	20-1/8	24-1/2
UNIFIED FINE															
2 (.086)-64	1191	3591	02CN	0.086	0.129	0.172	0.215	0.258	.110	.119	3-1/2	5-7/8	8-3/8	10-3/4	13-1/8
3 (.099)-56	1191	3591	03CN	0.099	0.148	0.198	0.248	0.297	.131	.146	3-3/8	5-5/8	8	10-3/8	12-5/8
4 (.112)-48	1191	3591	04CN	0.112	0.168	0.224	0.280	0.336	.147	.162	3-3/8	5-5/8	7-7/8	10-1/4	12-1/2
6 (.138)-40	1191	3591	06CN	0.138	0.207	0.276	0.345	0.414	.173	.193	3-1/2	6	8-3/8	10-3/4	13-1/4
8 (.164)-36	1191	3591	2CN	0.164	0.246	0.328	0.410	0.492	.204	.224	3-7/8	6-1/2	9-1/8	11-5/8	14-1/4
10 (.190)-32	1191	3591	3CN	0.190	0.285	0.380	0.475	0.570	.236	.256	4-1/8	6-7/8	9-1/2	12-1/4	14-7/8
1/4 (.2500)-28	1191	3591	4CN	0.250	0.375	0.500	0.625	0.750	.306	.326	5	8-1/4	11-3/8	14-1/2	17-5/8
5/16 (.3125)-24	1191	3591	5CN	0.312	0.469	0.625	0.781	0.938	.380	.400	5-1/2	8-7/8	12-1/4	15-5/8	19
3/8 (.3750)-24	1191	3591	6CN	0.375	0.562	0.750	0.938	1.125	.448	.468	6-7/8	11	15	19-1/8	23-1/8
7/16 (.4375)-20	1191	3591	7CN	0.438	0.656	0.875	1.094	1.312	.524	.549	6-5/8	10-5/8	14-5/8	18-1/2	22-1/2
1/2 (.5000)-20	1191	3591	8CN	0.500	0.750	1.000	1.250	1.500	.592	.617	7-7/8	12-3/8	16-7/8	21-3/8	25-7/8
9/16 (.5625)-18	1191	3591	9CN	0.562	0.844	1.125	1.406	1.688	.666	.691	8	12-1/2	17-1/8	21-3/4	26-1/4
5/8 (.6250)-18	1191	3591	10CN	0.625	0.938	1.250	1.562	1.875	.733	.758	9	14-1/8	19-1/4	24-1/4	29-3/8
3/4 (.7500)-16	1191	3591	12CN	0.750	1.125	1.500	1.875	2.250	.876	.901	9-3/4	15-1/8	20-5/8	26	31-1/2
7/8 (.8750)-14	1191	3591	14CN	0.875	1.312	1.750	2.188	2.625	1.021	1.051	9-7/8	15-1/2	21-1/8	26-5/8	32-1/4
1 (1.000)-14*	1191	3591	16CN	1.000	1.500	2.000	2.500	3.000	1.156	1.186	11-1/2	17-7/8	24-1/4	30-5/8	37
1 (1.000)-12	1191	3591	161CN	1.000	1.500	2.000	2.500	3.000	1.169	1.199	9-5/8	15	20-1/2	26	31-1/2
1-1/8 (1.1250)-12	1191	3591	18CN	1.125	1.688	2.250	2.812	3.375	1.304	1.334	11-1/8	17-1/4	23-3/8	29-1/2	35-3/4
1-1/4 (1.2500)-12	1191	3591	20CN	1.250	1.875	2.500	3.125	3.750	1.439	1.469	12-1/2	19-3/8	26-1/4	33	39-7/8
1-3/8 (1.3750)-12	1191	3591	22CN	1.375	2.062	2.750	3.438	4.125	1.575	1.610	13-3/4	21-3/8	28-7/8	36-1/2	44
1-1/2 (1.5000)-12	1191	3591	24CN	1.500	2.250	3.000	3.750	4.500	1.710	1.745	15-1/4	23-1/2	31-5/8	39-7/8	48-1/8

*Inactive for new design.

1185-4CNY375S

Type	Size	Material	Finish	Length	Packaging
1185 Free Running, Coarse	See Chart	CN – Stainless Steel	Blank – None	See Chart	Blank – Bulk
1191 Free Running, Fine		BN – Phosphor Bronze	Y – Cadmium		S – Strip Feed
3585 Screw-Lock, Coarse		TN – Inconel X	V – Silver		
3591 Screw-Lock, Fine		EN – Nitronic 60	W – Dry Film Lubricant		
		GN – Titanium	HG – Primer Free		

Complete Part No. Example:
1/4-20 x .375 Free Running Insert, Cadmium plated on Strip Feed.

Notes on Insert Specifications:

- Nominal Length is a computed value and cannot be measured. It is the actual assembled length + 1/2 pitch.
- The number of coils are counted 90° from the tang.
- Grip Coil(s) Location: for 1, 1-1/2 and 2 diameter long inserts, Grip Coil Location = 1/2 the number of free coils. For 2-1/2 and 3 diameter long inserts, Grip Coil Location (distance from the tang) is the same as 2 diameter long inserts.