







10 9 8 7 6 5 4 3 2 1


ENG. NO.		Au. PLATE THICKNESS (μ m MIN.)
FORM: LOOSE	FORM: CHAIN	
50394-8100	50394-8051	0.38
50394-8200	50394-8052	0.76
50394-8400	50394-8054	GOLD FLASH 0.05-0.125 μ m



B-B





A-A



NOTES :

1. APPLICABLE HOUSING : 51110-***1
: 51110-**5*

WINDING DIRECTION



VIEW Z

ADD WINDING DIRECTION EC NO: S2014-0327 DRWN:ATSEE CHKD:FANNYWONG APPR:LBLEE REV B1	DESCRIPTION 2013/09/30 2013/09/30 2013/11/13	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		F A =0	4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE SALES DRAWING 2.0MM GRID W TO B CONN. CRIMP TERMINAL				
			3 PLACES	± ---	± ---	CHECKED BY	DATE					
			2 PLACES	± 0.20	± ---	EDPOH	1994/04/27					
			1 PLACE	± ---	± ---	APPROVED BY	DATE	molex				
			0 PLACE	± ---	± ---	BBYEE	2013/04/28					
		ANGULAR ± 3 °			MATERIAL NO.			DOCUMENT NO.			SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE			SD-50394-8XXX 1 OF 1				
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

9 8 7 6 5 4 3 2 1