



SPECIFICATIONS

• CONSTRUCTION

Sealed pushbutton switch. Rear mounting for easier installation, variable panel thickness.

• MATERIALS


Case : PBT , UL94-V0
Plunger : Polyamide 6/6
Bushing/Collar : Brass, nickel plated
Contacts : Silver, gold plated

• ELECTRICAL CHARACTERISTICS

Electrical function : Normally open (NO)
Maximum ratings : 200mA 48VDC – 200mA 250VAC
Electrical life : 500 000 cycles minimum
Contact resistance : 100 milliohms Max
Insulation resistance: 1 Gigaohms min - 500 VDC
Dielectric strength : 1000 VAC rms 50Hz

• MECHANICAL AND ENVIRONMENTAL CHARACTERISTICS

Total travel : 1.8±0.3mm
Degree of protection : IP65
Robustness : IK06 according to EN 50102 (1 joule)
Temperature range : -40°C to +85°C
Panel thickness : 3mm



Replace the blank digit with the following color code

Code	1	2	3	4	5	6	7/1	8	9
Plunger Colour	Blue	Black	Green	Grey	Yellow	Red	White	Bright Chrome	Orange

		MATERIAL:	 Unité INTERRUPTEURS 55,av E.HERRIOT BP 1 82303 CAUSSADE CEDEX Tél:05.63.93.14.98 - Télécopie:05.63.93.19.03		DRAWN: F.Ricard	
		TREATMENT:			DATE : 28-01-2011	
		FINISH:			CHECKED: D.Sire	
		Scale: 3			Reference: DIP029S	
		PUSHBUTTON SWITCH			Code Nbr.	
		IZMR3S4_N				
Issue	Modifications	Date	Name			