

REV. Status

PRELIMINARY
02/13/01 MP

TELECOMMUNICATION V.90 MODEM TRANSFORMER


A. Electrical Specifications (@ 25° C)

1. Primary Impedance; 600Ω
2. Secondary Impedance; 560Ω
3. Insertion Loss: 1.5dB MAX @ 1KHz, 0dBm
4. Frequency Response; ±0.5dB @ 200Hz to 4KHz, 0dBm
5. Longitudinal Balance; 60dB MIN @ 200Hz to 4KHz, 0dBm
(Per IEEE Method)
6. Return Loss; 14dB MIN @ 200Hz to 4KHz, 0dBm
7. DC Resistance;
(1-3):60Ω ±15%
(4-6):78Ω ±15%
8. Turns Ratio; (1-3):(6-4)=1:1.00±2%
9. Total Harmonic Distortion;
-76dB MAX @ 600Hz, -10dBm
10. Dielectric Strength; 1875V 1 second, Pri-Sec





B. Marking; TTC-5016, TAMURA, date code and country of origin

C. Safety; Complies with UL1950 3rd Edition

D. Schematic;



E. Mechanical Specifications;



MODEL NUMBER

TTC-5016

PREPARED BY:

D. Rund

ENGINEER:

M. Pitchai

QUALITY CONTROL:

APPROVED:

J. Coleman

DWG CONTROL NO.
P-A1-12728
ACAD\TTC\A1127281.DWGREV
PRETELECOMMUNICATION V.90
MODEM TRANSFORMER

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

TTC-5016

MODEL SPECIFICATION

DIM: mm(In) SCL: 2/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.