


Technical drawing of a mechanical part with dimensions in inches and millimeters:

- Top horizontal dimension: 0.42 [10.7]
- Right vertical dimension: .25 [6.4]
- Left vertical dimension: 06 .5]
- Bottom horizontal dimension: 1.00 [25.4]
- Bottom right horizontal dimension: 0.20 (5.1)



*1. SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATION FOR
PACKAGE SIZE.

2. HOLE FOR STANDARD S6 FLAT HEAD SCREW.

CAD FILENAME/LAYERS G00239LU_DC_SGABM25S6_00



CORP. TINLEY PARK, ILLINOIS

SGABM25-S6-_
4 WAY MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY TMSA

MAT'L:

SCALE	2X
-------	----

2X

DATE	8/24/05
------	---------

SEE TABLE

DRAWING NO.

GB0239LU

DWG
A
SIZE

R	8/24/05	TMSA		INITIAL RELEASE OF NEW PART NUMBER SGABM25-S6-_	GB0239LU	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	